


7. PLEASE CONTACT FOXCONN SALES REPRESENTATIVE TO VERIFY PRODUCT DETAILS & AVAILABILITY.

A 3D perspective view of a mechanical part. It is a cross-shaped plate with a central rectangular hole. There are four smaller rectangular holes, one on each arm of the cross. The part is shown in a light gray color with black outlines.







X.± 0.5	X.± 1°	UNITS mm	NAME(INTENDED USE) SOCKET SP3 BP	 FOXCONN INTERCONNECT TECHNOLOGY LIMITED.			
.X± 0.2	.X± 0.5°	MAT'L					
.XX± 0.1	.XX'±		PART NO.(INTENDED USE) WNMEP06-90*0*-EH	CLASS: ☐ CONFIDENTIAL ☐ SECRET ☒ GENERAL			
.XXX±	.XXX'±	FINISH	APPD: Nick Lin	TITLE: CUSTOMER DRAWING FOR SOCKET SP3 BP			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF FOXCONN INTERCONNECT TECHNOLOGY LIMITED, AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF FOXCONN INTERCONNECT TECHNOLOGY LIMITED.			Q'TY	DWG NO.: 351-0000-1405			
			CHKD: Mac Peng DRAW: Roy 11/17' 20	 <table border="1"> <thead> <tr> <th>SCALE</th> <th>SHEET</th> <th>REV.</th> </tr> </thead> <tbody> <tr> <td>1: 1</td> <td>1/2</td> <td>E</td> </tr> </tbody> </table>	SCALE	SHEET	REV.
SCALE	SHEET	REV.					
1: 1	1/2	E					

PART NUMBER	STUD HEIGHT	PCB THICKNESS	THICKNESS RANGE
WNMEP06-90100-EH	4.8	2.36	1.95-2.66
WNMEP06-90200-EH	5.6	3.18	2.90-3.45
WNMEP06-90300-EH	4.0	1.57	1.27-1.90

IDEAS GENERATED DRAWING, DO NOT CHANGE BY HAND.

ENDNOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.
3. MATERIAL : BACK PLATE CARBON STEEL (SPCC) WITH 100u' min NI PLATING;
STUD CARBON STEEL (1018) WITH 80u' min NI PLATING;
INSULATOR PC1860B, (UL 94VTM-0);
4. 'BACK PLATE SP3(VER. -B)' IS LOCATED APPROXIMATELY.
5. 'FOXCONN' AND 'DATECODE' ARE LOCATED APPROXIMATELY.
6. THE CONCENTRATIONS OF Br & Cl CAN SATISFY THE REQUIREMENTS OF HALOGEN-FREE IN DOCUMENT EPI12.
7. PLEASE CONTACT FOXCONN SALES REPRESENTATIVE TO VERIFY PRODUCT DETAILS & AVAILABILITY.



PCB KEEP-OUT ZONE FOR SOCKET SP3 BACK PLATE

X.± 0.5	X.± 1*	UNITS	mm	NAME(INTENDED USE)	 FOXCONN INTERCONNECT TECHNOLOGY LIMITED.
.X± 0.2	.X± 0.5*	MAT'L		SOCKET SP3 BP	
.XX± 0.1	.XX±			PART NO.(INTENDED USE)	CLASS:
.XXX±	.XXX±	FINISH		WNMEP06-90*0*-EH	☐ CONFIDENTIAL ☐ SECRET ☒ GENERAL
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF FOXCONN INTERCONNECT TECHNOLOGY LIMITED, AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF FOXCONN INTERCONNECT TECHNOLOGY LIMITED.				APPD:	TITLE:
				Nick Lin	CUSTOMER DRAWING FOR SOCKET SP3 BP
				CHKD: Mac Peng	DWG NO.: 351-0000-1405
				DRAW: Roy 11/17'20	SCALE SHEET REV.
					1:1 2/2 E

PART NUMBER	STUD HEIGHT	PCB THICKNESS	THICKNESS RANGE
WNMEP06-90101-EH	4.8	2.36	1.95-2.66
WNMEP06-90201-EH	5.6	3.18	2.90-3.45
WNMEP06-90301-EH	4.0	1.57	1.27-1.90