


Description:

This P-Channel MOSFET uses advanced trench technology and design to provide excellent $R_{DS(on)}$ with low gate charge.

It can be used in a wide variety of applications.

Features:

- 1) $V_{DS}=-60V, I_D=-40A, R_{DS(on)}<35m\Omega @V_{GS}=-10V$ (Typ : $28m\Omega$)
- 2) Low gate charge.
- 3) Green device available.
- 4) Advanced high cell density trench technology for ultra $R_{DS(on)}$.
-) Excellent package for good heat dissipation.



Absolute Maximum Ratings: ($T_C=25^\circ C$ unless otherwise noted)

Symbol	Parameter	Ratings	Units
V_{DS}	Drain-Source Voltage	-60	V
V_{GS}	Gate-Source Voltage	± 20	V
I_D	Continuous Drain Current-	-40	A
	Continuous Drain Current- $T_C=100^\circ C$	-24	
	Pulsed Drain Current ¹	-120	
E_{AR}	Single Pulse Avalanche Energy ³	77	mJ
P_D	Power Dissipation	75	W
T_J, T_{STG}	Operating and Storage Junction Temperature Range	-55 to +150	$^\circ C$

Thermal Characteristics:

Symbol	Parameter	Max	Units
$R_{\theta JC}$	Thermal Resistance, Junction to Case	1.67	$^\circ C/W$

Package Marking and Ordering Information:

Part NO.	Marking	Package
DOP40P06	40P06	TO-220







Electrical Characteristics: ($T_C=25^{\circ}\text{C}$ unless otherwise noted)







Symbol	Parameter	Conditions	Min	Typ	Max	Units
Off Characteristics						
BV _{DSS}	Drain-Sourctce Breakdown Voltage	V _{GS} =0V, I _D =250 μ A	-60	---	---	V
I _{DSS}	Zero Gate Voltage Drain Current	V _{GS} =0V, V _{DS} =-60V	---	---	-10	μ A
I _{GSS}	Gate-Source Leakage Current	V _{GS} =± 20V, V _{DS} =0A	---	---	± 10	nA
On Characteristics						
V _{GS(th)}	GATE-Source Threshold Voltage	V _{GS} =V _{DS} , I _D =250 μ A	-1		-2	V
R _{DS(ON)}	Drain-Source On Resistance ⁴	V _{GS} =-10V, I _D =-15A	---	28	35	m Ω
		V _{GS} =-4V, I _D =-15A	---	38	55	
Dynamic Characteristics						
C _{iss}	Input Capacitance	V _{DS} =-10V, V _{GS} =0V, f=1MHz	---	2500	---	pF
C _{OSS}	Output Capacitance		---	1300	---	
C _{rss}	Reverse Transfer Capacitance		---	300	---	
Switching Characteristics						
t _{d(on)}	Turn-On Delay Time	V _{DD} =-0V, I _D =-15A, R _L =2 Ω .V _{GS} =-10V	---	25	---	ns
t _r	Rise Time		---	150	---	ns
t _{d(off)}	Turn-Off Delay Time		---	350	---	ns
t _f	Fall Time		---	220	---	ns
Q _g	Total Gate Charge	V _{GS} =-10V, V _{DS} =-50V, I _D =-10A	---	25	---	nC
Q _{gs}	Gate-Source Charge		---	5	---	nC
Q _{gd}	Gate-Drain “Miller” Charge		---	7	---	nC
Drain-Source Diode Characteristics						
Trr	Reverse Recovery Time		---	35	---	nS



Notes:

1. $PW \leq 10\mu s$, duty cycle $\leq 1\%$
2. Value at $T_C = 25^{\circ}\text{C}$
3. Value at $T_{ch} = 25^{\circ}\text{C}$, $R_g \geq 50\Omega$
4. Pulse test


Typical Characteristics: ($T_c=25^\circ\text{C}$ unless otherwise noted)







Avalanche Test Circuit



Avalanche Waveform

$$E_{AR} = \frac{1}{2} \cdot L \cdot I_{AP}^2 \cdot \frac{V_{DSS}}{V_{DSS} - V_{DD}}$$

