

VUA Series

Features

- 6.3 ϕ ~ 18 ϕ , 125°C, 1,000 ~ 2,000 hours assured
- Chip type high temperature range, for +125°C use
- For automobile modules and other high temperature applications
- RoHS compliant
- AEC-Q200 compliant



Marking color: Black

Specifications

Items	Performance																																		
Category Temperature Range	-40℃ ~ +125℃																																		
Capacitance Tolerance	± 20% (at 120 Hz, 20℃)																																		
Leakage Current (at 20℃)	I = 0.03CV or 4 (μA) whichever is greater (after 1 minutes) Where, C = rated capacitance in μF, V = rated DC working voltage in V																																		
Tanδ (at 120 Hz, 20℃)	<table><tr><td>Rated Voltage</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td><td>63</td></tr><tr><td>Tanδ (max.)</td><td>0.32</td><td>0.24</td><td>0.21</td><td>0.18</td><td>0.15</td><td>0.15</td></tr></table> When the capacitance exceeds 1,000 μF, 0.02 shall be added every 1,000μF increase.							Rated Voltage	10	16	25	35	50	63	Tanδ (max.)	0.32	0.24	0.21	0.18	0.15	0.15														
Rated Voltage	10	16	25	35	50	63																													
Tanδ (max.)	0.32	0.24	0.21	0.18	0.15	0.15																													
Low Temperature Characteristics (at 120 Hz)	Impedance ratio shall not exceed the values given in the table below. <table><tr><td colspan="2">Rated Voltage</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td><td>63</td></tr><tr><td rowspan="2">Impedance Ratio</td><td>Z(-25℃) / Z(+20℃)</td><td>6</td><td>5</td><td>4</td><td>3</td><td>3</td><td>3</td></tr><tr><td>Z(-40℃) / Z(+20℃)</td><td>12</td><td>8</td><td>6</td><td>4</td><td>4</td><td>4</td></tr></table>							Rated Voltage		10	16	25	35	50	63	Impedance Ratio	Z(-25℃) / Z(+20℃)	6	5	4	3	3	3	Z(-40℃) / Z(+20℃)	12	8	6	4	4	4					
Rated Voltage		10	16	25	35	50	63																												
Impedance Ratio	Z(-25℃) / Z(+20℃)	6	5	4	3	3	3																												
	Z(-40℃) / Z(+20℃)	12	8	6	4	4	4																												
Endurance	<table><tr><td>Test Time</td><td colspan="6">1,000 Hrs for ϕ D ≤ 8 × 6.5 mm 2,000 Hrs for ϕ D ≥ 8 × 10 mm</td></tr><tr><td>Capacitance Change</td><td colspan="6">Within ± 30% of initial value</td></tr><tr><td>Tanδ</td><td colspan="6">Less than 300% of specified value</td></tr><tr><td>Leakage Current</td><td colspan="6">Within specified value</td></tr></table> * The above specifications shall be satisfied when the capacitors are restored to 20℃ after the rated voltage applied for 1,000 / 2,000 hours at 125℃.							Test Time	1,000 Hrs for ϕ D ≤ 8 × 6.5 mm 2,000 Hrs for ϕ D ≥ 8 × 10 mm						Capacitance Change	Within ± 30% of initial value						Tanδ	Less than 300% of specified value						Leakage Current	Within specified value					
Test Time	1,000 Hrs for ϕ D ≤ 8 × 6.5 mm 2,000 Hrs for ϕ D ≥ 8 × 10 mm																																		
Capacitance Change	Within ± 30% of initial value																																		
Tanδ	Less than 300% of specified value																																		
Leakage Current	Within specified value																																		
Shelf Life Test	<table><tr><td>Test Time</td><td colspan="6">1,000 Hrs</td></tr><tr><td>Capacitance Change</td><td colspan="6">Within ± 30% of initial value</td></tr><tr><td>Tanδ</td><td colspan="6">Less than 300% of specified value</td></tr><tr><td>Leakage Current</td><td colspan="6">Within specified value</td></tr></table> * The above specifications shall be satisfied when the capacitors are restored to 20℃ after exposing them for 1,000 hours at 125℃ without voltage applied.							Test Time	1,000 Hrs						Capacitance Change	Within ± 30% of initial value						Tanδ	Less than 300% of specified value						Leakage Current	Within specified value					
Test Time	1,000 Hrs																																		
Capacitance Change	Within ± 30% of initial value																																		
Tanδ	Less than 300% of specified value																																		
Leakage Current	Within specified value																																		
Ripple Current and Frequency Multipliers	<table><tr><td>Freq.(Hz) Cap.(μF)</td><td>50</td><td>120</td><td>1k</td><td>10k up</td></tr><tr><td>≤ 330</td><td>0.80</td><td>1.0</td><td>1.25</td><td>1.40</td></tr><tr><td>330 < C ≤ 4,700</td><td>0.85</td><td>1.0</td><td>1.20</td><td>1.30</td></tr></table>							Freq.(Hz) Cap.(μF)	50	120	1k	10k up	≤ 330	0.80	1.0	1.25	1.40	330 < C ≤ 4,700	0.85	1.0	1.20	1.30													
Freq.(Hz) Cap.(μF)	50	120	1k	10k up																															
≤ 330	0.80	1.0	1.25	1.40																															
330 < C ≤ 4,700	0.85	1.0	1.20	1.30																															

Diagram of Dimensions

Fig. 1





Fig. 2



Lead Spacing and Diameter


Unit: mm

φ D	L	A	B	C	W	P	Fig. No.
6.3	5.7 ± 0.3	6.6	6.6	7.2	0.5 ~ 0.8	2.0	1
6.3	7.7 ± 0.3	6.6	6.6	7.2	0.5 ~ 0.8	2.0	1
8	6.5 ± 0.3	8.3	8.3	9.0	0.5 ~ 0.8	2.3	1
8	10 ± 0.5	8.3	8.3	9.0	0.7 ~ 1.1	3.1	1
10	10 ± 0.5	10.3	10.3	11.0	0.7 ~ 1.1	4.7	1
12.5	13.5 ± 0.5	13.0	13.0	13.7	1.1 ~ 1.4	4.4	2
12.5	16 ± 0.5	13.0	13.0	13.7	1.1 ~ 1.4	4.4	2
16	16.5 ± 0.5	17.0	17.0	18.0	1.1 ~ 1.4	6.4	2
18	16.5 ± 0.5	19.0	19.0	20.0	1.1 ~ 1.4	6.4	2


The diagram is marking " () " for reference dimension.

Marking


$\phi D = 6.3 \text{ mm}$



$\phi D = 8 \sim 10 \text{ mm}$



$\phi D \geq 12.5 \text{ mm}$



Dimension and Permissible Ripple Current

Dimension: $\phi D \times L (\text{mm})$

Ripple Current: mA/rms at 120 Hz, 125°C

Rated Volt. (Voc)		10V (1A)		16V (1C)		25V (1E)		35V (1V)		50V (1H)		63V (1J)	
Cap. (μF)	Contents	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA
10	100											8×6.5	60
22	220							6.3×5.7	50	8×6.5	75	8×10	100
33	330			6.3×5.7	50	6.3×5.7	50	6.3×7.7	70	8×10	130	10×10	150
47	470			6.3×7.7	70	6.3×7.7	70	8×6.5	75	8×10	130	10×10	150
68	680	6.3×5.7	50	8×6.5	75	8×6.5	75	8×10	130	10×10	180	10×10	150
100	101	8×6.5	75	8×6.5	75	8×10	130	10×10	180	12.5×13.5	357	12.5×13.5	300
220	221	8×10	130	10×10	180	10×10	180	12.5×13.5	357	12.5×16	400	16×16.5	600
330	331	8×10	130	12.5×13.5	480	12.5×13.5	480	16×16.5	650	16×16.5	650	16×16.5	600
470	471	12.5×13.5	480	12.5×13.5	480	12.5×13.5	480	16×16.5	650	16×16.5	650	18×16.5	800
680	681	12.5×13.5	480	12.5×13.5	480	12.5×16	585	16×16.5	650	18×16.5	855		
1,000	102	12.5×16	585	12.5×16	585	16×16.5	650	18×16.5	855				
1,500	152	12.5×16	585	16×16.5	650	18×16.5	855						
2,200	222	16×16.5	650	18×16.5	855								
3,300	332	18×16.5	855										
4,700	472	18×16.5	855										

Part Numbering System

VUA Series	33μF	± 20%	16V	Carrier Tape	6.3 ϕ × 5.7L	General Purpose
VUA	330	M	1C	TR	-	0606
Series Name	Capacitance	Capacitance Tolerance	Rated Voltage	Package Type	Terminal Type	Case Size
						Application

Note: For more details, please refer to "Part Numbering System - SMD Type" on page 106.