

1W isolated DC-DC converter  
Fixed input voltage, regulated single output



Continuous Short  
Circuit Protection

RoHS



Patent Protection

### FEATURES

- Continuous short-circuit protection
- No-load input current as low as 8mA
- Operating ambient temperature range: -40°C to +85°C
- High efficiency up to 75%
- I/O isolation test voltage 3k VDC
- Industry standard pin-out

CE Report UKCA Report CB

EN 62368-1 BS EN 62368-1 IEC 62368-1

IF\_S-1WR3 series is especially designed for distributed power supply systems where an isolated voltage is required. They are suitable for occasions of: pre-interference isolation, ground interference elimination, pure digital circuit, voltage isolation conversion, general low frequency analog circuit, relay drive circuit, etc.

### Selection Guide

Certification	Part No.	Input Voltage (VDC) Nominal (Range)	Output		Full Load Efficiency (%) Min./Typ.	Capacitive Load (µF) Max.
			Voltage (VDC)	Current (mA) Max./Min.		
EN/BS EN	IF0503S-1WR3	5 (4.75-5.25)	3.3	250/25	63/67	2400
EN/BS EN/IEC	IF0505S-1WR3		5	200/20	66/70	2400
	IF0509S-1WR3		9	111/12	67/71	1000
	IF0512S-1WR3		12	84/9	68/72	560
	IF0515S-1WR3		15	67/7	69/73	560
EN/BS EN	IF0524S-1WR3		24	41/4	69/73	100
EN/BS EN/IEC	IF1205S-1WR3	12 (11.4-12.6)	5	200/20	69/73	2400
EN/BS EN	IF1209S-1WR3		9	111/12	69/73	1000
EN/BS EN/IEC	IF1212S-1WR3		12	83/9	69/73	560
	IF1215S-1WR3		15	67/7	71/75	560
EN/BS EN	IF1505S-1WR3	15 (14.25-15.75)	5	200/20	69/73	2400
	IF1515S-1WR3		15	67/7	71/75	560
	IF2403S-1WR3	24 (22.8-25.2)	3.3	250/25	65/71	2400
	IF2405S-1WR3		5	200/20	67/73	2400
	IF2409S-1WR3		9	111/12	67/73	1000
	IF2412S-1WR3		12	83/9	67/73	560
	IF2415S-1WR3		15	67/7	67/73	560

### Input Specifications

Item	Operating Conditions		Min.	Typ.	Max.	Unit
Input Current (full load / no-load)	5V input	3.3VDC/5VDC output	--	286/8	303/--	mA
		9VDC/12VDC output	--	282/12	299/--	
		15VDC/24VDC output	--	274/18	290/--	
Input Current (full load / no-load)	12V input	5VDC/9VDC/12VDC output	--	115/8	121/--	mA
		15VDC output	--	112/8	118/--	
	15V input	5VDC output	--	92/8	97/--	
		15VDC output	--	89/8	94/--	
	24V input	3.3VDC output	--	59/8	65/--	
		5VDC/9VDC/12VDC/15VDC output	--	58/8	63/--	
Reflected Ripple Current*			--	15	--	

Input Filter		Capacitance Filter
Hot Plug		Unavailable
Note: * Refer to DC-DC Converter Application Notes for detailed description of reflected ripple current test method.		

### Output Specifications

Item	Operating Conditions		Min.	Typ.	Max.	Unit	
Voltage Accuracy			--	--	±3	%	
Linear Regulation	Input voltage change: ±1%		--	--	±0.25		
Load Regulation	10%-100% load	3.3VDC output	--	--	±3		
		Other output	--	--	±2		
Ripple & Noise*	20MHz bandwidth	5V input	Other output	--	30	75	mVp-p
			24VDC output	--	50	100	
		Other input	Other output	--	30	100	
			15VDC output	--	80	150	
Temperature Coefficient	100% load		--	±0.02	--	%/°C	
Short-circuit Protection			Continuous, self-recovery				

Note: \* The "parallel cable" method is used for Ripple and Noise test, please refer to DC-DC Converter Application Notes for specific information.

### General Specifications

Item	Operating Conditions		Min.	Typ.	Max.	Unit	
Isolation	Input-output electric strength test for 1 minute with a leakage current of 1mA max.		3000	--	--	VDC	
Insulation Resistance	Input-output resistance at 500VDC		1000	--	--	MΩ	
Isolation Capacitance	Input-output capacitance at 100kHz/0.1V		--	20	--	pF	
Operating Temperature	Derating when operating temperature ≥ 71°C (see Fig.1)		-40	--	85	°C	
Storage Temperature			-55	--	125		
Case Temperature Rise	Ta=25°C	5V input	3.3VDC output	--	30		--
			Other output	--	25	--	
		Other input	--	25	--		
Pin Soldering Resistance Temperature	Soldering spot is 1.5mm away from case for 10 seconds		--	--	300		
Storage Humidity	Non-condensing	5V input	--	--	95	%RH	
		Other input	5	--	95		
Vibration	12/15/24VDC input		10-150Hz, 5G, 0.75mm. along X, Y and Z				
Switching Frequency	100% load, nominal input voltage		5V input	--	270	--	kHz
			Other input	--	260	--	
MTBF	MIL-HDBK-217F@25°C		3500	--	--	k hours	

### Mechanical Specifications

Case Material	Black plastic; flame-retardant and heat-resistant (UL94V-0)
Dimensions	19.65 x 6.00 x 10.16mm
Weight	2.1g(Typ.)
Cooling Method	Free air convection

### Electromagnetic Compatibility (EMC)

Emissions	CE	CISPR32/EN55032 CLASS B
	RE	CISPR32/EN55032 CLASS B
Immunity	ESD	IEC/EN61000-4-2 Air ±8kV, Contact ±6kV perf. Criteria B

Note: Refer to Fig. 3 for recommended circuit test.

Typical Characteristic Curves

Temperature Derating Curve






Fig. 1


Efficiency Vs Input Voltage (Full Load)




Efficiency Vs Output Load (Vin=5V)



Efficiency Vs Input Voltage (Full Load)



Efficiency Vs Output Load (Vin=24V)



Design Reference

1. Typical application circuit

Input and/or output ripple can be further reduced, by connecting a filter capacitor from the input and/or output terminals to ground as shown in Fig. 2.

Choosing suitable filter capacitor values is very important for a smooth operation of the modules, particularly to avoid start-up problems caused by capacitor values that are too high. For recommended input and output capacitor values refer to Table 1.



Fig. 2

Table 1: Recommended input and output capacitor values

Vin	Cin	Vo	Cout
5VDC	4.7µF/16V	3.3VDC	10µF/16V
12VDC	2.2µF/25V	5VDC	10µF/16V
15VDC	2.2µF/25V	9VDC	2.2µF/16V
24VDC	1µF/50V	12VDC	2.2µF/25V
--	--	15VDC	1µF/25V

2. EMC compliance circuit






Fig. 3

Table 2: Recommended EMC filter values


Input voltage	5V input	Other input	
Output voltage	3.3/5/9VDC	12/15/24VDC	
EMI	C1/C2	4.7µF /25V	4.7µF /50V
	CY	100pF /4kV	1000pF /4kV
	C3	Refer to the Cout in table 1	
	LDM	6.8µH	

3. For additional information please refer to DC-DC converter application notes on [www.mornsun-power.com](http://www.mornsun-power.com).

Dimensions and Recommended Layout



Note: Grid 2.54\*2.54mm



Note:  
Unit: mm[inch]  
Pin section tolerances: ± 0.10[± 0.004]  
General tolerances: ± 0.25[± 0.010]

Pin-Out	
Pin	Mark
1	Vin
2	GND
4	0V
6	+Vo

Note:

1. For additional information on Product Packaging please refer to [www.mornsun-power.com](http://www.mornsun-power.com). Packaging bag number: 58200001;
2. If the product is not operated within the required load range, the product performance cannot be guaranteed to comply with all parameters in the datasheet;
3. The maximum capacitive load offered were tested at input voltage range and full load;
4. Unless otherwise specified, parameters in this datasheet were measured under the conditions of  $T_a=25^{\circ}\text{C}$ , humidity<75%RH with nominal input voltage and rated output load;
5. All index testing methods in this datasheet are based on our company corporate standards;
6. We can provide product customization service, please contact our technicians directly for specific information;
7. Products are related to laws and regulations: see "Features" and "EMC";
8. Our products shall be classified according to ISO14001 and related environmental laws and regulations, and shall be handled by qualified units.

Mornsun Guangzhou Science & Technology Co., Ltd.

Address: No. 8 Nanyun 4th Road, Huangpu District, Guangzhou, China  
Tel: 86-20-38601850

Fax: 86-20-38601272

E-mail: [info@mornsun.cn](mailto:info@mornsun.cn)

[www.mornsun-power.com](http://www.mornsun-power.com)