



RXK Series

Features


- 105°C, 2,000 ~ 5,000 hours assured
- Low ESR, suitable for switching power supplies
- Smaller size with large permissible ripple current
- RoHS compliant



Specifications

Items	Performance																																										
Category Temperature Range	-55℃ ~ +105℃																																										
Capacitance Tolerance	± 20% (at 120 Hz, 20℃)																																										
Leakage Current (at 20℃)	I = 0.01CV or 3 (μA) whichever is greater (after 2 minutes) Where, C = rated capacitance in μF, V = rated DC working voltage in V																																										
Tanδ (at 120 Hz, 20℃)	<table><tr><td>Rated Voltage</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td><td>63</td></tr><tr><td>Tanδ (max.)</td><td>0.22</td><td>0.19</td><td>0.16</td><td>0.14</td><td>0.12</td><td>0.10</td><td>0.09</td></tr></table> When the capacitance exceeds 1,000μF, 0.02 shall be added every 1,000μF increase.								Rated Voltage	6.3	10	16	25	35	50	63	Tanδ (max.)	0.22	0.19	0.16	0.14	0.12	0.10	0.09																			
Rated Voltage	6.3	10	16	25	35	50	63																																				
Tanδ (max.)	0.22	0.19	0.16	0.14	0.12	0.10	0.09																																				
Low Temperature Characteristics (at 120 Hz)	Impedance ratio shall not exceed the values given in the table below. <table><tr><td>Rated Voltage</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td><td>63</td></tr><tr><td>Impedance Ratio</td><td>Z(-55℃) / Z(+20℃)</td><td>4</td><td>4</td><td>3</td><td>3</td><td>3</td><td>3</td></tr></table>								Rated Voltage	6.3	10	16	25	35	50	63	Impedance Ratio	Z(-55℃) / Z(+20℃)	4	4	3	3	3	3																			
Rated Voltage	6.3	10	16	25	35	50	63																																				
Impedance Ratio	Z(-55℃) / Z(+20℃)	4	4	3	3	3	3																																				
Endurance	<table><tr><td>Test Time</td><td>2,000 Hrs for ϕ D ≤ 6.3 mm; 3,000 Hrs for ϕ D = 8 mm; 4,000 Hrs for ϕ D = 10 mm; 5,000 Hrs for ϕ D ≥ 12.5 mm</td></tr><tr><td>Capacitance Change</td><td>Within ± 20% of initial value</td></tr><tr><td>Tanδ</td><td>Less than 200% of specified value</td></tr><tr><td>Leakage Current</td><td>Within specified value</td></tr></table> * The above specifications shall be satisfied when the capacitors are restored to 20℃ after the rated voltage applied with rated ripple current for 2,000 ~ 5,000 hours at 105℃.								Test Time	2,000 Hrs for ϕ D ≤ 6.3 mm; 3,000 Hrs for ϕ D = 8 mm; 4,000 Hrs for ϕ D = 10 mm; 5,000 Hrs for ϕ D ≥ 12.5 mm	Capacitance Change	Within ± 20% of initial value	Tanδ	Less than 200% of specified value	Leakage Current	Within specified value																											
Test Time	2,000 Hrs for ϕ D ≤ 6.3 mm; 3,000 Hrs for ϕ D = 8 mm; 4,000 Hrs for ϕ D = 10 mm; 5,000 Hrs for ϕ D ≥ 12.5 mm																																										
Capacitance Change	Within ± 20% of initial value																																										
Tanδ	Less than 200% of specified value																																										
Leakage Current	Within specified value																																										
Shelf Life Test	<table><tr><td>Test Time</td><td>1,000 Hrs</td></tr><tr><td>Capacitance Change</td><td>Within ± 20% of initial value</td></tr><tr><td>Tanδ</td><td>Less than 200% of specified value</td></tr><tr><td>Leakage Current</td><td>Within specified value</td></tr></table> * The above specifications shall be satisfied when the capacitors are restored to 20℃ after exposing them for 1,000 hours at 105℃ without voltage applied.								Test Time	1,000 Hrs	Capacitance Change	Within ± 20% of initial value	Tanδ	Less than 200% of specified value	Leakage Current	Within specified value																											
Test Time	1,000 Hrs																																										
Capacitance Change	Within ± 20% of initial value																																										
Tanδ	Less than 200% of specified value																																										
Leakage Current	Within specified value																																										
Ripple Current and Frequency Multipliers	<table><tr><th>Cap.(μF) \ Freq.(Hz)</th><th>60 (50)</th><th>120</th><th>500</th><th>1k</th><th>10k</th><th>100k</th></tr><tr><td>≤ 33</td><td>0.40</td><td>0.55</td><td>0.65</td><td>0.80</td><td>0.90</td><td>1.00</td></tr><tr><td>39 ~ 330</td><td>0.60</td><td>0.70</td><td>0.80</td><td>0.90</td><td>0.95</td><td>1.00</td></tr><tr><td>390 ~ 1,000</td><td>0.65</td><td>0.80</td><td>0.85</td><td>0.98</td><td>1.00</td><td>1.00</td></tr><tr><td>1,200 ≤</td><td>0.80</td><td>0.90</td><td>0.95</td><td>0.98</td><td>1.00</td><td>1.00</td></tr></table>								Cap.(μF) \ Freq.(Hz)	60 (50)	120	500	1k	10k	100k	≤ 33	0.40	0.55	0.65	0.80	0.90	1.00	39 ~ 330	0.60	0.70	0.80	0.90	0.95	1.00	390 ~ 1,000	0.65	0.80	0.85	0.98	1.00	1.00	1,200 ≤	0.80	0.90	0.95	0.98	1.00	1.00
Cap.(μF) \ Freq.(Hz)	60 (50)	120	500	1k	10k	100k																																					
≤ 33	0.40	0.55	0.65	0.80	0.90	1.00																																					
39 ~ 330	0.60	0.70	0.80	0.90	0.95	1.00																																					
390 ~ 1,000	0.65	0.80	0.85	0.98	1.00	1.00																																					
1,200 ≤	0.80	0.90	0.95	0.98	1.00	1.00																																					

Diagram of Dimensions




Lead Spacing and Diameter

Unit: mm

ϕD	5	6.3	8	10	12.5	16	18
P	2.0	2.5	3.5	5.0	5.0	7.5	7.5
ϕd	0.5		0.6			0.8	
α	L<20: 1.5, L $\geq$ 20: 2.0						
β	0.5						

The case size of 16×20 is suitable for below diagram:





Dimension: $\phi D \times L(\text{mm})$
 Impedance: $\Omega/$ at 100k Hz
 Ripple Current: mA/rms at 105°C

Dimension and Permissible Ripple Current

Rated Volt. (Vdc) Contents Cap. (μF)	6.3V (0J)					10V (1A)					16V (1C)				
	$\phi D \times L$	Impedance (Ω , max./100k Hz)		Ripple Current (mA/rms, 105°C)		$\phi D \times L$	Impedance (Ω , max./100k Hz)		Ripple Current (mA/rms, 105°C)		$\phi D \times L$	Impedance (Ω , max./100k Hz)		Ripple Current (mA/rms, 105°C)	
		20°C	-10°C	120 Hz	100k Hz		20°C	-10°C	120 Hz	100k Hz		20°C	-10°C	120 Hz	100k Hz
56											5×11	0.72	1.8	116	165
68											5×11	0.72	1.8	126	180
82						5×11	0.72	1.8	116	165					
100						5×11	0.72	1.8	126	180					
120	5×11	0.72	1.8	116	165						6.3×11	0.38	0.95	179	255
180						6.3×11	0.38	0.95	179	255	6.3×15	0.27	0.68	231	330
220	6.3×11	0.38	0.95	179	255	6.3×11	0.38	0.95	196	280					
270	6.3×11	0.38	0.95	196	280	6.3×15	0.27	0.68	231	330	8×11.5	0.20	0.50	291	415
330	6.3×15	0.27	0.68	231	330	8×11.5	0.20	0.50	291	415	10×12.5	0.12	0.30	438	625
											8×11.5	0.20	0.50	315	450
											8×15	0.16	0.40	347	495
390	8×11.5	0.20	0.50	332	415	10×12.5	0.12	0.30	500	625	10×12.5	0.12	0.30	540	675
470	8×11.5 10×12.5	0.20 0.12	0.50 0.30	360 500	450 625	8×15 10×12.5	0.16 0.12	0.40 0.30	396 540	495 675	8×15	0.16	0.40	472	590
											8×20	0.11	0.28	512	640
											10×16	0.084	0.21	660	825
560	8×15 10×12.5	0.16 0.12	0.40 0.30	396 540	495 675	8×15	0.16	0.40	472	590	8×20	0.11	0.28	560	700
											10×16	0.084	0.21	728	910
680	10×16	0.084	0.21	660	825	8×20	0.11	0.28	512	640	10×20	0.062	0.16	832	1,040
820	8×15 8×20 10×16	0.16 0.11 0.084	0.40 0.28 0.21	472 512 728	590 640 910	8×20 10×16	0.11 0.084	0.28 0.21	560 728	700 910	10×20	0.062	0.16	904	1,130
											10×25	0.052	0.13	1,008	1,260
1,000	8×20	0.11	0.28	560	700	10×20	0.062	0.16	832	1,040	10×25	0.052	0.13	1,112	1,390
1,200	10×20	0.062	0.16	936	1,040	10×20	0.062	0.16	1,017	1,130	10×30	0.044	0.11	1,296	1,440
						10×25	0.052	0.13	1,134	1,260	12.5×20	0.046	0.12	1,206	1,340
1,500	10×20 10×25	0.062 0.052	0.16 0.13	1,017 1,134	1,130 1,260	10×25	0.052	0.13	1,251	1,390	10×30	0.044	0.11	1,413	1,570
						10×30	0.044	0.11	1,296	1,440	12.5×20	0.046	0.12	1,305	1,450
											12.5×25	0.034	0.085	1,521	1,690
1,800	10×25	0.052	0.13	1,251	1,390	10×30	0.044	0.11	1,413	1,570	12.5×25	0.034	0.085	1,629	1,810
						12.5×20	0.046	0.12	1,206	1,340					
2,200	10×30 12.5×20	0.044 0.046	0.11 0.12	1,296 1,206	1,440 1,340	12.5×20	0.046	0.12	1,305	1,450	12.5×30	0.030	0.075	1,755	1,950
						12.5×25	0.034	0.085	1,521	1,690	16×20	0.035	0.087	1,485	1,650
2,700	10×30 12.5×20 12.5×25	0.044 0.046 0.034	0.11 0.12 0.085	1,413 1,305 1,521	1,570 1,450 1,690	12.5×25	0.034	0.085	1,629	1,810	12.5×30	0.030	0.075	1,917	2,130
						12.5×30	0.030	0.075	1,755	1,950	12.5×35	0.027	0.068	1,980	2,200
											16×25	0.028	0.070	1,863	2,070
3,300	12.5×25	0.034	0.085	1,629	1,810	12.5×30	0.030	0.075	1,917	2,130	12.5×35	0.027	0.068	2,151	2,390
						12.5×35	0.027	0.068	1,980	2,200	12.5×40	0.024	0.060	2,196	2,440
											16×25	0.028	0.070	2,025	2,250
3,900	12.5×30	0.030	0.075	1,755	1,950	12.5×35	0.027	0.068	2,196	2,390	16×31.5	0.025	0.063	2,115	2,350
						12.5×40	0.024	0.060	2,151	2,440					
						16×20	0.035	0.087	1,692	1,880					
4,700	12.5×30 12.5×35 16×20	0.030 0.027 0.035	0.075 0.068 0.087	1,917 1,980 1,440	2,130 2,200 1,600	16×25	0.028	0.070	1,863	2,070	16×31.5	0.025	0.055	2,295	2,550
											16×35.5	0.022	0.055	2,295	2,550
5,600	12.5×35 12.5×40 16×25	0.027 0.024 0.028	0.068 0.060 0.070	2,151 2,196 1,863	2,390 2,440 2,070	16×31.5	0.025	0.063	2,115	2,350	16×35.5	0.022	0.055	2,394	2,660
											16×40	0.018	0.045	2,610	2,900
6,800	12.5×40 16×25 16×31.5	0.024 0.028 0.025	0.060 0.070 0.063	2,358 2,025 2,115	2,620 2,250 2,350	16×31.5	0.025	0.063	2,295	2,550	16×40	0.018	0.045	2,844	3,160
						16×35.5	0.022	0.055	2,295	2,550	18×35.5	0.021	0.053	2,448	2,720
8,200	16×31.5	0.025	0.063	2,295	2,550	16×35.5	0.022	0.055	2,448	2,720	18×35.5	0.021	0.053	2,601	2,890
10,000	16×35.5	0.022	0.055	2,691	2,990										



Dimension: $\phi D \times L(\text{mm})$
 Impedance: $\Omega/$ at 100k Hz
 Ripple Current: mA/rms at 105°C

Dimension and Permissible Ripple Current

Rated Volt. (V _{DC}) Contents Cap. (μF)	25V (1E)					35V (1V)					50V (1H)				
	$\phi D \times L$	Impedance (Ω , max./100k Hz)		Ripple Current (mA/rms, 105°C)		$\phi D \times L$	Impedance (Ω , max./100k Hz)		Ripple Current (mA/rms, 105°C)		$\phi D \times L$	Impedance (Ω , max./100k Hz)		Ripple Current (mA/rms, 105°C)	
		20°C	-10°C	120 Hz	100k Hz		20°C	-10°C	120 Hz	100k Hz		20°C	-10°C	120 Hz	100k Hz
18											5×11	1.1	3.3	72	130
22											5×11	1.1	3.3	83	150
27						5×11	0.72	1.8	91	165					
33						5×11	0.72	1.8	99	180					
39	5×11	0.72	1.8	116	165						6.3×11	0.56	1.6	154	220
47	5×11	0.72	1.8	126	180						6.3×11	0.56	1.6	161	230
56						6.3×11	0.38	0.95	179	255	6.3×15	0.41	1.2	217	310
68						6.3×11	0.38	0.95	196	280	8×11.5	0.29	0.84	238	340
82	6.3×11	0.38	0.95	179	255	6.3×15	0.27	0.68	231	330	8×11.5 8×15 10×12.5	0.29 0.25 0.16	0.84 0.75 0.40	249 329 336	355 470 480
100	6.3×11	0.38	0.95	196	280						10×12.5	0.16	0.40	371	530
120	6.3×15	0.27	0.68	231	330	8×11.5 10×12.5	0.20 0.12	0.50 0.30	291 438	415 625	8×15 8×20 10×16	0.25 0.18 0.12	0.75 0.52 0.30	392 427 529	560 610 755
150	8×11.5	0.20	0.50	291	415	8×11.5 10×12.5	0.20 0.12	0.50 0.30	315 473	450 675	10×16	0.12	0.30	588	840
180	8×11.5 10×12.5	0.20 0.12	0.50 0.30	315 438	450 625	8×15	0.16	0.40	347	495	8×20 10×20	0.18 0.088	0.52 0.22	525 662	750 945
220	8×15 10×12.5	0.16 0.12	0.40 0.30	347 473	495 675	8×15 8×20 10×16	0.16 0.11 0.084	0.40 0.28 0.21	413 448 578	590 640 825	10×20 10×25	0.088 0.068	0.22 0.17	728 805	1,040 1,150
270						8×20 10×16	0.11 0.084	0.28 0.21	490 637	700 910	10×25	0.068	0.17	896	1,280
330	8×15 8×20 10×16	0.16 0.11 0.084	0.40 0.28 0.21	413 448 578	590 640 825	10×20	0.062	0.16	728	1,040	10×30 12.5×20	0.059 0.059	0.15 0.15	882 833	1,260 1,190
390	8×20 10×16	0.11 0.084	0.28 0.21	560 728	700 910	10×20 10×25	0.062 0.052	0.16 0.13	904 1,008	1,130 1,260	12.5×20	0.059	0.15	952	1,190
470	10×20	0.062	0.16	832	1,040	10×25	0.052	0.13	1,112	1,390	10×30 12.5×25	0.059 0.045	0.15 0.11	1,176 1,192	1,470 1,490
560	10×20 10×25	0.062 0.052	0.16 0.13	904 1,008	1,130 1,260	10×30 12.5×20	0.044 0.046	0.11 0.12	1,152 1,072	1,440 1,340	12.5×25 12.5×30	0.045 0.039	0.11 0.098	1,304 1,376	1,630 1,720
680	10×25	0.052	0.13	1,112	1,390	10×30 12.5×20 12.5×25	0.044 0.046 0.034	0.11 0.12 0.085	1,256 1,160 1,352	1,570 1,450 1,690	12.5×30 12.5×35 16×20	0.039 0.033 0.048	0.098 0.083 0.120	1,520 1,512 1,248	1,800 1,900 1,560
820	10×30 12.5×20	0.044 0.046	0.11 0.12	1,152 1,072	1,440 1,340	12.5×25	0.034	0.085	1,448	1,810	12.5×35 12.5×40 16×25	0.033 0.029 0.033	0.083 0.073 0.083	1,624 1,656 1,504	2,030 2,070 1,880
1,000	10×30 12.5×20 12.5×25	0.044 0.046 0.034	0.11 0.12 0.085	1,256 1,160 1,352	1,570 1,450 1,690	12.5×30 16×20	0.030 0.035	0.075 0.087	1,560 1,376	1,950 1,720	12.5×40 16×25 16×31.5	0.029 0.033 0.029	0.073 0.083 0.073	1,800 1,664 1,720	2,250 2,080 2,150
1,200	12.5×25	0.034	0.085	1,629	1,810	12.5×30 12.5×35 16×25	0.030 0.027 0.028	0.075 0.068 0.070	1,917 1,980 1,863	2,130 2,200 2,070	16×31.5 16×35.5	0.029 0.025	0.073 0.063	2,088 2,115	2,320 2,350
1,500	12.5×30 16×20	0.030 0.035	0.075 0.087	1,755 1,539	1,950 1,710	12.5×35 12.5×40 16×25	0.027 0.024 0.028	0.068 0.060 0.070	2,151 2,196 2,025	2,390 2,440 2,250	16×35.5 16×40	0.025 0.021	0.063 0.063	2,160 2,336	2,400 2,595
1,800	12.5×30 12.5×35 16×25	0.030 0.027 0.028	0.075 0.068 0.070	1,917 1,980 1,863	2,130 2,200 2,070	12.5×40 16×31.5	0.024 0.025	0.060 0.063	2,358 2,115	2,620 2,350	16×40 18×35.5	0.021 0.023	0.063 0.058	2,466 2,286	2,740 2,540
2,200	12.5×35 12.5×40 16×25	0.027 0.024 0.028	0.068 0.060 0.070	2,151 2,196 2,025	2,390 2,440 2,250	16×31.5 16×35.5	0.025 0.022	0.063 0.055	2,295 2,295	2,550 2,550	18×35.5 18×40	0.023 0.020	0.058 0.050	2,349 2,385	2,610 2,650
2,700	16×31.5	0.025	0.063	2,115	2,350	16×35.5 16×40 18×35.5	0.022 0.018 0.021	0.055 0.045 0.053	2,394 2,610 2,448	2,660 2,900 2,720					
3,300	16×31.5 16×35.5	0.025 0.022	0.063 0.055	2,295 2,295	2,550 2,550	18×35.5 18×40	0.021 0.017	0.053 0.043	2,601 2,709	2,890 3,010					
3,900	16×35.5 16×40 18×35.5	0.022 0.018 0.021	0.055 0.045 0.053	2,394 2,610 2,448	2,660 2,900 2,720	18×40	0.017	0.043	2,934	3,260					
4,700	18×35.5 18×40	0.021 0.017	0.053 0.043	2,601 2,709	2,890 3,010										
5,600	18×40	0.017	0.043	2,934	3,260										



Dimension: $\phi D \times L(\text{mm})$
 Impedance: Ω / at 100k Hz
 Ripple Current: mA/rms at 105°C

Dimension and Permissible Ripple Current

Cap. (μF)	Contents	63V(1J)				
		$\phi D \times L$	Impedance (Ω , max./100k Hz)		Ripple Current (mA/rms, 105°C)	
			20°C	-10°C	120 Hz	100k Hz
12		5×11	1.90	4.78	55	100
27		6.3×11	1.10	2.78	88	160
33		6.3×11	1.10	2.75	96	175
39		6.3×15	0.62	1.55	161	230
47		8×11.5	0.49	1.23	193	275
56		8×11.5	0.49	1.23	203	290
		10×12.5	0.27	0.675	294	420
68		8×15	0.34	0.850	252	360
		10×12.5	0.27	0.675	354	505
		10×16	0.21	0.525	366	523
82		8×20	0.21	0.525	350	500
100		8×15	0.34	0.850	308	440
120		10×16	0.210	0.525	455	650
		10×20	0.160	0.400	490	700
150		8×20	0.210	0.525	476	680
		10×25	0.130	0.325	546	780
180		10×20	0.160	0.400	553	790
		10×30	0.100	0.250	672	960
220		10×25	0.130	0.325	648	925
		12.5×20	0.110	0.275	609	870
270		10×30	0.100	0.250	812	1,160
		12.5×25	0.074	0.185	805	1,150
330		12.5×20	0.110	0.275	746	1,065
390		12.5×25	0.074	0.185	1,088	1,280
		12.5×30	0.068	0.170	1,024	1,360
470		12.5×30	0.068	0.170	1,120	1,360
		12.5×35	0.063	0.158	1,112	1,400
		16×20	0.059	0.148	1,080	1,350
		16×25	0.055	0.138	1,184	1,480
560		12.5×40	0.051	0.128	1,224	1,530
		16×25	0.055	0.138	1,296	1,620
680		12.5×40	0.051	0.128	1,336	1,670
		16×31.5	0.046	0.115	1,376	1,720
820		12.5×40	0.051	0.128	1,480	1,850
		16×31.5	0.046	0.115	1,512	1,890
		16×35.5	0.040	0.100	1,528	1,910
1,000		16×35.5	0.040	0.100	1,576	1,970
		18×35.5	0.040	0.100	1,688	2,110
1,500		18×35.5	0.040	0.100	2,169	2,410

Part Numbering System

RXK Series	470μF	± 20%	6.3V	Bulk Package	Gas Type	8 ϕ × 11.5L	General Purpose
RXK	471	M	0J	BK	-	0811	
Series Name	Capacitance	Capacitance Tolerance	Rated Voltage	Lead Configuration and Package	Rubber Type	Case Size	Application

Note: For more details, please refer to "Part Numbering System - Radial Type" on page 139.