







RoHS



SECTION A-A



适用线路板 (PCB LAYOUT)

Model No.	Pin	A	B	C
WAFER-PH2.0-2PWZ-W	2	2.00	6.00	5.00
WAFER-PH2.0-3PWZ-W	3	4.00	8.00	7.00
WAFER-PH2.0-4PWZ-W	4	6.00	10.00	9.00
WAFER-PH2.0-5PWZ-W	5	8.00	12.00	11.00
WAFER-PH2.0-6PWZ-W	6	10.00	14.00	13.00
WAFER-PH2.0-7PWZ-W	7	12.00	16.00	15.00
WAFER-PH2.0-8PWZ-W	8	14.00	18.00	17.00
WAFER-PH2.0-9PWZ-W	9	16.00	20.00	19.00
WAFER-PH2.0-10PWZ-W	10	18.00	22.00	21.00
WAFER-PH2.0-11PWZ-W	11	20.00	24.00	23.00
WAFER-PH2.0-12PWZ-W	12	22.00	26.00	25.00
WAFER-PH2.0-13PWZ-W	13	24.00	28.00	27.00
WAFER-PH2.0-14PWZ-W	14	26.00	30.00	29.00
WAFER-PH2.0-15PWZ-W	15	28.00	32.00	31.00
WAFER-PH2.0-16PWZ-W	16	30.00	34.00	33.00
WAFER-PH2.0-17PWZ-W	17	32.00	36.00	35.00
WAFER-PH2.0-18PWZ-W	18	34.00	38.00	37.00
WAFER-PH2.0-19PWZ-W	19	36.00	40.00	39.00
WAFER-PH2.0-20PWZ-W	20	38.00	42.00	41.00

Specifications/技术规格:

- 1.Poles/线数: 2~20P
- 2.Wire range/适用线规: AGW 30#~24#
- 3.Applicable PC board thickness/适用PC板厚度: 0.8~1.6mm
- 4.Current rating/额定电流: 2.0A
- 5.Voltage rating/额定电压: 100V DC/AC
- 6.Insulation Resistance/绝缘电阻: 1000MΩ Min
- 7.Dielectric Withstanding/ 耐电压: 800V AC/minute
- 8.Contact Resistance/ 接触电阻: 20mΩ Max
- 9.Operating Temperature/ 工作温度: -25℃ to +85℃

⑧	Terminal			Brass	Plating Sn
⑨	Housing		1	PA66	White
NO.	Name	Number	Qty	Materil	Remarks

YUANDI® Yuandi Electronics Co.,Ltd
元迪

design	date	name	WAVER CONNECTOR
Review	date	model	WAFER-PH2.0-□□PWZ-W
Approved	date		

Drawing number:	Proportion	1:1	unit	mm	gaps	number	A4
-----------------	------------	-----	------	----	------	--------	----