




REV	ECN NO.	DESCRIPTION	DATE	APP'D
A/0		RELEASE TO PRODUCTION	05/21/20'	Xuanwen Ye





2 Pin

3 Pin


LOCK CONFIGURATION





PCB LAYOUT




WITHOUT COVER



WITH COVER



SECTION A-A



Poles	DIM(mm)			
	A	B	C	D
2	1.25	3.25	7.25	7.25
3	2.50	4.50	8.50	8.50
4	3.75	5.75	9.75	9.75
5	5.00	7.00	11.00	11.00
6	6.25	8.25	12.25	12.25
7	7.50	9.50	13.50	13.50
8	8.75	10.75	14.75	14.75
9	10.00	12.00	16.00	16.00
10	11.25	13.25	17.25	17.25
11	12.50	14.50	18.50	18.50
12	13.75	15.75	19.75	19.75
13	15.00	17.00	21.00	21.00
14	16.25	18.25	22.25	22.25
15	17.50	19.50	23.50	23.50
16	18.75	20.75	24.75	24.75
17	20.00	22.00	26.00	26.00
18	21.25	23.25	27.25	27.25
19	22.50	24.50	28.50	28.50
20	23.75	25.75	29.75	29.75

NOTES:

- Material:
Insulation: LCP, UL94V-0 (Beige)
Pin: Phosphor bronze/Tin-Plated
Tab: Brass/Tin-Plated
- Current Rating: 1A AC, DC
- Voltage Rating: 125V AC, DC
- Temperature Range: -25°C ~ +85°C
- Contact Resistance: 20mΩ Max
- Insulation Resistance: 100MΩ Min
- Withstanding Voltage: 500V AC/minute
- Ordering Code: A1250VS-x

TOLERANCE		APPROVALS		DATE	深圳市金航标电子有限公司			www.kinghelm.com.cn		
		DRAWN <i>Zhang Xiao Tao</i>		05/21/20'	KH-A1251LF-10A			0755-28190160		
		CHK'D <i>Art Shi</i>		05/21/20'	PART NO. A1250VS-x		TITLE: WIRE TO BOARD, PLUG, PITCH 1.25mm, CRIMP TYPE, ASSEMBLY			
		APP'D <i>Art Shi</i>		05/21/20'	DRAWING NO. EN-A1250VS-x					
		UNITS mm	SCALE 1:1	SIZE: A4		SHEET 1 OF 1				
UNLESS OTHERWISE SPECIFIED										
X.	±0.30									
X.X	±0.25									
X.XX	±0.20									
Angle	±3°									