








A | B | C | D | E



REV.		ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN	CHECKED	APPROVED
A	N/A			INITIAL RELEASE				



RECOMMENDED PCB LAYOUT

NOTES:

1. CONTACT CURRENT RATING: 12V DC, 1A.
2. CONTACT RESISTANCE: 50mΩ MAX.;
3. INSULATION RESISTANCE: 100MΩ MIN., 250V DC/1min;
4. DIELECTRIC WITHSTANDING: 500V AC MIN.;
5. DURABILITY: 5,000 CYCLES MIN.;
6. CONNECTOR INSERTION FORCES: 0.3kgf–3kgf;
7. CONNECTOR EXTRACTION FORCES: 0.3kgf–3kgf;
8. OPERATING TEMPERATURE RANGE: -20 to +80°C;

⑦	HOUSING	1	PA9T,UL94V-0	Black
⑥	CONTACT F	1	C5191-EH T=0.20mm	
⑤	CONTACT E	1	C5191-EH T=0.20mm	
④	CONTACT D	1	C5191-EH T=0.20mm	
③	CONTACT C	1	C5191-EH T=0.20mm	
②	CONTACT B	1	C5191-EH T=0.20mm	
①	CONTACT A	1	C5191-EH T=0.20mm	
ITEM	PART NAME	Q'TY	MATERIAL	DESCRIPTION
				REMARK

MEASURE POINT:
QUADRANT POINT
TANGENCY POINT
INTERSECTION POINT

UNLESS OTHERWISE
SPECIFIED, TOLERANCE:
X. ±5°
X.x ±0.30
X.xx ±0.20
X...xx ±0.10
ANGULAR ±



深圳市韩下电子有限公司

DESIGN	黄彬	DATE	2020/10/20	TITLE:				
CHECKED	张伟	DATE	2020/10/20	PHONE JACK				
APPROVED	罗小春	DATE	2020/10/20					
PART NO.	HX PJ-342C		REV.:	A	SCALE:	1:1		
DRAWING NO.			UNIT:	mm	SIZE:	A4		
			SHEET:	1/1				

A | B | C | D | E