



Sensors > Position Sensors > Potentiometer Sensors > Cable Actuated Position Sensors > Dual Output String Pot



Position Sensor Product Type: **SP Series, String Pots**

Full Stroke Range: **101.6 – 1270 mm [ 4 – 50 in ]**

Output Signal Type: **0 – 10 VDC, 4 – 20 mA**

Accuracy: **±.25 % of FS**

Repeatability: **.02 % of FS**

[All Dual Output String Pot \(4\)](#)

Features

Product Type Features

Position Sensor Product Type	SP Series, String Pots
------------------------------	------------------------

Body Features

Case Material	Polycarbonate + Stainless Mounting Bracket
---------------	--

Dimensions

Full Stroke Range	101.6 – 1270 mm[4 – 50 in]
-------------------	----------------------------

Usage Conditions

Accuracy	±.25 % of FS
Operating Temperature Range	-40 – 70 °C[-40 – 158 °F]

Operation/Application

Output Signal Type	0 – 10 VDC, 4 – 20 mA
--------------------	-----------------------

Industry Standards

IP Rating	IP67
Hazardous Area Approval	None

Other

Repeatability	.02 % of FS
---------------	-------------



Encoder Drive	No
Measuring Cable	Nylon-Coated Stainless Steel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2023 (233) SVHC > Threshold: Pb (1.2% in Component a) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-CAPS0070  
Dual Output String Pot

TE Part # 9036810-0040  
CONN,PLUG,STRGHT,4COND,5M, SC4

Also in the Series | MEAS SP



Cable Actuated Position Sensors(22)

Customers Also Bought



TE Part #AEA577N00000201000  
623 RECEPTACLE, SPEEDTEC-READY



TE Part #1-2176614-4  
EP 10W (SS) 3R6 5% BULK BOX




TE Part #2418143-1  
FSA Sheet 300mm sq x 1.6mm




TE Part #ZPF000000000207314  
732-8254-22 R-A1533




TE Part #CAT-CAPS0074  
IP67 String Pots, 4-20Ma Output, SR1M




TE Part #04-0981-5052  
PT8420-0040-941-1121



TE Part #20004503-00  
PT9420-0150-424-1160: CTO-11500000-01



TE Part #1-2427762-1  
Strada Cable Assy, 100 ohm, Space-Rated



TE Part #20009252-00  
PT8420-0040-941-1521: CTO-11500000-03

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_SPD-25-3\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_SPD-25-3\_A.3d\_igs.zip



English

Customer View Model

[ENG\\_CVM\\_CVM\\_SPD-25-3\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SPD](#)

English