









REV.	ECN	DESCRIPTION	MDF'D	DATE
	—	新订图面		



备注 (NOTE) :

1. 材质:

1. 1 胶芯: LCP UL94 V-0
1. 2 端子: C2680, T=0.2mm; 镍底, 镀金
1. 3 外壳: 不锈钢201-H 表面镀镍
2. 电气特性:

2. 1. 接触区: 接触电阻40mΩ Max, 允许10mΩ变化量. 测试条件: 20mv, 100mA下测量.

2. 2. 接触电流: 3A VBUS引脚; 1. 25A用于GND引脚; 其他引脚为0.25A.

2. 3. 额定电压: 5V.

2. 4. 耐电电压: 100VAC.

2. 5. 绝缘电阻: 至少100兆欧 .3

. 机械性能:

3. 1. 插入力: 0.5-2.0Kg

3. 2. 拔出力: 0.6-2.04Kg

3. 3. 插拔次数: 5000次.

4. 工作环境: -30°C to +80°C.

USB TYPE C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
	B12	GND	
	B9	VBUS	
A5	CC1		
	B5	CC2	
A9	VBUS		
A12	GND		

TABLE:

NO	PART	Q'TY	Material
1	SHELL	1	ZINC ALLOY, NI30u"Min PLATED
2	CONTACT	6	C2680, TIN80u"/Au1u"/NI30u" PLATED
3	1MD HOUSING	1	LCP UL94 V-0 BLACK
4	CAP	1	LCP UL94 V-0 BLACK
5	WATERPROOF RING	1	SILICONE UL94 V-0 BLACK



® 深圳市韩下电子有限公司

品名 (ITEM NO) HX TYPE-C 6P LT H7.8

料号 (PART NO)

图号 (DWG NO) A1

页码 (SHEET)	1	单位 (UNIT) : MM
版本 (REV)	A1	比例 (SCALE) 1:1
日期 (DATE)	2020.8.25	○
设计 (DESIGN)	董彬	未注公差 TOLERANCE UNSPECIFIED
审核 (CHECKED)	张伟	X. X 0.20 X. XX 0.15 X. XXX 0.10
核准 (APPROVED)	罗小春	X° ±5° X. X° ±2°