

# Product Specification

## XBLW CD4043

Quad R/S Latch With 3-state Outputs

WEB | [www.xinboleic.com](http://www.xinboleic.com)



## Description

The CD4043 is a quad R/S latch with 3-state outputs with a common output enable input (OE). Each latch has an active HIGH set input (1S to 4S), an active HIGH reset input (1R to 4R) and an active HIGH 3-state output (1Q to 4Q).


When OE is HIGH, the latch output (nQ) is determined by the nR and nS inputs as shown in function table.

When OE is LOW, the latch outputs are in the high impedance OFF-state. OE does not affect the state of the latch.

The high impedance off-state feature allows common bussing of the outputs.

It operates over a recommended  $V_{DD}$  power supply range of 3V to 15V referenced to  $V_{SS}$  (usually ground).

Unused inputs must be connected to  $V_{DD}$ ,  $V_{SS}$ , or another input.



## Feature

- 5V, 10V, and 15V parametric ratings
- Standardized symmetrical output characteristics
- Specified from -40°C to +85°C
- Packaging information: DIP16/SOP16/TSSOP16

## Ordering Information

| Product Model    | Package Type | Marking  | Packing | Packing Qty  |
|------------------|--------------|----------|---------|--------------|
| XBLW CD4043BE    | DIP-16       | CD4043BE | Tube    | 1000Pcs/Box  |
| XBLW CD4043BDTR  | SOP-16       | CD4043B  | Tape    | 2500Pcs/Reel |
| XBLW CD4043BTDTR | TSSOP-16     | CD4043B  | Tape    | 3000Pcs/Reel |

## Block Diagram And Pin Description

### Block Diagram




Figure 1. Functional diagram





Figure 2. Logic diagram for one latch

### Pin Configurations



### Pin Description

| Pin No. | Pin Name        | Description                   |
|---------|-----------------|-------------------------------|
| 1       | 4Q              | 3-state buffered latch output |
| 2       | 1Q              | 3-state buffered latch output |
| 3       | 1R              | reset input(active HIGH)      |
| 4       | 1S              | set input (active HIGH)       |
| 5       | OE              | common output enable input    |
| 6       | 2S              | set input(active HIGH)        |
| 7       | 2R              | reset input(active HIGH)      |
| 8       | V <sub>SS</sub> | ground supply voltage         |
| 9       | 2Q              | 3-state buffered latch output |
| 10      | 3Q              | 3-state buffered latch output |
| 11      | 3R              | reset input(active HIGH)      |
| 12      | 3S              | set input(active HIGH)        |
| 13      | NC              | not connected                 |
| 14      | 4S              | set input(active HIGH)        |
| 15      | 4R              | reset input(active HIGH)      |
| 16      | V <sub>DD</sub> | supply voltage                |

## Function Table

| Inputs |    |    | Output  |
|--------|----|----|---------|
| OE     | nS | nR | nQ      |
| L      | X  | X  | Z       |
| H      | L  | H  | L       |
| H      | H  | X  | H       |
| H      | L  | L  | latched |

Note: [ 1 ] H=HIGH voltage level; L=LOW voltage level; X=don't care; Z=high impedance state.

## Electrical Parameter

### Absolute Maximum Ratings

| Parameter               | Symbol    | Conditions                             | Min. | Max.           | Unit |
|-------------------------|-----------|----------------------------------------|------|----------------|------|
| supply voltage          | $V_{DD}$  |                                        | -0.5 | +18            | J    |
| input clamping current  | $I_{IK}$  | $V_I < -0.5V$ or $V_I > V_{DD} + 0.5V$ | -    | $\pm 10$       | mA   |
| input voltage           | $V_I$     |                                        | -0.5 | $V_{DD} + 0.5$ | V    |
| output clamping current | $I_{OK}$  | $V_O < -0.5V$ or $V_O > V_{DD} + 0.5V$ | -    | $\pm 10$       | mA   |
| output current          | $I_O$     | $V_O = 0V$ to $V_{CC}$                 | -    | $\pm 10$       | mA   |
| supply current          | $I_{DD}$  | -                                      | -    | 50             | mA   |
| total power dissipation | $P_{tot}$ | -                                      | -    | 500            | mW   |
| power dissipation       | $P_D$     | per output                             | -    | 100            | mW   |
| storage temperature     | $T_{tsg}$ | -                                      | -65  | +150           | °C   |
| soldering temperature   | $T_L$     | 10s                                    | DIP  | 245            | °C   |
|                         |           |                                        | SOP  | 260            | °C   |

### Recommended Operating Conditions

| Parameter             | Symbol    | Conditions | Min. | Typ. | Max.     | Unit |
|-----------------------|-----------|------------|------|------|----------|------|
| supply voltage        | $V_{DD}$  | -          | 3    | -    | 15       | V    |
| input voltage         | $V_I$     | -          | 0    | -    | $V_{DD}$ | V    |
| operating temperature | $T_{amb}$ | -          | -40  | -    | +85      | °C   |

## Electrical Characteristics

DC Characteristics 1 (Tamb=25℃, voltages are referenced to V<sub>SS</sub> (ground=0V), unless otherwise specified.)

| Parameter                 | Symbol          | Conditions(V)                               |                 |                 | Tamb=25℃ |      |       | Unit |
|---------------------------|-----------------|---------------------------------------------|-----------------|-----------------|----------|------|-------|------|
|                           |                 | V <sub>O</sub>                              | V <sub>IN</sub> | V <sub>DD</sub> | Min.     | Typ. | Max.  |      |
| supply current            | I <sub>DD</sub> | -                                           | 0, 5            | 5               | -        | -    | 20    | μA   |
|                           |                 | -                                           | 0, 10           | 10              | -        | -    | 40    | μA   |
|                           |                 | -                                           | 0, 15           | 15              | -        | -    | 80    | μA   |
| LOW-level output current  | I <sub>OL</sub> | 0.4                                         | 0, 5            | 5               | 0.44     | -    | -     | mA   |
|                           |                 | 0.5                                         | 0, 10           | 10              | 1.1      | -    | -     | mA   |
|                           |                 | 1.5                                         | 0, 15           | 15              | 3.0      | -    | -     | mA   |
| HIGH-level output current | I <sub>OH</sub> | 4.6                                         | 0, 5            | 5               | -        | -    | -0.44 | mA   |
|                           |                 | 2.5                                         | 0, 5            | 5               | -        | -    | -1.4  | mA   |
|                           |                 | 9.5                                         | 0, 10           | 10              | -        | -    | -1.1  | mA   |
|                           |                 | 13.5                                        | 0, 15           | 15              | -        | -    | -3.0  | mA   |
| LOW-level output voltage  | V <sub>OL</sub> | -                                           | 0, 5            | 5               | -        | -    | 0.05  | V    |
|                           |                 | -                                           | 0, 10           | 10              | -        | -    | 0.05  | V    |
|                           |                 | -                                           | 0, 15           | 15              | -        | -    | 0.05  | V    |
| HIGH-level output voltage | V <sub>OH</sub> | -                                           | 0, 5            | 5               | 4.95     | -    | -     | V    |
|                           |                 | -                                           | 0, 10           | 10              | 9.95     | -    | -     | V    |
|                           |                 | -                                           | 0, 15           | 15              | 14.95    | -    | -     | V    |
| LOW-level input voltage   | V <sub>IL</sub> | 0.5, 4.5                                    | -               | 5               | -        | -    | 1.5   | V    |
|                           |                 | 1, 9                                        | -               | 10              | -        | -    | 3     | V    |
|                           |                 | 1.5, 13.5                                   | -               | 15              | -        | -    | 4     | V    |
| HIGH-level input voltage  | V <sub>IH</sub> | 0.5, 4.5                                    | -               | 5               | 3.5      | -    | -     | V    |
|                           |                 | 1, 9                                        | -               | 10              | 7        | -    | -     | V    |
|                           |                 | 1.5, 13.5                                   | -               | 15              | 11       | -    | -     | V    |
| input leakage current     | I <sub>I</sub>  | -                                           | 0, 15           | 15              | -        | -    | ±1.0  | μA   |
| OFF-state output current  | I <sub>oz</sub> | nQ output HIGH; returned to V <sub>DD</sub> |                 | 15              | -        | -    | 1.6   | μA   |
|                           |                 | nQ output LOW; returned to V <sub>SS</sub>  |                 | 15              | -        | -    | 1.6   | μA   |
| input capacitance         | C <sub>I</sub>  | -                                           | -               | -               | -        | -    | 7.5   | pF   |

## DC Characteristics 2

(Tamb=-40℃ to +85℃, voltages are referenced to V<sub>SS</sub> (ground=0V), unless otherwise specified.)

| Parameter                 | Symbol          | Conditions(V)                                  |                 |                 | Tamb=-40℃ |       | Tamb=+85℃ |       | Unit |
|---------------------------|-----------------|------------------------------------------------|-----------------|-----------------|-----------|-------|-----------|-------|------|
|                           |                 | V <sub>O</sub>                                 | V <sub>IN</sub> | V <sub>DD</sub> | Min.      | Max.  | Min.      | Max.  |      |
| supply current            | I <sub>DD</sub> | -                                              | 0, 5            | 5               | -         | 20    | -         | 150   | μA   |
|                           |                 | -                                              | 0, 10           | 10              | -         | 40    | -         | 300   | μA   |
|                           |                 | -                                              | 0, 15           | 15              | -         | 80    | -         | 600   | μA   |
| LOW-level output current  | I <sub>OL</sub> | 0.4                                            | 0, 5            | 5               | 0.52      | -     | 0.36      | -     | mA   |
|                           |                 | 0.5                                            | 0, 10           | 10              | 1.3       | -     | 0.9       | -     | mA   |
|                           |                 | 1.5                                            | 0, 15           | 15              | 3.6       | -     | 2.4       | -     | mA   |
| HIGH-level output current | I <sub>OH</sub> | 4.6                                            | 0, 5            | 5               | -         | -0.52 | -         | -0.36 | mA   |
|                           |                 | 2.5                                            | 0, 5            | 5               | -         | -1.7  | -         | -1.1  | mA   |
|                           |                 | 9.5                                            | 0, 10           | 10              | -         | -1.3  | -         | -0.9  | mA   |
|                           |                 | 13.5                                           | 0, 15           | 15              | -         | -3.6  | -         | -2.4  | mA   |
| LOW-level output voltage  | V <sub>OL</sub> | -                                              | 0, 5            | 5               | -         | 0.05  | -         | 0.05  | V    |
|                           |                 | -                                              | 0, 10           | 10              | -         | 0.05  | -         | 0.05  | V    |
|                           |                 | -                                              | 0, 15           | 15              | -         | 0.05  | -         | 0.05  | V    |
| HIGH-level output voltage | V <sub>OH</sub> | -                                              | 0, 5            | 5               | 4.95      | -     | 4.95      | -     | V    |
|                           |                 | -                                              | 0, 10           | 10              | 9.95      | -     | 9.95      | -     | V    |
|                           |                 | -                                              | 0, 15           | 15              | 14.95     | -     | 14.95     | -     | V    |
| LOW-level input voltage   | V <sub>IL</sub> | 0.5, 4.5                                       | -               | 5               | -         | 1.5   | -         | 1.5   | V    |
|                           |                 | 1, 9                                           | -               | 10              | -         | 3     | -         | 3     | V    |
|                           |                 | 1.5, 13.5                                      | -               | 15              | -         | 4     | -         | 4     | V    |
| HIGH-level input voltage  | V <sub>IH</sub> | 0.5, 4.5                                       | -               | 5               | 3.5       | -     | 3.5       | -     | V    |
|                           |                 | 1, 9                                           | -               | 10              | 7         | -     | 7         | -     | V    |
|                           |                 | 1.5, 13.5                                      | -               | 15              | 11        | -     | 11        | -     | V    |
| input leakage current     | I <sub>I</sub>  | -                                              | 0, 15           | 15              | -         | ±1.0  | -         | ±1.0  | μA   |
| OFF-state output current  | I <sub>OZ</sub> | nQ output HIGH;<br>returned to V <sub>DD</sub> |                 | 15              | -         | 1.6   | -         | 12    | μA   |
|                           |                 | nQ output LOW;<br>returned to V <sub>SS</sub>  |                 | 15              | -         | 1.6   | -         | 12    | μA   |

AC Characteristics ( $T_{amb}=25^{\circ}\text{C}$ ,  $V_{SS}=0\text{V}$ , unless otherwise specified.)

| Parameter                           | Symbol             | Conditions                                 | $V_{DD}$            | Min. | Typ. | Max. | Unit |
|-------------------------------------|--------------------|--------------------------------------------|---------------------|------|------|------|------|
| HIGH to LOW propagation delay       | $t_{PHL}$          | nR→nQ; see Figure 4                        | 5 <sup>[1]</sup>    | -    | 90   | 180  | ns   |
|                                     |                    |                                            | 10                  | -    | 35   | 70   | ns   |
|                                     |                    |                                            | 15                  | -    | 25   | 50   | ns   |
| LOW to HIGH propagation delay       | $t_{PLH}$          | nS→nQ; see Figure 4                        | 5 <sup>[1]</sup>    | -    | 65   | 135  | ns   |
|                                     |                    |                                            | 10                  | -    | 25   | 50   | ns   |
|                                     |                    |                                            | 15                  | -    | 15   | 35   | ns   |
| transition time                     | $t_{THL}, t_{TLH}$ | nQ output; see Figure 4                    | 5 <sup>[1][2]</sup> | -    | 60   | 120  | ns   |
|                                     |                    |                                            | 10                  | -    | 30   | 60   | ns   |
|                                     |                    |                                            | 15                  | -    | 30   | 60   | ns   |
| HIGH to OFF-state propagation delay | $t_{PHZ}$          | OE→nQ; see Figure 5                        | 5                   | -    | 45   | 90   | ns   |
|                                     |                    |                                            | 10                  | -    | 25   | 50   | ns   |
|                                     |                    |                                            | 15                  | -    | 20   | 40   | ns   |
| LOW to OFF-state propagation delay  | $t_{PLZ}$          | OE→nQ; see Figure 5                        | 5                   | -    | 50   | 100  | ns   |
|                                     |                    |                                            | 10                  | -    | 20   | 40   | ns   |
|                                     |                    |                                            | 15                  | -    | 15   | 30   | ns   |
| OFF-state to HIGH propagation delay | $t_{PZH}$          | OE→nQ; see Figure 5                        | 5                   | -    | 40   | 80   | ns   |
|                                     |                    |                                            | 10                  | -    | 26   | 60   | ns   |
|                                     |                    |                                            | 15                  | -    | 25   | 50   | ns   |
| OFF-state to LOW propagation delay  | $t_{PZL}$          | OE→nQ; see Figure 5                        | 5                   | -    | 45   | 90   | ns   |
|                                     |                    |                                            | 10                  | -    | 30   | 60   | ns   |
|                                     |                    |                                            | 15                  | -    | 30   | 60   | ns   |
| pulse width                         | $t_W$              | nS input HIGH; minimum width; see Figure 4 | 5                   | 30   | 15   | -    | ns   |
|                                     |                    |                                            | 10                  | 20   | 10   | -    | ns   |
|                                     |                    |                                            | 15                  | 16   | 8    | -    | ns   |
|                                     |                    | nR input HIGH; minimum width; see Figure 4 | 5                   | 30   | 15   | -    | ns   |
|                                     |                    |                                            | 10                  | 20   | 10   | -    | ns   |
|                                     |                    |                                            | 15                  | 16   | 8    | -    | ns   |

Note:

The typical values of the propagation delay and transition times are calculated from the extrapolation formulas shown ( $C_L$  in pF).

## Testing Circuit

### AC Testing Circuit




Figure 3. Test circuit for switching times

Definitions for test circuit:

DUT=Device Under Test

$R_L$ =Load resistance;

$C_L$ =Load capacitance including jig and probe capacitance.

$R_T$ =Termination resistance should be equal to the output impedance  $Z_o$  of the pulse generator.  $V_{EXT}$ =External voltage for measuring switching times.

### AC Testing Waveforms




Figure 4. Input minimum set (nS) and reset (nR) pulse widths, inputs nS or nR to latch output (nQ) propagation delay and nQ transition time




Figure 5. Output enable (OE) to latch output (nQ) enable time ( $t_{PLZ}$  and  $t_{PZH}$ ) and disable time ( $t_{PLZ}$  and  $t_{PZH}$ )

#### Measurement Points

| Supply voltage | Input          |                     | Output              |                     |                     |
|----------------|----------------|---------------------|---------------------|---------------------|---------------------|
| $V_{DD}$       | $V_I$          | $V_M$               | $V_M$               | $V_X$               | $V_Y$               |
| 5V to 15V      | $V_{DD}$ or 0V | $0.5 \times V_{DD}$ | $0.5 \times V_{DD}$ | $0.1 \times V_{DD}$ | $0.9 \times V_{DD}$ |


#### Test Data

| Supply voltage | Input    |             | Load  |             | $V_{EXT}$          |                    |                    |
|----------------|----------|-------------|-------|-------------|--------------------|--------------------|--------------------|
| $V_{DD}$       | $V_I$    | $t_r, t_f$  | $C_L$ | $R_L$       | $t_{PLH}, t_{PHL}$ | $t_{PLZ}, t_{PZL}$ | $t_{PHZ}, t_{PZH}$ |
| 5V to 15V      | $V_{DD}$ | $\leq 20ns$ | 50pF  | 1K $\Omega$ | open               | $V_{DD}$           | GND                |

## Package Information




### · DIP-16

| Size<br>Symbol | Dimensions In Millimeters |          | Size<br>Symbol | Dimensions In Inches |          |
|----------------|---------------------------|----------|----------------|----------------------|----------|
|                | Min( mm)                  | Max( mm) |                | Min( in)             | Max( in) |
| A              | 3.710                     | 4.310    | A              | 0.146                | 0.170    |
| A1             | 0.510                     |          | A1             | 0.020                |          |
| A2             | 3.200                     | 3.600    | A2             | 0.126                | 0.142    |
| B              | 0.380                     | 0.570    | B              | 0.015                | 0.022    |
| B1             | 1.524 (BSC)               |          | B1             | 0.060 (BSC)          |          |
| C              | 0.204                     | 0.360    | C              | 0.008                | 0.014    |
| D              | 18.80                     | 19.20    | D              | 0.740                | 0.756    |
| E              | 6.200                     | 6.600    | E              | 0.244                | 0.260    |
| E1             | 7.320                     | 7.920    | E1             | 0.288                | 0.312    |
| e              | 2.540 (BSC)               |          | e              | 0.100 (BSC)          |          |
| L              | 3.000                     | 3.600    | L              | 0.118                | 0.142    |
| E2             | 8.400                     | 9.000    | E2             | 0.331                | 0.354    |




· SOP-16

| Size<br>Symbol | Dimensions In Millimeters |         |         | Size<br>Symbol | Dimensions In Inches |         |         |
|----------------|---------------------------|---------|---------|----------------|----------------------|---------|---------|
|                | Min(mm)                   | Nom(mm) | Max(mm) |                | Min(in)              | Nom(in) | Max(in) |
| A              | 1.500                     | 1.600   | 1.700   | A              | 0.059                | 0.063   | 0.067   |
| A1             | 0.100                     | 0.150   | 0.250   | A1             | 0.004                | 0.006   | 0.010   |
| A2             | 1.400                     | 1.450   | 1.500   | A2             | 0.055                | 0.057   | 0.059   |
| A3             | 0.600                     | 0.650   | 0.700   | A3             | 0.024                | 0.026   | 0.028   |
| b              | 0.300                     | 0.400   | 0.500   | b              | 0.012                | 0.016   | 0.020   |
| c              | 0.150                     | 0.200   | 0.250   | c              | 0.006                | 0.008   | 0.010   |
| D              | 9.800                     | 9.900   | 10.00   | D              | 0.386                | 0.390   | 0.394   |
| E              | 5.800                     | 6.000   | 6.200   | E              | 0.228                | 0.236   | 0.244   |
| E1             | 3.850                     | 3.900   | 3.950   | E1             | 0.152                | 0.154   | 0.156   |
| e              | 1.27 (BSC)                |         |         | e              | 0.050 (BSC)          |         |         |
| L              | 0.500                     | 0.600   | 0.700   | L              | 0.020                | 0.024   | 0.028   |
| L1             | 1.05 (BSC)                |         |         | L1             | 0.041 (BSC)          |         |         |
| θ              | 0°                        | 4°      | 8°      | θ              | 0°                   | 4°      | 8°      |



· TSSOP-16

| Size<br>Symbol | Dimensions In Millimeters |         | Size<br>Symbol | Dimensions In Inches |         |
|----------------|---------------------------|---------|----------------|----------------------|---------|
|                | Min(mm)                   | Max(mm) |                | Min(in)              | Max(in) |
| A              |                           | 1.200   | A              |                      | 0.047   |
| A1             | 0.050                     | 0.150   | A1             | 0.002                | 0.006   |
| A2             | 0.800                     | 1.050   | A2             | 0.031                | 0.041   |
| b              | 0.190                     | 0.300   | b              | 0.007                | 0.012   |
| c              | 0.090                     | 0.200   | c              | 0.004                | 0.0089  |
| D              | 4.900                     | 5.100   | D              | 0.193                | 0.201   |
| E              | 6.200                     | 6.600   | E              | 0.244                | 0.260   |
| E1             | 4.300                     | 4.480   | E1             | 0.169                | 0.176   |
| e              | 0.65 (BSC)                |         | e              | 0.0256 (BSC)         |         |
| K              | 0°                        | 8°      | K              | 0°                   | 8°      |
| L              | 0.450                     | 0.750   | L              | 0.018                | 0.030   |



## Statement:

- XBLW reserves the right to modify the product manual without prior notice! Before placing an order, customers need to confirm whether the obtained information is the latest version and verify the completeness of the relevant information.
- Any semi-guide product is subject to failure or malfunction under specified conditions. It is the buyer's responsibility to comply with safety standards when using XBLW products for system design and whole machine manufacturing. And take the appropriate safety measures to avoid the potential in the risk of loss of personal injury or loss of property situation!
- XBLW products have not been licensed for life support, military, and aerospace applications, and therefore XBLW is not responsible for any consequences arising from the use of this product in these areas.
- If any or all XBLW products (including technical data, services) described or contained in this document are subject to any applicable local export control laws and regulations, they may not be exported without an export license from the relevant authorities in accordance with such laws.
- The specifications of any and all XBLW products described or contained in this document specify the performance, characteristics, and functionality of said products in their standalone state, but do not guarantee the performance, characteristics, and functionality of said products installed in Customer's products or equipment. In order to verify symptoms and conditions that cannot be evaluated in a standalone device, the Customer should ultimately evaluate and test the device installed in the Customer's product device.
- XBLW documentation is only allowed to be copied without any alteration of the content and with the relevant authorization. XBLW assumes no responsibility or liability for altered documents.
- XBLW is committed to becoming the preferred semiconductor brand for customers, and XBLW will strive to provide customers with better performance and better quality products.