




3191-2Y




3191-3Y




3191-4Y




3191-6Y



3191-9Y



3191-12Y




NOTES:


1. Rated voltage: 300V AC.DC
2. Rated current: 12-8A AC DC
3. Contact resistance: $\leq 20 \text{ m}\Omega$
4. Insulation resistance: $\geq 1000 \text{ M}\Omega$
5. Withstand voltage: 1500V AC/minute
6. Ambient temprature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
7. Material : Nylon UL94V-0(2)
8. Matched RoHS criteria

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: DL67001 (3191) -Y	TITLE: 6.70 mm Pitch Wire To Wire Housing
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR: Chen Quan Long	DATE:20/10/12
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	CHKD: Wu Hui	DATE:20/10/12
DRAWING NO:		APPD:Ren An De	DATE:20/10/12
		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: A


3191-2R




3191-3R




3191-4R




3191-6R



3191-9R




3191-12R



NOTES:

1. Rated voltage: 300V AC. DC
2. Rated current: 12-8A AC DC
3. Contact resistance: $\leq 20 \text{ m}\Omega$
4. Insulation resistance: $\geq 1000 \text{ M}\Omega$
5. Withstand voltage: 1500V AC/minute
6. Ambient temprature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
7. Material : Nylon UL94V-0(2)
8. Matched RoHS criteria



RECOMMENDED HOLE CUTOUT

Circuits	Product name	Dimension mm	
		A	B
1x2	3191-2R	20.90	10.00
1x3	3191-3R	27.20	10.00
1x4	3191-4R	34.30	10.00
2x3	3191-6R	27.90	17.30
3x3	3191-9R	28.40	23.70
3x4	3191-12R	35.40	23.70

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME: DL67001 (3191) -R	TITLE: 6.70 mm Pitch Wire To Wire Housing
.XX: ± 0.15	.X° : $\pm 2.0^{\circ}$		
.XXX: ± 0.01	.XX° : $\pm 1.0^{\circ}$	DR: Chen Quan Long	DATE:20/10/12
FINISH:		CHKD: Wu Hui	DATE:20/10/12
DRAWING NO:		APPD:Ren An De	DATE:20/10/12
		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: A

REV.	REVISION DESCRIPTION	DATE	APPD

NOTES:

Rated voltage: 300V AC.DC

Rated current: 12-8A AC DC

Contact resistance: ≤20 mΩ

Insulation resistance: ≥1000 MΩ




Withstand voltage: 1500V AC/minute

Ambient temprature:-40℃~+105℃


Wire range: AWG#20~#14

Materials:

Terminal: Phosphor bronze,Tin plated



GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL67001 (3191)-RT		TITLE: 6.70 mm Pitch Crimp Terminal	
.XX: ± 0.15	.X° : ± 2.0°				
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Ni Sheng Le	DATE:21/05/20	PART NO:	
FINISH:		CHKD: Wu Hui	DATE:21/05/20		
DRAWING NO:		APPD:Ren An De	DATE:21/05/20	UNITS: mm	PAGE: 1/1 REV.: A



REV.	REVISION DESCRIPTION	DATE	APPD

NOTES:

Rated voltage: 300V AC.DC

Rated current: 12-8A AC DC

Contact resistance: $\leq 20\text{ m}\Omega$

Insulation resistance: $\geq 1000\text{ M}\Omega$

Withstand voltage: 1500V AC/minute

Ambient temprature: -40℃ ~ +105℃

Wire range: AWG#20 ~ #14

Materials:

Terminal: Phosphor bronze, Tin plated

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL67001 (3191)-T	TITLE: 6.70 mm Pitch Crimp Terminal
.XX: ± 0.15	.X° : ± 2.0°	DR: Ni Sheng Le	DATE: 21/05/20
.XXX: ± 0.01	.XX° : ± 1.0°	DATE: 21/05/20	PART NO:
FINISH:		CHKD: Wu Hui	SCALE: N/A
DRAWING NO:		APPD: Ren An De	DATE: 21/05/20
			PAGE: 1/1
			UNITS: mm
			REV.: A