




SEC:A-A



SEC:B-B

Ordering Information:

A2543 - *** - ***
1 2 3

1.Part NO.

2.Material:

GB: Brass

GP: Phosphor Bronze

3.Finish:

(Blank): Gold over Nickel(Au:1μin[0.03μm] Min)

G10: Gold over Nickel(Au:10μin[0.25μm] Min,Mating Area)

G15: Gold over Nickel(Au:15μin[0.38μm] Min,Mating Area)

G30: Gold over Nickel(Au:30μin[0.76μm] Min,Mating Area)

Ordering information & Specifications

Unit:mm

Part No	Wire Range	Insultion O.D.	Material	Finish	Qty/reel
A2543-TB	AWG#22-#28	1.57mm(max)	Brass	Tin over Nickel	10,000 PCS
A2543-TP	AWG#22-#28	1.57mm(max)	Phosphor Bronze	Tin over Nickel	10,000 PCS
A2543-GB	AWG#22-#28	1.57mm(max)	Brass	Gold over Nickel	10,000 PCS
A2543-GP	AWG#22-#28	1.57mm(max)	Phosphor Bronze	Gold over Nickel	10,000 PCS

A3	CHANGE THE DRAWING	2023.12.07
A2	CHANGE THE DRAWING	2023.06.16
A1	CHANGE THE DRAWING	2022.11.19
A0	NEW RELEASE	2013.03.29
REV	DESCRIPTION	DATE

CJTconn CHANGJIANG CONNECTORS CO.,LTD.			TITLE	
Unit	Scale	Sheet	2.54mm PITCH	
mm	8:1	1 of 1		
DRAWN	CHK'D	APPR	CRIMP TERMINAL	
Chengbiao Ye	Djankui Wan	Jack Yin		
General Tolerances		THIRD ANGLE PROJECTION	DRAWING NO.	REV
x,x±0.25 x.xx±0.20 x.xxx±0.15 ANGLES ±1°			A2543-T	A3