






RECOMMENDED PCB LAYOUT – COMPONENT SIDE
RECOMMENDED PCB THICKNESS : 2.36MM(.093 INCH)
(MINIMUM PCB THICKNESS : 1.57)

THE ENTIRE AREA OF THE CONNECTOR FOOTPRINT
TO BE CONSIDERED THE KEEP OUT AREA FOR COMPONENTS
THIS AREA IS INDICATED BY THE DASHED LINE



DETAIL-KEEPOUT ZONES


THE HATCHED AREA IN THIS VIEW INDICATES ZONES
THAT ARE OCCUPIED BY THE PLASTIC HOUSING THAT
SEATS AGAINST THE PCB AND BY THE VERTICAL METAL
CAGE WALL THAT STOPS JUST SHORT OF THE PCB




L11	L10	T1	T20
⊕ L12	⊕ L9	⊕ T3	⊕ T19
⊕ L13	⊕ L8	⊕ T4	⊕ T18
⊕ L14	⊕ L7	⊕ T5	⊕ T17
⊕ L15	⊕ L6	⊕ T6	⊕ T16
⊕ L16	⊕ L5	⊕ T7	⊕ T15
⊕ L17	⊕ L4	⊕ T8	⊕ T14
⊕ L18	⊕ L3	⊕ T9	⊕ T13
⊕ L19	⊕ L2	⊕ T10	⊕ T12
⊕ L20	⊕ L1	⊕ T11	⊕ T1

CIRCUIT NUMBERING
COMPONENT SIDE OF BOARD
4:1

TITLE SFP 2X1 CAGE+CONNECTOR			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd				
PART NO. SFP 1658391 2x1Y			GENERAL TOLERANCE			UNIT:MM	SIZE: A4
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1	SHEET:2/3	REV:A
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5°			
			.XXX±0.10				



BEZEL CUT-OUT CENTER SPACING DETAIL



SECTION Z-Z

TITLE SFP 2X1 CAGE+CONNECTOR			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd			
PART NO. SFP 1658391 2x1Y			GENERAL TOLERANCE		UNIT:MM	SIZE: A4
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1	SHEET:3/3
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5°		
			.XXX±0.10			