




Connectors > Contacts > PCB Spring Contacts



Spring Finger Type: **Ultra Small - C-Clip**

Scalable: **No**

Side Protected: **Yes**

Uncompressed Height: **1.2 mm [.047 in]**

Product Length: **2 mm [.079 in]**

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board
Spring Finger Type	Ultra Small - C-Clip
Scalable	No

Configuration Features

Number of Positions	1
Side Protected	Yes

Contact Features

Contact Underplating Material	Nickel
Contact Base Material	Stainless Steel
PCB Contact Termination Area Plating Material	Gold
Contact Working Range (Low)	.5 mm[.02 in]
Contact Working Range (High)	.9 mm[.035 in]
Point of Contact Area Plating Material	Gold



Contact Current Rating (Max)	1 A
------------------------------	-----

Dimensions

Uncompressed Height	1.2 mm[.047 in]
Product Length	2 mm[.079 in]
Product Width	1 mm[.039 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Method	Tape & Reel
Packaging Quantity	9000

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 2118788-1 DUAL BAND WIFI, STAMPED ANTENNA	 TE Part # 2108788-1 PCB Antenna, SMD, 824-960 & 1710-1990MHz	 TE Part # 2108788-2 PCB Antenna, SMD, 824-960 & 1710-1990MHz	 TE Part # 1513273-1 PCB Antenna DUAL BAND US EU
 TE Part # 1513430-2 PCB ANTENNA SINGLE BAND BULK PKGD	 TE Part # 1513431-1 PCB ANTENNA SINGLE BAND TAPE AND REELED	 TE Part # 1513259-1 WORLD GSM PCB ANTENNA BULK PACKAGED	 TE Part # 1513156-1 PCB ANTENNA TAPE & REELED PACKED
 TE Part # 1513169-1 PCB ANTENNA SINGLE BAND	 TE Part # 1513259-9 WORLD GSM PCB ANTENNA TAPE AND REELED	 TE Part # 2118903-1 LTE/Cell Band Antenna	 TE Part # 2118908-1 PCB WLAN TRIPLE BAND BULK PACKAGED
 TE Part # 2118908-2 PCB,WLAN TRIPLE BAND TAPE AND REELED	 TE Part # 2108891-1 PCB Ant, Tab mount, Wi-Fi 6E Triple Band	 TE Part # 2195728-1 LTE + GNSS ANTENNA	 TE Part # 2195852-1 PCB ANT, TAB MOUNT, 698-5875MHz, 55X20mm
 TE Part # 1513317-1 PCB ANTENNA PENTA BAND	 TE Part # 1513430-1 PCB ANTENNA SINGLE BAND TAPE AND REELED	 TE Part # 2108790-1 PCB ANTENNA SINGLE BAND BULK PACKAGED	 TE Part # 2108991-1 Helical Antenna,PCB,SMT, For IoT

Customers Also Bought



Documents

Product Drawings
SPRING FINGER 1.2H
English

CAD Files
3D PDF
3D

Customer View Model
ENG_CVM_CVM_2306334-3_A.2d_dxf.zip
English

Customer View Model
ENG_CVM_CVM_2306334-3_A.3d_igs.zip
English

Customer View Model
ENG_CVM_CVM_2306334-3_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

2306334-3

Ultra Small - C-Clip PCB Spring Contact, Side Protected, 1.2 mm [.047 in]
Uncompressed Height, 2 mm [.079 in] Length, 1 mm [.039 in] Width



Product Specification

English