

|                                       |  |   |  |              |           |                                      |         |         |         |                  |          |               |        |                              |          |
|---------------------------------------|--|---|--|--------------|-----------|--------------------------------------|---------|---------|---------|------------------|----------|---------------|--------|------------------------------|----------|
| 1                                     |  | 2 |  | 3            | 4         |                                      | 5       |         | 6       |                  |          |               |        |                              |          |
| 芯位排布                                  |  |   |  | 技术<br>参<br>数 | 芯数        | 2                                    | 3       | 4       | 4D      | 5                | 5B       | 6             | 8      | 12                           | 17       |
|                                       |  |   |  |              | 额定电流/电压   | 4A/250V                              | 4A/250V | 4A/250V | 4A/250V | 4A/60V           | 4A/60V   | 2A/30V        | 2A/30V | 1.5A/30V                     | 1.5A/30V |
|                                       |  |   |  |              | 额定脉冲电压    | 2500V                                | 2500V   | 2500V   | 2500V   | 1500V            | 1500V    | 800V          | 800V   | 800V                         | 800V     |
|                                       |  |   |  |              | 绝缘电阻 (MΩ) | ≥100                                 | ≥100    | ≥100    | ≥100    | ≥100             | ≥100     | ≥100          | ≥100   | ≥100                         | ≥100     |
|                                       |  |   |  |              | 接触电阻 (mΩ) | ≤5                                   | ≤5      | ≤5      | ≤5      | ≤5               | ≤5       | ≤5            | ≤5     | ≤5                           | ≤5       |
| P.C.B. 开孔尺寸                           |  |   |  |              |           |                                      |         |         |         |                  |          |               |        |                              |          |
| 面板开孔尺寸                                |  |   |  |              |           |                                      |         |         |         |                  |          |               |        |                              |          |
| 6 插板式母针直针镀金                           |  |   |  | pc           | 2~17      | GENERAL TOLERANCE (UNLESS SPECIFIED) |         | 绘图 DWN  |         | W. M 2024. 8. 24 |          |               |        |                              |          |
| 5 六角螺母黄铜 M16*1.5螺纹, 单边倒角 (M12座子螺母) 亮镍 |  |   |  | pc           | 1         | ≤10 ±0.1                             |         | 确认 CHK  |         |                  |          |               |        |                              |          |
| 4 丁腈橡胶 φ16*φ12*2黑色                    |  |   |  | pc           | 1         | <10~≤20 ±0.2                         |         | 核准 APVD |         |                  |          | 品名 TITLE      |        | M12板前安装孔型金属插座 插板式 锁板牙M16*1.5 |          |
| 3 M12螺纹式板前, 母座铜外壳 锁板牙M16*1.5          |  |   |  | pc           | 1         | <20~≤50 ±0.5                         |         |         |         |                  |          | 品号 PART NO    |        |                              |          |
| 2 M12 孔型胶芯长体带倒角 黑色                    |  |   |  | pc           | 1         | Angle ±1°                            |         |         |         |                  |          | 型号 DRAWING NO |        | M12-Sxx-GPBM16               |          |
| 1 丁腈橡胶 φ9*φ6*1.5黑色                    |  |   |  | pc           | 1         |                                      |         | 单位 UNIT |         | MM               | 版本 REV   | A             |        |                              |          |
| No. Specification                     |  |   |  | Unit         | Q'ty      | 视角 THIRD ANGLE                       |         | 尺寸 SIZE |         | A4               | 页码 SHEET | 1 OF 1        |        |                              |          |