







NOTES:

备注

1. Red Copper, nickel base, matte tin
紫铜T2, 镍底, 镀雾锡
2. Wire screw hole M5
压线螺孔M5
3. Current Rating: 150A
额定电流: 150A
4. Operating temperature: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$
工作温度: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$
5. There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
6. Unmarked dimensions refer to tolerances
未标注的尺寸参考公差



Ordering Information

HC - * * * - * * * - FD * * * * - 02

Type	Screw Thread	Welding Feet	Series	D-BIP	Product No.	Material
M-Pull Teeth (铆牙)	S-M5 (螺牙)	(焊脚)	0808-8x8mm	S-SMT	产品序号	默认=Copper
BN-Rivet Nut (铆螺母)	4-M5 (螺牙)	2-2个	16D-16x20mm	FD-Flag		(黄铜)
RG-Rivet Gasket (铆垫片)	S-M5 (螺牙)	4-4个		Rip		HC=Red Copper (紫铜)
	6-M6 (螺牙)	6-6个				

			GENERAL TOLERANCE	制图 DRAWING	02	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审核 CHECK					
			5 or more ± 0.35	批准 APPROVAL		产品名称 TITLE	PCB 焊接端子 侧插 铆垫片 M5 4焊脚 13x19x14.1mm 紫铜	版本 REV.	A
1	初版发行		2~5 ± 0.25	比例 SCALE		产品料号 PART NO.	HC-RG54-1319-FD066RC-02	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	0~2 ± 0.15	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
			Angle $\pm 3.0^{\circ}$						