


### 1. External Dimensions (Unit:m/m)



TYPE	A	B	C	D	E	Q'Ty/Reel
ANL322522	3.2±0.2	2.5±0.2	2.2±0.2	1.9±0.2	0.5Ref	2000

### 2. Part Number Code

ANL 322522 LC J 4R7  
 A B C D E

- A: Series Name Wire Wound Chip Inductors
- B: Dimensions(mm) 322522:3.2×2.5×2.2
- C: Internal controls
- D: Tolerance J: ±5%
- E: Inductance 4R7=4.7uH

### 3. Electrical Characteristics

Part Number	Inductance (uH)	Tolerance	Q Min.	DCR (Ω) Max.	Rated Current (mA)Max.	SRF (MHz)Min.	L,Q Test Frequency (MHz)
ANL322522LCJ4R7	4.7	±5%	30	1.5	220	50	7.96

### 4. Curve

Typical electrical characteristics inductance change vs.DC superposition characteristics

