


Features

- 5µA Current at no Load
- ±2% Output Accuracy
- 150mA Output Current
- Current Limit Protection

Applications


- Industrial Controls
- Home Automation
- Modules (Wireless, Camera, etc.)
- Portable, Battery Powered Equipment

PIN CONFIGURATION



| Pin Number | | | | Pin Name | Pin Function |
|------------|-----------|-----------|----------|----------|-------------------------|
| SOT23-5(K) | SOT89(RA) | SOT89(RB) | SOT89(R) | | |
| 2 | 1 | 2 | 2 | GND | Ground |
| 1 | 2 | 3 | 1 | VIN | Input of Supply Voltage |
| 5 | 3 | 1 | 3 | VOUT | Output of the Regulator |
| 3 | -- | -- | -- | EN | Enable Control Input |
| 4 | -- | -- | -- | NC | No Internal Connection |

Ordering Information




Example: AP2204K-3.3TRG1
→ 3.3V Version, in SOT23-5 Package & Tape & Reel Packing Type

Absolute Maximum Ratings


over operating free-air temperature range (unless otherwise noted)

| | | MIN | MAX | UNIT |
|-------------|------------------------------------|--------------------|----------|------|
| VIN | Continuous input voltage range | -0.3 | 29 | V |
| VOUT | Output voltage range | -0.3 | 6 | |
| EN | EN pin voltage range | -0.3 | VOUT+0.3 | |
| IOUT | Output pin current | Internally limited | | mA |
| Temperature | Operating junction, T _J | -25 | 85 | °C |
| | Storage, T _{stg} | -40 | 125 | |

BLOCK DIAGRAM



Typical Application Circuit



Electrical Characteristics

(VIN=15V, VEN=5V, TA=25°C, unless otherwise specified)


| PARAMETER | SYMBOL | TEST Conditions | MIN | TYP | MAX | UNIT |
|--|--------------|---|-----|------|-----|------|
| Supply Voltage | VIN | | 1.7 | -- | 27 | V |
| Output current | IOUT | | 0 | 250 | 300 | mA |
| DC Output Voltage Accuracy | | IOUT = 0.1mA | -2 | -- | 2 | % |
| Dropout Voltage (VIN-VOUT) | IOUT = 100mA | VOUT = 2.8V | -- | 480 | -- | mV |
| | | VOUT = 3.0V | -- | 450 | -- | |
| | | VOUT = 3.3V | -- | 420 | -- | |
| | | VOUT = 5.0V | -- | 350 | -- | |
| Maximum output current | Ioutmax | VIN= VOUT+1V | -- | 500 | -- | mA |
| Ground Current (IOUT = 0mA) | IQ | VOUT = 3.3V | -- | 5 | -- | uA |
| Shutdown Ground Current | ISD | VEN = 0V, VOUT = 0V | -- | 0.01 | 0.5 | |
| VOUT Shutdown Leakage Current | ILEAK | | -- | 0.01 | 0.5 | |
| Enable Threshold Voltage | VIH | EN Rising | 1.3 | -- | -- | V |
| | VIL | EN Falling | -- | -- | 0.7 | |
| EN Input Current | IEN | VEN = 5V | -- | 10 | 100 | nA |
| Line Regulation | ΔLINE | IOUT = 1mA, 2≤VIN≤18V | -- | 0.3 | -- | % |
| Load Regulation | ΔLOAD | 10mA≤ IOUT ≤ 100mA | -- | 0.3 | -- | |
| Output Current Limit | ILIM | VOUT=0.9× VOUT(NOM) | 300 | 450 | | mA |
| Power Supply Rejection Ratio | PSRR | VOUT = 3.3V, IOUT = 30mA, VIN = 6V, f = 1kHz | -- | 65 | -- | dB |
| Thermal Shutdown Temperature | TSD | IOUT = 10mA | -- | 160 | -- | °C |
| Thermal Shutdown Hysteresis | ΔTSD | | -- | 15 | -- | |
| Package Thermal Resistance θJA (Note 1) | SOT23-5 | Thermal Resistance Junction-toAmbient | -- | 220 | -- | °C/W |
| | SOT23-3L | | -- | 210 | -- | |
| | SOT89-3 | | -- | 120 | -- | |
| Total Power Dissipation Tc=25°C | SOT23-5 | PDTOT | -- | 0.25 | -- | W |
| | SOT23-3L | | -- | 0.3 | -- | |
| | SOT89-3 | | -- | 0.5 | -- | |

Note: 1. Test condition: the device is mounted on FR-4 substrate PC board, with minimum recommended pad layout.


Typical Operating Characteristics (25 °C, unless otherwise noted)

Unless otherwise specified: $T_A = 25^\circ\text{C}$, $V_{IN} = V_O(\text{NOM}) + 1\text{V}$, $C_{OUT} = 1\ \mu\text{F}$, $C_{IN} = 1\ \mu\text{F}$ all voltage options, EN pin tied to V_{IN} .


Output Voltage vs. Input Voltage




Output Voltage vs. Junction Temperature




Supply Current vs. Input Voltage




Ground Current vs. Junction Temperature



Dropout Voltage vs. Junction Temperature




Output Voltage vs. Input Voltage



Package information


SOT23-5



| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|----------|------------------------------|-------|-------------------------|-------|
| | MIN | MAX | MIN | MAX |
| A | 1.050 | 1.250 | 0.041 | 0.049 |
| A1 | 0.000 | 0.100 | 0.000 | 0.004 |
| A2 | 1.050 | 1.150 | 0.041 | 0.045 |
| b | 0.300 | 0.500 | 0.012 | 0.020 |
| c | 0.100 | 0.200 | 0.004 | 0.008 |
| D | 2.820 | 3.020 | 0.111 | 0.119 |
| E | 1.500 | 1.700 | 0.059 | 0.067 |
| E1 | 2.650 | 2.950 | 0.104 | 0.116 |
| e | 0.950 BSC | | 0.037 BSC | |
| e1 | 1.900 BSC | | 0.075 BSC | |
| L | 0.300 | 0.600 | 0.012 | 0.024 |
| θ | 0° | 8° | 0° | 8° |

Package information

SOT89-3



| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|--------|---------------------------|-------|----------------------|-------|
| | Min | Max | Min | Max |
| A | 1.400 | 1.600 | 0.055 | 0.063 |
| b | 0.350 | 0.520 | 0.013 | 0.197 |
| b | 0.400 | 0.580 | 0.016 | 0.023 |
| c | 0.350 | 0.450 | 0.014 | 0.018 |
| D | 4.400 | 4.600 | 0.173 | 0.181 |
| D | 1.550 | 1.750 | 0.061 | 0.069 |
| E | 2.350 | 2.600 | 0.091 | 0.102 |
| E | 3.720 | 4.530 | 0.146 | 0.178 |
| e | 1.500TYP | | 0.060TYP | |
| e | 3.000TYP | | 0.118TYP | |
| L | 0.820 | 1.100 | 0.032 | 0.047 |