

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
40V	1.2mΩ@10V	120A



合肥矽普半导体

Siliup Semiconductor Technology Co., Ltd

技术 品质 服务

www.siliup.com


Feature

- Fast Switching
- Low Gate Charge and Rdson
- Advanced Split Gate Trench Technology
- 100% Single Pulse avalanche energy Test

Applications


- Power switching application
- PWM Application
- DC-DC Converter

Package




PDFN5X6-8L

Circuit diagram



Marking



40N01GH :Device Code
* :Month Code

Order Information

Device	Package	Unit/Tape
SP40N01GHNK	PDFN5X6-8L	5000

Absolute maximum ratings (Ta=25°C, unless otherwise noted)

Parameter		Symbol	Rating	Unit
Drain-Source Voltage		V_{DS}	40	V
Gate-Source Voltage		V_{GS}	± 20	V
Continuous Drain Current (Tc=25°C)	Silicon Limit	I_D	230	A
Continuous Drain Current (Tc=25°C)	Package Limit	I_D	120	A
Continuous Drain Current (Tc=100°C)		I_D	80	A
Pulse Drain Current Tested		I_{DM}	480	A
Single pulsed avalanche energy ¹		E_{AS}	1089	mJ
Power Dissipation (Tc=25°C)		P_D	130	W
Thermal Resistance Junction-to-Case		$R_{\theta JC}$	0.96	°C/W
Storage Temperature Range		T_{STG}	-55 to 150	°C
Operating Junction Temperature Range		T_J	-55 to 150	°C







Electrical characteristics (Ta=25°C, unless otherwise noted)






Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	VGS=0V , ID=250uA	40	-	-	V
Drain-Source Leakage Current	IDSS	VDS=32V , VGS=0V , TJ=25℃	-	-	1	uA
Gate-Source Leakage Current	IGSS	VGS=±20V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	VGS(th)	VGS=VDS , ID =250uA	2	2.8	4	V
Static Drain-Source On-Resistance	RDS(ON)	VGS =10V, ID =20A	-	1.2	1.5	mΩ
Dynamic characteristics						
Input Capacitance	Ciss	VDS=20V , VGS=0V , f=1MHz	-	5750	-	pF
Output Capacitance	Coss		-	1950	-	
Reverse Transfer Capacitance	Crss		-	69	-	
Total Gate Charge	Qg	VDS=20V , VGS=20V , ID=30A	-	126	-	nC
Gate-Source Charge	Qgs		-	18	-	
Gate-Drain Charge	Qgd		-	15.5	-	
Switching Characteristics						
Turn-On Delay Time	Td(on)	VDD=20 VGS=20V , RG=3Ω, ID=30A	-	18	-	nS
Rise Time	Tr		-	5	-	
Turn-Off Delay Time	Td(off)		-	52	-	
Fall Time	Tf		-	9.5	-	
Diode Characteristics						
Diode Forward Voltage	VSD	VGS=0V , IS=1A , TJ=25℃	-	-	1.2	V
Diode Continuous Current	IS	IS=20A, di/dt=100A/us, Tj=25℃	-	-	120	A
Reverse recover time	Trr		-	29	-	nS
Reverse recovery charge	Qrr		-	113	-	nC

Note:


- The EAS Test condition is $V_{DD}=20V, V_{GS}=10V, L=0.5mH, R_G=25\Omega$

Typical Characteristics







PDFN5X6-8L Package Information



Top View
[顶视图]



Bottom View
[背视图]



Side View
[侧视图]

Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.900	1.000	0.035	0.039
A3	0.254REF.		0.010REF.	
D	4.944	5.096	0.195	0.201
E	5.974	6.126	0.235	0.241
D1	3.910	4.110	0.154	0.162
E1	3.375	3.575	0.133	0.141
D2	4.824	4.976	0.190	0.196
E2	5.674	5.826	0.223	0.229
k	1.190	1.390	0.047	0.055
b	0.350	0.450	0.014	0.018
e	1.270TYP.		0.050TYP.	
L	0.559	0.711	0.022	0.028
L1	0.424	0.576	0.017	0.023
H	0.574	0.726	0.023	0.029
θ	10°	12°	10°	12°