




Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



KIT

REPRESENTATION ONLY

TE Part # 7-2150312-7
OCEAN_2.0_SPARE_PART_KIT-110F250F




TE Part # 2150312-1
OCEAN_2.0_Applicator-E-110F250F-REM



TE Part # 2150312-2
OCEAN_2.0_Applicator-E-110F250F-REA

Also in the Series | **FASTON 187**



Crimp Terminal Housings(40)



Insertion & Extraction Tools(1)



Insulation Boots & Sleeves(1)



Joints & Splices(1)



PCB Terminals(42)




Quick Disconnects(207)



Splices(1)

Customers Also Bought



TE Part #745229-4
PIN CONT 20DF L.P.



TE Part #521596-2
ULTRA-POD 187 ASSY REC 22-18 AWG TPBR



TE Part #1-2106123-1
CONTACT,Recept, SLC, Tin Plated, On Stri




TE Part #2154854-1
SlimSeal Assembly, Plug, 1 position




TE Part #2106123-2
Contact, Receptacle, Tin Plated, Loose P



TE Part #52454
PG SPR SPD 22-16COMM 22-18MIL8



TE Part #2-2106124-7
Contact, Tab, Tin Plated, LP 22-16 AWG



TE Part #2106124-9
Contact, Tab, Tin Plated, Std Lgth, LP



Documents

Product Drawings

187 FASTON REC 18-14 AWG BR

English

CAD Files

Customer View Model

ENG_CVM_CVM_60742-1_AD.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_60742-1_AD.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_60742-1_AD.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

82004 FASTON Terminals (Insulated and Uninsulated) Catalog - FASTON Receptacles Section

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Application and Maintenance for Hand Crimping Tool

English

Agency Approvals

UL Report

English