

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
40V	0.8mΩ@10V	200A
	1.1mΩ@4.5V	



合肥矽普半导体
Siliup Semiconductor Technology Co., Ltd
技术 品质 服务
www.siliup.com


Feature

- Fast Switching
- Low Gate Charge and Rdson
- Cu-Clip Process
- Advanced Split Gate Trench Technology
- 100% Single Pulse avalanche energy Test

Applications


- PWM Application
- Hard switched and high frequency circuits
- Power Management

Package




PDFN5X6-8L

Circuit diagram



Marking



40N01ABGP
**

:Device Code
:Week Code

Order Information

Device	Package	Unit/Tape
SP40N01ABGNP	PDFN5X6-8L	5000

**Absolute maximum ratings (Ta=25°C, unless otherwise noted)**

Parameter	Symbol	Rating	Units
Drain-Source Voltage	V_{DS}	40	V
Gate-Source Voltage	V_{GS}	± 20	V
Continuous Drain Current (Tc=25°C)	I_D	200	A
Continuous Drain Current (Tc=100°C)	I_D	135	A
Pulsed Drain Current	I_{DM}	800	A
Single Pulse Avalanche Energy ¹	E_{AS}	756	mJ
Power Dissipation (Tc=25°C)	P_D	150	W
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	0.83	°C/W
Storage Temperature Range	T_{STG}	-55 to 150	°C
Operating Junction Temperature Range	T_J	-55 to 150	°C

Electrical characteristics (Ta=25°C, unless otherwise noted)


Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	VGS=0V , ID=250uA	40	-	-	V
Drain-Source Leakage Current	I _{DSS}	VDS=32V , VGS=0V , TJ=25℃	-	-	1	uA
Gate-Source Leakage Current	I _{GSS}	VGS=±20V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	VGS(th)	VGS=VDS , ID =250uA	1	1.7	2.5	V
Static Drain-Source On-Resistance	R _{DS(ON)}	VGS=10V , ID=20A	-	0.8	1	mΩ
		VGS=4.5V , ID=20A	-	1.1	1.5	
Dynamic characteristics						
Input Capacitance	C _{iss}	VDS=20V , VGS=0V , f=1MHz	-	6300	-	pF
Output Capacitance	C _{oss}		-	1450	-	
Reverse Transfer Capacitance	C _{rss}		-	95	-	
Total Gate Charge	Q _g	VDS=20V , VGS=10V , ID=50A	-	98	-	nC
Gate-Source Charge	Q _{gs}		-	17	-	
Gate-Drain Charge	Q _{gd}		-	21	-	
Switching Characteristics						
Turn-On Delay Time	T _{d(on)}	VDD=20V , VGS=10V , RG=1.6Ω ID=50A	-	13.5	-	nS
Rise Time	T _r		-	35.8	-	
Turn-Off Delay Time	T _{d(off)}		-	66	-	
Fall Time	T _f		-	24.8	-	
Diode Characteristics						
Diode Forward Voltage	V _{SD}	VGS=0V , IS=1A , TJ=25℃	-	-	1.2	V
Maximum Body-Diode Continuous Current	I _S		-	-	200	A
Reverse Recovery Time	T _{rr}	IS=20A, di/dt=200A/us, TJ=25	-	58	-	nS
Reverse Recovery Charge	Q _{rr}		-	85	-	nC

Note :


1. The test condition is $V_{DD}=20V, V_{GS}=10V, L=0.5mH, R_G=25\Omega$




Typical Characteristics




Output Characteristics




Transfer Characteristics




Capacitance Characteristics




Gate Charge




On-Resistance vs Gate to Source Voltage




Normalized On-Resistance




RDS(on) VS Drain Current




Forward characteristics of reverse diode




Normalized breakdown voltage




Normalized Threshold voltage




Current dissipation



Power dissipation




Maximum Transient Thermal Impedance




Safe Operation Area


PDFN5X6-8L Package Information



Top View
[顶视图]



Bottom View
[背视图]



Side View
[侧视图]

Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.900	1.000	0.035	0.039
A3	0.254REF.		0.010REF.	
D	4.944	5.096	0.195	0.201
E	5.974	6.126	0.235	0.241
D1	3.910	4.110	0.154	0.162
E1	3.375	3.575	0.133	0.141
D2	4.824	4.976	0.190	0.196
E2	5.674	5.826	0.223	0.229
k	1.190	1.390	0.047	0.055
b	0.350	0.450	0.014	0.018
e	1.270TYP.		0.050TYP.	
L	0.559	0.711	0.022	0.028
L1	0.424	0.576	0.017	0.023
H	0.574	0.726	0.023	0.029
θ	10°	12°	10°	12°