

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
-20V	35mΩ@-4.5V	-4A
	45mΩ@-2.5V	



合肥矽普半导体

Siliup Semiconductor Technology Co., Ltd

技术 品质 服务

www.siliup.com


Feature

- High power and current handling capability
- Surface mount package

Application


- Battery Switch
- DC/DC Converter

Package




SOT-23-6L

Circuit diagram



Marking



20P35 :Device Code

Order Information

Device	Package	Unit/Tape
SP20P35TS	SOT-23-6L	3000


Absolute maximum ratings (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	-20	V
Gate-Source Voltage	V_{GS}	± 12	V
Continuous Drain Current	I_D	-4	A
Pulse Drain Current Tested	I_{DM}	-16	A
Power Dissipation	P_D	1.5	W
Thermal Resistance Junction-to-Ambient	$R_{\theta JA}$	83	°C/W
Storage Temperature Range	T_{STG}	-55 to 150	°C
Operating Junction Temperature Range	T_J	-55 to 150	°C


Electrical characteristics (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	VGS=0V , ID=-250μA	-20	-	-	V
Drain-Source Leakage Current	I _{DSS}	VDS=-16V , VGS=0V	-	-	-1	uA
Gate-Source Leakage Current	I _{GSS}	VGS=±12V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	VGS(th)	VDS=VGS , ID=-250μA	-0.4	-0.75	-0.9	V
Static Drain-Source On-Resistance	R _{DS(ON)}	VGS=-4.5V, ID=-3.3A	-	35	57	mΩ
		VGS=-2.5V, ID=-2.8A	-	45	76	
Dynamic characteristics						
Input Capacitance	C _{iss}	VDS=-15V , VGS=0V , f=1MHz	-	686	-	pF
Output Capacitance	C _{oss}		-	90.8	-	
Reverse Transfer Capacitance	C _{rss}		-	80.4	-	
Total Gate Charge	Q _g	VDS=-15V , VGS=-4.5V , ID=-3A	-	9.7	-	nC
Gate-Source Charge	Q _{gs}		-	2.05	-	
Gate-Drain Charge	Q _{gd}		-	2.43	-	
Switching Characteristics						
Turn-On Delay Time	t _{d(on)}	VDD=-10V VGS=-4.5V , RG=3.3Ω, ID=3A,	-	4.8	-	nS
Turn-On Rise Time	t _r		-	9.6	-	
Turn-Off Delay Time	t _{d(off)}		-	52	-	
Turn-Off Fall Time	t _f		-	8.4	-	
Source-Drain Diode characteristics						
Diode Forward Voltage	V _{SD}	VGS=0V , IS=-1A , TJ=25℃	-	-	-1.2	V


Typical Characteristics




Output Characteristics




Transfer Characteristics




Capacitance Characteristics




Gate Charge




Current dissipation




Power dissipation




$R_{DS(on)}$ VS Drain Current




Forward characteristics of reverse diode




Normalized breakdown voltage



Normalized Threshold voltage




Maximum Transient Thermal Impedance



Safe Operation Area

SOT-23-6L Package Information



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
e	0.950(BSC)		0.037(BSC)	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°