

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
-20V	18mΩ@-4.5V	-7A
	28mΩ@-2.5V	



合肥矽普半导体

Siliup Semiconductor Technology Co., Ltd

技术 品质 服务

www.siliup.com


Feature

- High power and current handing capability
- Surface mount package

Application


- Battery Switch
- DC/DC Converter

Package




SOT-23-3L

Circuit diagram



Marking



Order Information

Device	Package	Unit/Tape
SP20P18T1	SOT-23-3L	3000


Absolute maximum ratings (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	-20	V
Gate-Source Voltage	V_{GS}	± 10	V
Continuous Drain Current	I_D	-7	A
Pulse Drain Current Tested	I_{DM}	-28	A
Power Dissipation	P_D	1.3	W
Thermal Resistance Junction-to-Ambient	$R_{\theta JA}$	96	°C/W
Storage Temperature Range	T_{STG}	-55 to 150	°C
Operating Junction Temperature Range	T_J	-55 to 150	°C


Electrical characteristics (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	VGS=0V , ID=-250μA	-20	-	-	V
Drain-Source Leakage Current	IDSS	VDS=-16V , VGS=0V	-	-	-1	uA
Gate-Source Leakage Current	IGSS	VGS=±10V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	VGS(th)	VDS=VGS , ID=-250μA	-0.4	-0.7	-1.1	V
Static Drain-Source On-Resistance	RDS(ON)	VGS=-4.5V, ID=-5A	-	18	26	mΩ
		VGS=-2.5V, ID=-4A	-	28	36	
Dynamic characteristics						
Input Capacitance	Ciss	VDS=-10V , VGS=0V , f=1MHz	-	1258	-	pF
Output Capacitance	Coss		-	191	-	
Reverse Transfer Capacitance	Crss		-	151	-	
Total Gate Charge	Qg	VDS=-10V , VGS=-4.5V , ID=-5A	-	32	-	nC
Gate-Source Charge	Qgs		-	3.6	-	
Gate-Drain Charge	Qgd		-	10	-	
Switching Characteristics						
Turn-On Delay Time	td(on)	VDD=-10V VGS=-4.5V , RG=10Ω, ID=-5A,	-	9	-	nS
Turn-On Rise Time	tr		-	35	-	
Turn-Off Delay Time	td(off)		-	30	-	
Turn-Off Fall Time	tr		-	11	-	
Source-Drain Diode characteristics						
Diode Forward Voltage	VSD	VGS=0V , IS=-1A , TJ=25℃	-	-	-1.2	V


Typical Characteristics




Output Characteristics




Transfer Characteristics




Capacitance Characteristics




Gate Charge




Current dissipation




Power dissipation




$R_{DS(on)}$ VS Drain Current




Forward characteristics of reverse diode




Normalized breakdown voltage




Normalized Threshold voltage



Maximum Transient Thermal Impedance



Safe Operation Area

SOT-23-3L Package Information


Symbol	Dimensions in millimeters	
	Min.	Max.
A	1.050	1.250
A1	0.000	0.100
A2	1.050	1.150
b	0.300	0.500
c	0.100	0.200
D	2.820	3.020
E	1.500	1.700
E1	2.650	2.950
e	0.950 Typ.	
e1	1.800	2.000
L	0.300	0.600
θ	0°	8°