

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
20V	60mΩ@4.5V	1.2A
	70mΩ@2.5V	



合肥矽普半导体

Siliup Semiconductor Technology Co., Ltd

技术 品质 服务

www.siliup.com

Feature

- High power and current handing capability
- Surface mount package

Application


- Battery Switch
- DC/DC Converter

Package




PDFN1006-3L

Circuit diagram



Marking



262

:Device Code

Order Information

Device	Package	Unit/Tape
SP2620NC	PDFN1006-3L	10000


Absolute maximum ratings (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	20	V
Gate-Source Voltage	V_{GS}	± 12	V
Continuous Drain Current	I_D	1.2	A
Pulse Drain Current Tested	I_{DM}	4.8	A
Power Dissipation	P_D	150	mW
Thermal Resistance Junction-to-Ambient	$R_{\theta JA}$	833	°C/W
Storage Temperature Range	T_{STG}	-55 to 150	°C
Operating Junction Temperature Range	T_J	-55 to 150	°C


Electrical characteristics (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	VGS=0V , ID=250μA	20	-	-	V
Drain-Source Leakage Current	IDSS	VDS=13V , VGS=0V	-	-	1	uA
Gate-Source Leakage Current	IGSS	VGS=±20V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	VGS(th)	VDS=VGS , ID=250μA	0.4	0.65	1	V
Static Drain-Source On-Resistance	RDS(ON)	VGS=4.5V, ID =1A	-	60	90	mΩ
		VGS=2.5V, ID =0.5A	-	70	110	
Dynamic characteristics						
Input Capacitance	Ciss	VDS=10V , VGS=0V , f=1MHz	-	226	-	pF
Output Capacitance	Coss		-	35	-	
Reverse Transfer Capacitance	Crss		-	21	-	
Total Gate Charge	Qg	VDS=10V , VGS=4.5V , ID=1.2A	-	4.0	-	nC
Gate-Source Charge	Qgs		-	0.85	-	
Gate-Drain Charge	Qgd		-	0.67	-	
Switching Characteristics						
Turn-On Delay Time	td(on)	VDD=10V VGS=4.5V , RG=6Ω , ID=1.2A	-	7	-	nS
Turn-On Rise Time	tr		-	55	-	
Turn-Off Delay Time	td(off)		-	14	-	
Turn-Off Fall Time	tf		-	43	-	
Source-Drain Diode characteristics						
Diode Forward Voltage	VSD	VGS=0V , IS=1A , TJ=25℃	-	-	1.2	V


Typical Characteristics




Output Characteristics




Transfer Characteristics




Capacitance Characteristics




Gate Charge




Current dissipation




Power dissipation




$R_{DS(on)}$ VS Drain Current




Forward characteristics of reverse diode




Normalized breakdown voltage



Normalized Threshold voltage




Maximum Transient Thermal Impedance



Safe Operation Area

PDFN1006-3L Package Information



Symbol	Dimensions in millimeters	
	Min.	Max.
A	0.46	0.51
A1	0	0.05
b	0.45	0.55
b1	0.1	0.2
c	0.08	0.18
D	0.95	1.05
D1	0.65	
E	0.55	0.65
E1	0.325	
L	0.2	0.3
L1	0.2	0.3