

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
-30V	6m Ω @-10V	-55A
	9m Ω @-4.5V	



合肥矽普半导体

Siliup Semiconductor Technology Co., Ltd

技术 品质 服务

www.siliup.com


Feature

- Fast switching speed
- Surface mount package
- ROHS Compliant & Halogen-Free
- 100% Single Pulse avalanche energy Test

Applications


- DC-DC Converters.
- Motor Control.

Package




PDFN5X6-8L

Circuit diagram



Marking



30P06
*

:Device Code
:Month Code

Order Information

Device	Package	Unit/Tape
SP30P06NK	PDFN5X6-8L	5000

Absolute maximum ratings (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Rating	Unit
Drain-Source Voltage	V_{DS}	-30	V
Gate-Source Voltage	V_{GS}	± 20	V
Continuous Drain Current (Tc=25°C)	I_D	-55	A
Continuous Drain Current (Tc=100°C)	I_D	-36	A
Pulse Drain Current Tested	I_{DM}	-220	A
Single pulsed avalanche energy ¹	E_{AS}	130	mJ
Power Dissipation (Tc=25°C)	P_D	45	W
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	2.8	°C/W
Storage Temperature Range	T_{STG}	-55 to 150	°C
Operating Junction Temperature Range	T_J	-55 to 150	°C


Electrical characteristics (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	VGS=0V , ID=-250uA	-30	-	-	V
Drain-Source Leakage Current	IDSS	VDS=-24V , VGS=0V , TJ=25℃	-	-	-1	uA
Gate-Source Leakage Current	IGSS	VGS=±20V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	VGS(th)	VGS=VDS , ID =-250uA	-1.0	-1.5	-2.5	V
Static Drain-Source On-Resistance	RDS(on)	VGS =-10V, ID =-15A	-	6	8	mΩ
		VGS =-4.5V, ID =-10A	-	9	13	
Dynamic characteristics						
Input Capacitance	Ciss	VDS=-15V , VGS=0V , f=1MHz	-	3456	-	pF
Output Capacitance	Coss		-	387	-	
Reverse Transfer Capacitance	Crss		-	335	-	
Total Gate Charge	Qg	VDS=-15V , VGS=-10V , ID=-20A	-	62	-	nC
Gate-Source Charge	Qgs		-	12	-	
Gate-Drain Charge	Qgd		-	14	-	
Switching Characteristics						
Turn-On Delay Time	Td(on)	VDD=-15V ,VGS=-10V , RG=3Ω, ID=-20A	-	15	-	nS
Rise Time	Tr		-	61	-	
Turn-Off Delay Time	Td(off)		-	54	-	
Fall Time	Tf		-	65	-	
Diode Characteristics						
Diode Forward Voltage	VSD	VGS=0V , IS=-1A , TJ=25℃	-	-	1.2	V
Maximum Body-Diode Continuous Current	IS		-	-	-55	A
Reverse recover time	Trr	IS=-20A, di/dt=100A/us, TJ=25℃	-	25	-	nS
Reverse recovery charge	Qrr		-	12	-	nC


Note:

- The EAS Test condition is $V_{DD}=-15V, V_{GS}=-10V, L=0.1mH, R_g=25\Omega$


Typical Characteristics




Output Characteristics




Transfer Characteristics




Capacitance Characteristics




Gate Charge




Current dissipation




Power dissipation




$R_{DS(on)}$ VS Drain Current




Forward characteristics of reverse diode




Normalized breakdown voltage



Normalized Threshold voltage




Maximum Transient Thermal Impedance




Safe Operation Area


PDFN5X6-8L Package Information



Top View
[顶视图]



Bottom View
[背视图]



Side View
[侧视图]

Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.900	1.000	0.035	0.039
A3	0.254REF.		0.010REF.	
D	4.944	5.096	0.195	0.201
E	5.974	6.126	0.235	0.241
D1	3.910	4.110	0.154	0.162
E1	3.375	3.575	0.133	0.141
D2	4.824	4.976	0.190	0.196
E2	5.674	5.826	0.223	0.229
k	1.190	1.390	0.047	0.055
b	0.350	0.450	0.014	0.018
e	1.270TYP.		0.050TYP.	
L	0.559	0.711	0.022	0.028
L1	0.424	0.576	0.017	0.023
H	0.574	0.726	0.023	0.029
θ	10°	12°	10°	12°