

174193-1

✓ ACTIVE

AMPLIMITE | AMPLIMITE Kit

TE Internal #: 174193-1

Cable Clamp Kit, Zinc, 3 Shell Size, Shielded, 25 Position,

AMPLIMITE Kit

[View on TE.com >](#)

Connectors > Connector Accessories > Connector Strain Relief

Strain Relief Accessory Type: **Cable Clamp Kit**Primary Product Material: **Zinc**Compatible With Connector Shell Size: **3**Shielded: **Yes**Number of Positions: **25****Features****Product Type Features**

Strain Relief Accessory Type	Cable Clamp Kit
Sealable	No

Configuration Features

Number of Positions	25
---------------------	----

Body Features

Primary Product Plating Material	Nickel over Copper
Cable Exit Angle	180°
Primary Product Material	Zinc

Mechanical Attachment

Thread Size	4-40
-------------	------

Housing Features

Compatible With Connector Shape	D-Shaped
Body Orientation	Straight

Dimensions

Compatible Insulation Diameter Range	13.5 mm [.531 in]
--------------------------------------	-------------------

Operation/Application

Compatible With Connector Shell Size	3
Shielded	Yes

Packaging Features

Packaging Method	Bag
Packaging Quantity	1

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUN 2012 (84) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability





Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.


Compatible Parts



Also in the Series | AMPLIMITE Kit



Customers Also Bought



Documents

Product Drawings

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_174193-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_174193-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_174193-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English