




TOP VIEW




FRONT VIEW




RECOMMENDED PANEL CUTOUT



SIDE VIEW




RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)




DETAIL 'A'
(ENLARGED)


SMT LED SOLDER PAD
(SMT LED TO BE PROVIDED
BY THE CUSTOMER)



LIGHT PIPE



FINISH CONNECTOR



MATERIALS:

PLASTIC HOUSING: HIGH TEMPERATURE ENGINEERING THERMOPLASTIC
FLAMMABILITY RATING UL 94V-0

CONTACTS:

PHOSPHOR BRONZE

PLATING: 20 μ " [0.51 MICRONS]
MIN. GOLD ON MATING SURFACES.
50 μ " [1.27 MICRONS]
MIN. NICKEL UNDERPLATE.
100 μ " [2.54 MICRONS]
MIN. MATTE TIN ON CONTACT TAILS.

SHIELD:

COPPER ALLOY
PLATING: NICKEL

LIGHT PIPE:

CLEAR POLYCARBONATE
FLAMMABILITY RATING UL 94V-0

PART NUMBER: RJSS-5S81

SHELL OPTION _____
S - SPECIAL SOLDER
TAIL OF SHEEL

MATERIAL	DRAWN	MT Chen	DATE	Oct 29, 09	Amphenol Canada Corp.		
	DESIGNED						
	CHECKED	L.CHAN		Oct 29, 09			
	I. E. APPRD.						
FINISH	Q. A. APPRD.				TITLE		
	DWG. APPRD.						
	ENG. REL. NO.						
	REF. EAR 13608						
	DIMENSIONS ARE IN	INCHES	CODE ID. NO.	03554	DWG	DRAWING NO.	REV.
				SCALE	2:1	WT.	
				SURF.			
				SHEET	1	OF	1

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION
MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING
PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.