

Data Sheet | Item Number: 216-244


Ferrule; Sleeve for 1.5 mm² / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black

<https://www.wago.com/216-244>



Color: ■ black

Similar to illustration



Dimensions in mm

Connection data

Cross-section metric	1.5 mm ²
Strip length	12 ... 13 mm / 0.47 ... 0.51 inches
Cross-section AWG	16 AWG

Physical data

Wall thickness plastic collar	0.25 mm
Total length	16 mm
Wall thickness crimp sleeve	0.15 mm
Crimp length (length of sleeve)	10 mm
Inner Diameter plastic collar	3.5 mm
Diameter crimp sleeve inside	1.7 mm

Mechanical data

Plastic collar	Standard collar
Suitable	2001 – 2002 Series

Material data

Color	black
Fire load	0.002 MJ
Weight	0.1 g

Commercial data

Product Group	2 (Terminal Block Accessories)
eCl@ss 10.0	27-40-02-01
eCl@ss 9.0	27-40-02-01
ETIM 9.0	EC000005
ETIM 8.0	EC000005
PU (SPU)	1000 pcs
Packaging type	Box
Country of origin	DE
GTIN	4044918016346
Customs tariff number	85369010000



Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption


Downloads

Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 216-244	

Documentation

Bid Text			
216-244	19.02.2019	xml 2.80 KB	
216-244	11.09.2017	doc 23.50 KB	

Installation Notes



A perfect gas-tight crimp – both electrical-ly and mechanically reliable