



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.75 – 2.5 mm²**

Mating Tab Width: **4.75 mm [.187 in]**

Mating Tab Thickness: **.51 mm [.02 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Product Length	14.99 mm[.6 in]
Compatible Insulation Diameter Range	2.79 – 4.06 mm[.11 – .16 in]
Terminal Material Thickness	.3 mm[.012 in]
Wire Size	.75 – 2.5 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
---	---------

Packaging Features

Packaging Quantity	20000
Packaging Method	Strip/Reel

Other

Line	Premier
------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




KIT

REPRESENTATION ONLY

TE Part # 7-2150420-7
[OCEAN_2.0_SPARE_PART_KIT-090F180F](#)



TE Part # 42197-2
[205 FASTON REC 22-18 AWG TPBR](#)



TE Part # 2150420-1
[OCEAN_2.0_APPLICATOR-E-090F180F-REM](#)



TE Part # 2150420-2
[OCEAN_2.0_APPLICATOR-E-090F180F-REA](#)



TE Part # 180436-2
[110 FASTON,REC.,26-18 AWG,TPBR](#)



TE Part # 60674-1
[205 FASTON REC 26-22 AWG TPBR](#)

Also in the Series | **FASTON 187**



[Crimp Terminal Housings\(40\)](#)



[Insertion & Extraction Tools\(1\)](#)



[Insulation Boots & Sleeves\(1\)](#)



[Joints & Splices\(1\)](#)



PCB Terminals(42)



Quick Disconnects(207)




Splices(1)

Customers Also Bought




TE Part #179317-4
HYBRID MINI DRAWER REC CONT.#2



TE Part #174712-1
PL 187 (4.8 MM) HOUSING
RECEPTACLE



TE Part #2029076-2
2P MICRO MNL 1R RA HDR ASY NAT




TE Part #3-292246-4
1.5 MINI CT LATTICE REC KEY B



TE Part #1-353293-3
MINI CT MT REC ASSY 13P GRAY




TE Part #3-2213627-2
ASSEMBLY, ROT DIM REC 49.22MM 7
POS 150C



TE Part #CAT-C339-T419
Power Resistor: Aluminum Housed, 75
Watt



TE Part #292171-8
CT POST HDR ASSY 8P IN-TUBE BL



TE Part #8-292155-5
SGL HDR PANEL MOUNT ASSY

Documents

Product Drawings

187 FASTON,REC.,18-14 AWG,TPBR

English

CAD Files

Customer View Model

ENG_CVM_CVM_1217149-1_E.2d_dxf.zip

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_1217149-1_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1217149-1_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[82004 FASTON Terminals \(Insulated and Uninsulated\) Catalog - FASTON Receptacles Section](#)

English

Product Specifications

[Wire Preparation And Crimp Inspection Guide](#)

English

[.110,.187 & 250 Series FASTON Terminals](#)

English

[Product Specification](#)

English

Agency Approvals

[UL Report](#)

English