Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
-100V	40mΩ@-10V	-32A
	48mΩ@-4.5V	

合肥矽普半导体
Siliup Semiconductor Technology Co.Ltd
技术 品质 服务
www.siliup.com

Feature

- Fast Switching
- Low Gate Charge and Rdson
- 100% Single Pulse avalanche energy Test

Applications

- DC-DC Converter
- Load Switching

Package



TO-252(1:G 2:D 3:S)

Circuit diagram



Marking



010P40 :Device Code
**** :Week Code

Order Information

Device	Package	Unit/Tape
SP010P40TH	TO-252	2500

Absolute maximum ratings (Ta=25℃,unless otherwise noted)

Parameter	Symbol	Rating	Units
Drain-Source Voltage	V_{DS}	-100	V
Gate-Source Voltage	V_{GS}	±20	V
Continuous Drain Current (T_C=25℃)	I_D	-32	A
Continuous Drain Current (T_C=100℃)	I_D	-21	A
Pulsed Drain Current	I_{DM}	-128	A
Single Pulse Avalanche Energy[1]	E_{AS}	272	mJ
Power Dissipation (T_C=25℃)	P_D	86	W
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	1.5	℃/W
Storage Temperature Range	T_{STG}	-55 to 150	℃
Operating Junction Temperature Range	T_J	-55 to 150	℃

Electrical characteristics (Ta=25℃, unless otherwise noted)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV_{DSS}	VGS=0V , ID=-250uA	-100	-	-	V
Drain-Source Leakage Current	I_{DSS}	VDS=-80V , VGS=0V , TJ=25℃	-	-	-1	uA
Gate-Source Leakage Current	I_{GSS}	VGS=±20V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	$V_{GS(th)}$	VGS=VDS , ID =-250uA	-1.0	-1.8	-2.5	V
Static Drain-Source On-Resistance	$R_{DS(ON)}$	VGS=-10V , ID=-15A	-	40	50	mΩ
		VGS=-4.5V , ID=-15A	-	48	64	
Dynamic characteristics						
Input Capacitance	C_{iss}	VDS=-50V , VGS=0V , f=1MHz	-	5414	-	pF
Output Capacitance	C_{oss}		-	177	-	
Reverse Transfer Capacitance	C_{rss}		-	89	-	
Total Gate Charge	Q_g	VDS=-50V , VGS=-10V , ID=-15A	-	96	-	nC
Gate-Source Charge	Q_{gs}		-	24	-	
Gate-Drain Charge	Q_{gd}		-	10	-	
Switching Characteristics						
Turn-On Delay Time	$T_{d(on)}$	VDD=-50V,VGS=-10V,RG=3Ω, ID=-15A	-	8	-	nS
Rise Time	T_r		-	38	-	
Turn-Off Delay Time	$T_{d(off)}$		-	94	-	
Fall Time	T_f		-	226	-	
Diode Characteristics						
Diode Forward Voltage	V_{SD}	VGS=0V , IS=-1A , TJ=25℃	-	-	1.2	V
Maximum Body-Diode Continuous Current	I_S		-	-	-32	A
Reverse Recovery Time	T_{rr}	IS=-15A, di/dt=100A/us, TJ=25℃	-	36	-	nS
Reverse Recovery Charge	Q_{rr}		-	43	-	nC

Note :

1. The EAS test condition is VDD=-50V,VGS=-10V,L=0.5mH,RG=25Ω

Typical Characteristics



Output Characteristics



Transfer Characteristics



Capacitance Characteristics



Gate Charge



Current dissipation



Power dissipation



RDS(on) VS Drain Current



Forward characteristics of reverse diode



Normalized breakdown voltage



Normalized Threshold voltage



Maximum Transient Thermal Impedance



Safe Operation Area

TO-252 Package Information



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	2.200	2.400	0.087	0.094
A1	0.000	0.127	0.000	0.005
b	0.660	0.860	0.026	0.034
c	0.460	0.580	0.018	0.023
D	6.500	6.700	0.256	0.264
D1	5.100	5.460	0.201	0.215
D2	4.830 REF.		0.190 REF.	
E	6.000	6.200	0.236	0.244
e	2.186	2.386	0.086	0.094
L	9.800	10.400	0.386	0.409
L1	2.900 REF.		0.114 REF.	
L2	1.400	1.700	0.055	0.067
L3	1.600 REF.		0.063 REF.	
L4	0.600	1.000	0.024	0.039
Φ	1.100	1.300	0.043	0.051
θ	0°	8°	0°	8°
h	0.000	0.300	0.000	0.012
V	5.350 REF.		0.211 REF.	