




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.82 – 2.08 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Piggyback
Contact Base Material	Brass
Terminal Plating Material	Unplated
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Product Length	19.56 mm[.77 in]
Compatible Insulation Diameter Range	3.1 – 4.3 mm[.12 – .17 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	.82 – 2.08 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
---	---------

Packaging Features

Packaging Quantity	2500
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2266067-1
OCEAN_2.0_Applicator-S-110F180F-RSM

TE Part # 1-280079-2
250 FASTON,REC.,14-17AWG,TPBR

TE Part # 720725-1
DAHT 250 FASTIN-ON TAB REC 18-14 ASSY

TE Part # 2305570-1
Strip Terminal Cutter-Side Feed-No Crimp

TE Part # 2266067-2
OCEAN_2.0_Applicator-S-110F180F-RSA

TE Part # 7-2266067-7
OCEAN_2.0_SPARE_PART_KIT-110F180F


Also in the Series | FASTON 250

Compression Connectors(4)

Crimp Terminal Housings(118)

Insertion & Extraction Tools(6)

Insulation Boots & Sleeves(16)



Magnet Wire Terminals(1)



PCB Terminals(133)




Quick Disconnects(425)




Splices(4)

Customers Also Bought




TE Part #480053-3
FF 250 TAB HSG 1P NYLON NAT




TE Part #53245-2
TERMINAL,PG SPR SPD 16-14 10




TE Part #42801-2
187 FASTON REC 20-16 AWG TPBR




TE Part #61300-1
SPLICE IS 10000-16000 .031 TPST




TE Part #1586019-2
2P RCPT VAL-U-LOK V0



TE Part #1-1586019-4
14P RCPT VAL-U-LOK V0



TE Part #3-520402-2
ULTRA-FAST 187 ASY REC 16-14 AWG TPBR



TE Part #1217043-1
250 FASTON,REC.,14-10 AWG,TPBR



TE Part #42660-2
250 FASTON REC 18-14 AWG TPBR



TE Part #6609059-2
3EZ1=F7328 S0

Documents

Product Drawings

250 FASTON REC 18-14 AWG BR

English

CAD Files

Customer View Model

ENG_CVM_CVM_62109-1_AL.2d_dxf.zip

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_62109-1_AL.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_62109-1_AL.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[82004 FASTON Terminals \(Insulated and Uninsulated\) Catalog - FASTON Receptacles Section](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English