



#### General ordering data

Order No.	9512110000
Part designation	PCF 10.00/4/135 3.5 OR
Version	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 10.00 mm, No. of poles: 4, 135°, Box
EAN	4008190558260
Qty.	100 pc(s).

#### System parameters

Product family	System PCF
Conductor connection system	Flat-blade connection
Fitted to PCB	Soldered connection
Outgoing direction of conductor	135°
Pitch	10 mm
Pitch in inch	0.394 inch
No. of poles	4
Fitted by customer	no
No. of rows	1
Solder pin length	3.5 mm
Dia. of fitting hole	1.3 mm
Fitting hole tolerance	+ 0.1 mm
No. of solder pins per pole	2
L1 in mm	30 mm

**System parameters**

L1 in inch	1.181 inch
Electric shock protection to DIN VDE 0470	IP 00

**Material data**

Insulating material	PA
Colour	orange
colour chart	Similar to RAL 2000
Insulating material group	I
Flammability class UL 94	V-2
CTI	$\geq 600$
Contact base material	CuSn
Contact surface	tinned
Storage temperature, min.	-25 °C
Storage temperature, max.	55 °C

**DIN IEC rating data**

Rated current, min. No. pins (Tu=20°C)	24 A
Rated current, max. No. pins (Tu=20°C)	26 A
Rated current, min. No. pins (Tu=40°C)	24 A
Rated current, max. No. pins (Tu=40°C)	22 A
Rated voltage for overvoltage class/pollution severity II/2	1,000 V
Rated voltage for overvoltage class/pollution severity III/2	690 V
Rated voltage for overvoltage class/pollution severity III/3	690 V
Rated impulse withstand voltage for overvoltage class/pollution severity II/2	6 kV
Rated impulse withstand voltage for overvoltage class/pollution severity III/2	6 kV
Rated impulse withstand voltage for overvoltage class/pollution severity III/3	6 kV
Short-time withstand current resistance	3 x 1s mit 192 A

**CSA rating data**

Rated current (Use group C)	15 A
Rated voltage (Use group C)	300 V
Rated voltage (Use group D)	300 V
Rated current (Use group D)	10 A

**UL 1059 rating data**

Rated voltage (Use group C)	300 V
Rated current (Use group C)	15 A
Rated voltage (Use group D)	300 V
Rated current (Use group D)	10 A

**Approvals**

Approvals institutes

**Classifications**

ETIM 2.0	NK
ETIM 3.0	EC001284
eClass 4.1	NK
eClass 5.0	NK
eClass 5.1	NK

**Similar products**

Order No.	Part designation	Version
9512090000	PCF 10.00/2/135 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 10.00 mm, No. of poles: 2, 135°, Box
9512100000	PCF 10.00/3/135 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 10.00 mm, No. of poles: 3, 135°, Box
9512120000	PCF 10.00/5/135 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 10.00 mm, No. of poles: 5, 135°, Box
9512130000	PCF 10.00/6/135 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 10.00 mm, No. of poles: 6, 135°, Box
9512140000	PCF 10.00/7/135 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 10.00 mm, No. of poles: 7, 135°, Box
9512150000	PCF 10.00/8/135 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 10.00 mm, No. of poles: 8, 135°, Box
9512160000	PCF 10.00/9/135 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 10.00 mm, No. of poles: 9, 135°, Box
9512170000	PCF 10.00/10/135 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 10.00 mm, No. of poles: 10, 135°, Box