

Accessories
VGM25-MS68 11-20 BG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



With blueglobe®, Weidmüller has introduced a cable gland from Pflitsch into its portfolio that convinces both in terms of reliability and functionality.

A large sealing range from 1.5 to 77 mm thanks to removable inlets with just 11 cable glands, highly effective sealing, excellent strain relief and a groove-guided upstream O-ring – these are the features of the blueglobe® cable glands which Weidmüller offers in brass and stainless steel.

The heart of the blueglobe® cable gland is the spherical seal insert that squeezes the cable gently and over a large area. This permanently avoids the incisive notch effect that is common with lamella systems.

General ordering data

Type	VGM25-MS68 11-20 BG
Order No.	1193600000
Version	Heavy-duty connectors, Accessories, Cable glands, Brass, nickel-plated
GTIN (EAN)	4032248976560
Qty.	50 pc(s).

Accessories

VGM25-MS68 11-20 BG

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	36.5 mm	Length (inches)	1.437 inch
Net weight	70 g		

Temperatures

Limit temperature	-40 °C ... 130 °C
-------------------	-------------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General data

AF size	30 mm	Cable diameter, max.	20 mm
Cable diameter, min.	11 mm	Cable glands	M 25
External thread	M 25	Length of thread	7.5 mm
Material	Brass, nickel-plated	O-Ring	NBR
Protection degree	IP68	Sealing material	T80s
Tightening torque, max.	15 Nm	Type of sealing	Rubber ring

Classifications

ETIM 5.0	EC002625	ETIM 6.0	EC000441
eClass 6.2	27-18-92-34	eClass 7.1	27-18-92-34
eClass 8.1	27-18-92-34	eClass 9.0	27-14-44-32
eClass 9.1	27-14-44-32		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN FL FIELDWIRING EN
Engineering Data	EPLAN
Engineering Data	STEP