



General ordering data

Order No.	9500790000
Part designation	PCF 10.00/180 3.5 OR
Version	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 10.00 mm, No. of poles: 6, 180°, Box
EAN	4008190191818
Qty.	50 pc(s).

System parameters

Product family	System PCF
Conductor connection system	Flat-blade connection
Fitted to PCB	Soldered connection
Outgoing direction of conductor	180°
Pitch	10 mm
Pitch in inch	0.394 inch
No. of poles	6
Fitted by customer	no
No. of rows	1
Solder pin length	3.5 mm
Dia. of fitting hole	1.3 mm
Fitting hole tolerance	+ 0.1 mm
No. of solder pins per pole	2
L1 in mm	50 mm
L1 in inch	1.969 inch
Electric shock protection to DIN VDE 0470	IP 00

Material data

Insulating material	PA
Colour	orange
colour chart	Similar to RAL 2000
Insulating material group	I
Flammability class UL 94	V-2
CTI	>= 600
Contact base material	CuSn

Material data

Contact surface	tinned
Storage temperature, min.	-25 °C
Storage temperature, max.	55 °C

DIN IEC rating data

Rated current, min. No. pins (Tu=20°C)	24 A
Rated current, max. No. pins (Tu=20°C)	26 A
Rated current, min. No. pins (Tu=40°C)	24 A
Rated current, max. No. pins (Tu=40°C)	22 A
Rated voltage for overvoltage class/pollution severity II/2	1,000 V
Rated voltage for overvoltage class/pollution severity III/2	690 V
Rated voltage for overvoltage class/pollution severity III/3	690 V
Rated impulse withstand voltage for overvoltage class/pollution severity II/2	6 kV
Rated impulse withstand voltage for overvoltage class/pollution severity III/2	6 kV
Rated impulse withstand voltage for overvoltage class/pollution severity III/3	6 kV
Short-time withstand current resistance	3 x 1s mit 192 A

CSA rating data

Rated current (Use group C)	15 A
Rated voltage (Use group C)	300 V
Rated voltage (Use group D)	300 V
Rated current (Use group D)	10 A

UL 1059 rating data

Rated voltage (Use group C)	300 V
Rated current (Use group C)	15 A
Rated voltage (Use group D)	300 V
Rated current (Use group D)	10 A

Approvals

Approvals institutes



Classifications

ETIM 2.0	NK
ETIM 3.0	EC001284
eClass 4.1	NK
eClass 5.0	NK
eClass 5.1	NK

Similar products

Order No.	Part designation	Version
9500750000	PCF 10.00/2/180 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 10.00 mm, No. of poles: 2, 180°, Box
9500760000	PCF 10.00/3/180 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 10.00 mm, No. of poles: 3, 180°, Box
9500770000	PCF 10.00/4/180 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 10.00 mm, No. of poles: 4, 180°, Box
9500780000	PCF 10.00/5/180 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 10.00 mm, No. of poles: 5, 180°, Box
9500810000	PCF 10.00/7/180 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 10.00 mm, No. of poles: 7, 180°, Box
9500820000	PCF 10.00/8/180 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 10.00 mm, No. of poles: 8, 180°, Box
9500830000	PCF 10.00/9/180 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 10.00 mm, No. of poles: 9, 180°, Box
9500840000	PCF 10.00/10/180 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 10.00 mm, No. of poles: 10, 180°, Box