



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Cluster Blocks



Number of Circuits: 3

Primary Product Material: PBT

Wire Size: .326 – 5.26 mm²

Operating Temperature Range: -20 – 120 °C [-4 – 248 °F]

Features

Product Type Features

Compatible With Discrete Wire Type	Lead Wire
------------------------------------	-----------

Configuration Features

Number of Circuits	3
--------------------	---

Body Features

Primary Product Color	Natural
Primary Product Material	PBT

Contact Features

Mating Pin Diameter	3.18 mm[.125 in]
---------------------	------------------

Mechanical Attachment

Mount Diameter	13.46 mm[.53 in]
Block Mounting Configuration	2 Forward - 1 Back

Dimensions

Product Length	47.23 mm[1.859 in]
Wire Size	.326 – 5.26 mm ²

Usage Conditions

--	--



Operating Temperature Range	-20 – 120 °C[-4 – 248 °F]
-----------------------------	---------------------------

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1217172-1
Cluster Block Rcpt Amplivar 400-1600




TE Part # 1217173-1
Cluster Block Rcpt Amplivar 4000-8500



TE Part # 316293-3
3.2 CLUSTER BLOCK HSG, LCP TYPE




TE Part # 1217671-1
CLSTR BLK RCPT AMVAR 1500-4200




TE Part # 63454-1
Cluster Block Recpt Amplivar 1500-4200




TE Part # 1217670-1
CLSTR BLK RCPT AMVAR 400-1600




TE Part # 1217176-1
CLUSTER BLOCK RECPT.




TE Part # 1742657-1
CLUSTER BLOCK RECP 22-18 020TP



TE Part # 62243-3
125 PIN RECEPTACLE 14-10




TE Part # 63453-1
Cluster Block Recpt Amplivar 400-1600




TE Part # 62244-3
125 PIN RCPT 18-16



TE Part # 360051-2
CLUSTER BLOCK



TE Part # 63455-1
Cluster Block Recpt Amplivar 4000-8500




TE Part # 1217672-1
CLSTR BLK RCPT AMVAR 4000-8500



TE Part # 62243-5
125 PIN RECEPTACLE 14-10




TE Part # 1217174-1
Cluster Block Recpt Amplivar 1500-4200




TE Part # 62244-6
125 PIN RECEPTACLE 18-16



TE Part # 2825316-1
CLUSTER BLOCK HOUSING GWT




TE Part # 1217175-1
CLUSTER BLOCK RECPT.




TE Part # 1217176-5
CLUSTER BLK RECP,18-16 020PHBR

Customers Also Bought



TE Part #62308-2
AMVAR SPLC 3000-7000 020TPBR



TE Part #63453-1
Cluster Block Recpt Amplivar 400-1600




TE Part #1-926475-2
MOD 4 HSG



TE Part #1217175-1
CLUSTER BLOCK RECPT.





TE Part #63455-1

Cluster Block Recpt Amplivar 4000-8500



TE Part #1742981-1

2.29 DIA CLUST PIN AMPLVR REC 400-1600




TE Part #2381807-2

TRI-SLOT MAG-MATE, SLIM LINE



TE Part #4-1630012-0

HSC150 200R 5%



TE Part #63454-1

Cluster Block Recpt Amplivar 1500-4200



TE Part #60274-5

250 FASTON FLAG REC 18-12 AWG TPBR

Documents

Product Drawings

CLUSTER BLOCK HOUSING

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1217200-1_L_c-1217200-1-l.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1217200-1_L_c-1217200-1-l.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1217200-1_L_c-1217200-1-l.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Magnet Wire Terminals & Splices

English

Product Specifications

Engineering Report

English

Agency Approvals

UL Report

1217200-1

3 Circuit Cluster Block, PBT, 22 – 10 AWG, .326 – 5.26 mm² Wire, -20 – 120 °C [-4 – 248 °F]



English