

T1270165129-000 ✓ ACTIVE

HDC | HDC IP68 EMC

TE Internal #: T1270165129-000

Heavy Duty Connector Hood, Side Entry, Locking, Sealable, HDC
IP68 EMC

[View on TE.com >](#)



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Hood**

Cable Entry Location: **Side**

Hood & Base Locking Device Type: **Locking**

Sealable: **Yes**

Features

Product Type Features

Hood & Base Connector Product Type	Hood
Sealable	Yes

Body Features

Cable Entry Location	Side
----------------------	------

Mechanical Attachment

Thread Size	PG29
Locking Device Location	Hood
Hood & Base Locking Device Type	Locking

Housing Features

Housing Material	Die Cast Aluminum
------------------	-------------------

Dimensions

Product Width	43 mm
Product Length	93.5 mm
Product Height	76 mm

Usage Conditions

Corrosion Protected	Yes
---------------------	-----

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



Also in the Series | [HDC IP68 EMC](#)



Connector Caps & Covers(4)



Rectangular Connector Hoods & Bases (444)

Customers Also Bought

TE Part #640250-1
01P SL156 HSG W/LCK RAMP NATLTE Part #T2120100219-000
ZGG-10DSTK,1-7,2-8,3-9,4-6,5-10TE Part #1SNA195638R2300
M4/6.4A.PTE Part #T2106062201-000
HWK6/6-012-FTE Part #T2120100220-000
ZGGP-H10BSK 1-7/2-8/3-9/4-6/5-10TE Part #T0931003003-000
CODING-PIN-M3TE Part #T1730060000-000
H6B-TBF-TTE Part #1-480711-9
15P UMNL CAP HSG BLKTE Part #T2020082201-000
HD-008-FTE Part #1473203-1
025 CAP ASSY 16P P/BACK BRCKT

Documents

Product Drawings

[H16B-TSBHS-EMC-PG29](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_T1270165129-000_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T1270165129-000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T1270165129-000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[HEAVY DUTY CONNECTORS](#)

English

[HEAVY DUTY CONNECTORS](#)

Japanese

Product Specifications

[Application Specification](#)

English