



#### General ordering data

Order No.	9500680000
Part designation	PCF 7.50/8/180 3.5 OR
Version	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 7.50 mm, No. of poles: 8, 180°, Box
EAN	4008190191719
Qty.	50 pc(s).

#### System parameters

Product family	System PCF
Conductor connection system	Flat-blade connection
Fitted to PCB	Soldered connection
Outgoing direction of conductor	180°
Pitch	7.5 mm
Pitch in inch	0.295 inch
No. of poles	8
Fitted by customer	no
No. of rows	1
Solder pin length	3.5 mm
Dia. of fitting hole	1.3 mm
Fitting hole tolerance	+ 0.1 mm
No. of solder pins per pole	2
L1 in mm	52.5 mm

**System parameters**

L1 in inch	2.067 inch
Electric shock protection to DIN VDE 0470	IP 00

**Material data**

Insulating material	PA
Colour	orange
colour chart	Similar to RAL 2000
Insulating material group	I
Flammability class UL 94	V-2
CTI	>= 600
Contact base material	CuSn
Contact surface	tinned
Storage temperature, min.	-20 °C
Storage temperature, max.	55 °C

**DIN IEC rating data**

Rated current, min. No. pins (Tu=20°C)	24 A
Rated current, max. No. pins (Tu=20°C)	26 A
Rated current, min. No. pins (Tu=40°C)	24 A
Rated current, max. No. pins (Tu=40°C)	23 A
Rated voltage for overvoltage class/pollution severity II/2	1,000 V
Rated voltage for overvoltage class/pollution severity III/2	690 V
Rated voltage for overvoltage class/pollution severity III/3	500 V
Rated impulse withstand voltage for overvoltage class/pollution severity II/2	6 kV
Rated impulse withstand voltage for overvoltage class/pollution severity III/2	6 kV
Rated impulse withstand voltage for overvoltage class/pollution severity III/3	6 kV
Short-time withstand current resistance	3 x 1s mit 192 A

**CSA rating data**

Rated current (Use group C)	15 A
Rated voltage (Use group C)	150 V
Rated voltage (Use group D)	300 V
Rated current (Use group D)	10 A

**UL 1059 rating data**

Rated voltage (Use group C)	150 V
Rated current (Use group C)	15 A
Rated voltage (Use group D)	300 V
Rated current (Use group D)	10 A

**Approvals**

Approvals institutes

**Downloads**

CAD Library (P-CAD Format - Standard)

PCF.LIB

**Classifications**

ETIM 2.0	NK
ETIM 3.0	EC001284
eClass 4.1	NK
eClass 5.0	NK
eClass 5.1	NK

**Similar products**

Order No.	Part designation	Version
9500620000	PCF 7.50/2/180 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 7.50 mm, No. of poles: 2, 180°, Box
9500640000	PCF 7.50/4/180 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 7.50 mm, No. of poles: 4, 180°, Box
9500630000	PCF 7.50/3/180 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 7.50 mm, No. of poles: 3, 180°, Box
9500650000	PCF 7.50/5/180 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 7.50 mm, No. of poles: 5, 180°, Box
9500660000	PCF 7.50/6/180 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 7.50 mm, No. of poles: 6, 180°, Box
9500670000	PCF 7.50/7/180 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 7.50 mm, No. of poles: 7, 180°, Box
9500690000	PCF 7.50/9/180 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 7.50 mm, No. of poles: 9, 180°, Box
9500710000	PCF 7.50/10/180 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 7.50 mm, No. of poles: 10, 180°, Box
9500720000	PCF 7.50/11/180 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 7.50 mm, No. of poles: 11, 180°, Box
9500730000	PCF 7.50/12/180 3.5 OR	PCB terminal, Flat-blade connection, Soldered connection, Pitch: 7.50 mm, No. of poles: 12, 180°, Box

9500740000 PCF 7.50/13/180 3.5 OR

PCB terminal, Flat-blade connection, Soldered connection, Pitch: 7.50 mm, No. of poles: 13, 180°, Box