



深圳市首韩科技有限公司

SHENZHEN SHOUHAN TECHNOLOGY CO., LTD

Tel: 0755-27597601 Fax: 0755-27597491

承 认 书

SPECIFICATION FOR APPROVAL

产 品 编 码

Material code:

05759

产品名称 Project:

针座

规格型号 Part No:

2.0-2P LT

贵公司承认印 Approval signatures

料 号/Part No.	签 章/Signatures

日期 Date:

拟制/Drawn	李春风	
审核/Check	钟华华	
批准/Approved	罗孝金	

1、SCOPE: (适用范围)

- 1.1 This specification covers production and inspection of Connector.
本规范内容适用于本公司普通系列型条形连接器（针座）产品的生产与检验.

2、USE CONDITION: (使用条件)

2.1 Ambient temperature Range:-25℃~+85℃

环境温度: -25℃~+85℃

2.2 Applicable Wire Sizes:AWG#28~#32

适用线规: AWG#28~#32

2.3 Applicable PC board thickness:0.6~1.2mm

适用 PC 板厚度: 0.6~1.2 mm

3、Appearance and Dimension: (外观及尺寸)

3.1 Appearance:Product surface without defect、dirt、crack、and mechanical damang, Contact without rust,plating not oxidized and not peeled.

产品表面不应有对制品有害的缺陷、污垢、裂痕及机械损伤; 接触件无锈蚀、镀层氧化、脱落等现象.

3.2 Dimension:According to drawings

外形尺寸: 依照附图

3.3 Exchangable:Exchangable with same specification products.

互换性: 相同规格应能互换

4、Material:

材 料

P/N 零件名称	Type 类 型	Material 材 料	Finish 表面处理	Expiain 说 明
Terminal 端子	Contact 插 簧	Phosphor bronze 锡青磷铜 厚 0.15mm	Tin Plating:3~4 μ m 镀锡: 3~4 μ m	RoHS Comp liant
Housing 孔 座	Plastic 塑 壳	Nylon66 UL94V-0	Color:White 颜色: 白色	
Opening Wafer 开口针座	Contact 插 针	Phosphor bronze 锡青磷铜 厚 0.30mm	Tin Plating:3~4 μ m 镀锡: 3~4 μ m	
	Plastic 塑 壳	Nylon46 UL94V-0	Color: Beige 颜色: 米色	
Lips Wafer 闭口针座	Contact 插 针	Phosphor bronze 锡青磷铜 厚 0.30mm	Gold Plating:3~4 μ " m 镀金: 3~4 μ " m	
	Plastic 塑 壳	PBT UL94V-0	Color: White 颜色: 白色	
Tiepian Wafer 卧贴针座 立贴针座	Contact 插 针	Phosphor bronze 锡青磷铜 厚 0.30mm	Tin Plating:3~4 μ m 镀锡: 3~4 μ m	
	Solder tabs 焊护耳	Phosphor bronze 锡青磷铜 厚 0.25mm	Tin Plating:3~4 μ m 镀锡: 3~4 μ m	
	Plastic 塑 壳	Nylon46 UL94V-0	Color: Beige 颜色: 米色	

5、Electrical Performance:

电 气 性 能

N0. 序号	Ltem 项 目	Requirement 技术要求
5.1	Voltage Rated 额定电压	100V AC DC
5.2	Current Rated 额定电流	2A AC DC
5.3	Contact Resistance 接触电阻	$\leq 10 \text{ m}\Omega$
5.4	Insulation Resistance 绝缘电阻	$\geq 1000 \text{ M}\Omega$
5.5	Dielectric Strength 耐 压	$\geq 800\text{V AC/minute}$

6、Mechanical Performance:

机 械 性 能

N0. 序号	Ltem 项 目	Requirement 技术要求
6.1	Male contact Retention force PIN 针固定力	$\geq 15\text{N}$ per pin
6.2	Female contact Retention force 端子固定力	$\geq 15\text{N}$ per pin
6.3	Plug-in force 插入力	$\leq 3\text{N}$ per pin
6.4	Plug-out force 拔出力	$\geq 0.5\text{N}$ per pin

7、Endurance Characteristics:

环 境 性 能

N0. 序号	Ltem 项 目	Requirement 技术要求
7.1	Soldering rest 可焊性	Time: $2.5 \pm 0.5\text{S}$ 时间: $2.5 \pm 0.5\text{S}$ Temperature: $260 \pm 5^\circ\text{C}$ 温度: $260 \pm 5^\circ\text{C}$ Area of Soldering: $\geq 95\%$ 焊锡面积: $\geq 95\%$

7.2	Resistance to soldering Heat 耐焊接热	Time: $5 \pm 1\text{S}$ 时间: $5 \pm 1\text{S}$ Temperature: $260 \pm 5^\circ\text{C}$ 温度: $260 \pm 5^\circ\text{C}$ Appearance: NO Damage 外观: 无损坏
7.3	Heat test 耐热性	Time: 96h 时间: 96 小时 Temperature: $+85 \pm 3^\circ\text{C}$ 温度: $+85 \pm 3^\circ\text{C}$ Appearance: NO Damage 外观: 无损坏 Contact resistance: $\leq 20\text{ m}\Omega$ 接触电阻: $\leq 20\text{ m}\Omega$
7.4	Cold test 耐冷性	Time: 48h 时间: 48 小时 Temperature: $-25 \pm 3^\circ\text{C}$ 温度: $-25 \pm 3^\circ\text{C}$ Appearance: NO Damage 外观: 无损坏 Contact resistance: $\leq 20\text{ m}\Omega$ 接触电阻: $\leq 20\text{ m}\Omega$
7.5	Temperature Cycling 温度循环	Low temperature: $-25 \pm 3^\circ\text{C}$ 低温: $-25 \pm 3^\circ\text{C}$ High temperature: $-85 \pm 3^\circ\text{C}$ 高温: $-85 \pm 3^\circ\text{C}$ For 5 cycles. test after keeping in Normal Condition for 30 min. 5 次循环后, 放置在正常环境中 30 分钟, 在进行测试 Appearance: NO Damage 外观: 无损坏 Contact resistance: $\leq 20\text{ m}\Omega$ 接触电阻: $\leq 20\text{ m}\Omega$

7.6	Invariab lenes humidity 恒定湿热	Temperature: $60 \pm 2^{\circ}\text{C}$ 温度: $60 \pm 2^{\circ}\text{C}$ Relative humidity: 90%-96% RH 相对湿度: 90%-96% RH Tim: 96h 时间: 96 小时 Appearance: NO Damage 外观: 无损坏 Contact resistance: $\leq 20\text{ m}\Omega$ 接触电阻: $\leq 20\text{ m}\Omega$ Insulation Resistance: $\geq 100\text{ M}\Omega$ 绝缘电阻: $\geq 100\text{ M}\Omega$
7.7	Salt Spray 盐雾试验	Salt concentration: $5 \pm 1\%$ 浓度: $5 \pm 1\%$ Temperature: $35 \pm 2^{\circ}\text{C}$ 温度: $35 \pm 2^{\circ}\text{C}$ Tim: $16 \pm 2\text{ h}$ 时间: 16 ± 2 小时 After salt is removed by running wafer and A drop is removed ,it is measured. 把试验样品从试验箱顶悬挂下来,采用浓度 (5 ± 1) %的氯化钠溶液,连续雾化 16 小时,试验后用流动的蒸馏水轻轻洗去表面沉积物,在常温常驻湿条件下恢复 1-2 小时,外观无损伤 Appearance: NO Damage 外观: 无损坏 Contact resistance: $\leq 20\text{ m}\Omega$ 接触电阻: $\leq 20\text{ m}\Omega$

8、Packaging Transportation Storage

包装、运输、贮存

8.1 Packaging

包装

- (1) **The packing of plastic inner is the plastic bag,the packing of inner terminal is panel mounting attach material packing, marked with product name, specification model, quantity, date in produced.**

塑件内包装为塑料袋，端子内包装为盘装带料包装，装（贴）入合格证，注明产品名称、规格型号、数量生产日期

- (2) **Exterior package is carton, facing the packing list, the packing list marked with product name, specificcation model, quantity, date of dispatch.**

外包装为纸箱，贴装箱单、装箱单上注明产品名称、规格型号、数量、出货日期

- (3) **The product in the box must not rock.**

产品在箱内不晃动

8.2 Transportation

运输

Allow for any way transportation, can't get wet and mechanical in jury.


允许用任何方式运输，勿淋湿及机械性损伤

8.3 Storage

贮存

The connector of packing finished should be in the ambient temperature between-10℃ to+40℃, Relative humidity≤80%. To store in storehouse does not have acidic, alkaline air and other corrosive gas in the ambient air.

包装完毕的连接器应在环境温度为-10℃~+40℃，相对湿度≤80%，周围空气没有酸性，碱性及其它腐蚀性气体的库房中贮存



技术要求:

- 1) 材质:见附表;2
-) 电镀:见附表;
- 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;
- 4) 端子表面无氧化、电镀不良等现象。

适应基板厚度: 1.2mm~1.6mm
温度范围: -25℃~85℃
额定电压: 250V AC/DC
额定电流: 2A
绝缘电阻: 1000MΩ
耐压: 800VAC/minute

深圳市首韩科技有限公司

DRAW :		李春风	2020-05-20	TITLE:		针座		DRAW NAME:		2.0mm-2P LT	
DESIGN:				CHECK:		钟德华		SERIES:			
APPROVED				P/N:		罗孝金		DRAW NO.		UNIT:	
		CUSTOMER DRAWING		REV.	1.00	SCALE	N/A	SHEET:		1/1	

GENERAL TOLERANCES		
DIM	TOL	DIM DEG
X	X°	±3.0°
XX	±0.35	±2.0°
XXX	±0.25	±1.0°
XXXX	±0.15	±1.0°

NO.		NAME		Q'TY		DESCRIPTION	
4	Cap	1	PCS			材质:LCP (UL94V-0),颜色:本色或黑色	
3	FITTING NAIL	2	PCS			材质:黄铜,电镀:镀亮锡60u"MIN	
2	PTN	n	PCS			材质:黄铜,电镀:镀亮锡60u"MIN	
1	Housing	1	PCS			材质:LCP (UL94V-0),颜色:本色或黑色	

2.0立式贴片		DIMA (mm)		DIMB (mm)		DIMC (mm)	
2.0LT-2P	2.0mm	2.0mm	7.90mm				
2.0LT-3P	4.0mm	4.0mm	9.90mm				
2.0LT-4P	6.0mm	6.0mm	11.90mm				
2.0LT-5P	8.0mm	8.0mm	13.90mm				
2.0LT-6P	10.0mm	10.0mm	15.90mm				
2.0LT-7P	12.0mm	12.0mm	17.90mm				
2.0LT-8P	14.0mm	14.0mm	19.90mm				
2.0LT-9P	16.0mm	16.0mm	21.90mm				
2.0LT-10P	18.0mm	18.0mm	23.90mm				
2.0LT-11P	20.0mm	20.0mm	25.90mm				
2.0LT-12P	22.0mm	22.0mm	27.90mm				
2.0LT-13P	24.0mm	24.0mm	29.90mm				
2.0LT-14P	26.0mm	26.0mm	31.90mm				
2.0LT-15P	28.0mm	28.0mm	33.90mm				
2.0LT-16P	30.0mm	30.0mm	35.90mm				
2.0LT-17P	32.0mm	32.0mm	37.90mm				
2.0LT-18P	34.0mm	34.0mm	39.90mm				
2.0LT-19P	36.0mm	36.0mm	41.90mm				
2.0LT-20P	38.0mm	38.0mm	43.90mm				