

FCA-125-DY8

✓ ACTIVE

CII | CII FCA-125 Series

TE Internal #: 8-1617748-5

General Purpose Power Relay, AC, Polarized, Monostable, 1 Form C SPDT-CO, 25 A Contact Rating, 115 VAC Coil Voltage, Socket Mount, CII FCA-125 Series

[View on TE.com >](#)



Relays & Contactors > Electromechanical Relays



Relay & Contactor Type: **General Purpose Power Relay**

Current Type: **AC**

Coil Magnetic System: **Polarized, Monostable**

Contact Arrangement: **1 Form C SPDT-CO**

Contact Current Rating: **25 A**

Features

Product Type Features

Relay & Contactor Type	General Purpose Power Relay
------------------------	-----------------------------

Configuration Features

Contact Arrangement	1 Form C SPDT-CO
---------------------	------------------

Electrical Characteristics

Coil Current	.04 A
Contact Switching Voltage (Max)	115 VAC, 200 VAC
Contact Current Rating	25 A
Coil Voltage Rating	115 VAC

Body Features

Enclosure Type	Hermetically Sealed
----------------	---------------------

Contact Features

Contact Material	Silver Cadmium Oxide
Terminal Plating	Gold

Termination Features

Main Termination & Connection Type	Socket Pins
Coil Termination & Connection Type	Socket Pins

Mechanical Attachment



Product Mounting Feature Type	Mounting Brackets
-------------------------------	-------------------

Product Mount Type	Socket Mount
--------------------	--------------

Usage Conditions

Operating Temperature Range	-70 – 125 °C[-94 – 257 °F]
-----------------------------	----------------------------

Environmental Ambient Temperature (Max)	125 °C[257 °F]
---	----------------

Operation/Application

Vibration Resistance	30G's, 33 – 3000Hz
----------------------	--------------------

Shock Resistance	200G's, 6ms
------------------	-------------

Current Type	AC
--------------	----

Coil Magnetic System	Polarized, Monostable
----------------------	-----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
------------------------------	---------------

EU ELV Directive 2000/53/EC	Not Compliant
-----------------------------	---------------

China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
---	--------------------------------------

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
--	--

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | CII FCA-125 Series



Customers Also Bought



Documents

Product Drawings  
FCA-125-DY8

English

CAD Files  
3D PDF

3D

Customer View Model  
ENG\_CVM\_CVM\_8-1617748-5\_A.2d\_dxf.zip

English

Customer View Model  
ENG\_CVM\_CVM\_8-1617748-5\_A.3d\_igs.zip

English

Customer View Model  
ENG\_CVM\_CVM\_8-1617748-5\_A.3d\_stp.zip



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

5-1773450-5\_sec5\_FCA-125

English