

531117-1

✓ ACTIVE


AMP

TE Internal #: 531117-1

External Keying, Stainless Steel

[View on TE.com >](#)

Connectors &gt; Connector Accessories &gt; Connector Hardware

Connector Hardware Accessory Type: **External Keying**Primary Product Material: **Stainless Steel**Hardware Accessory Function: **Coding & Keying**

## Features

### Product Type Features

Connector Hardware Accessory Type	External Keying
Hardware Accessory Function	Coding & Keying

### Body Features

Primary Product Material	Stainless Steel
--------------------------	-----------------

### Packaging Features

Packaging Method	Package
Packaging Quantity	50

## Product Compliance

For compliance documentation, visit the product page on [TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2019 (197) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.


## Customers Also Bought



TE Part #205419-1  
RECEPT ASSY,37 POSN,AMPLIMITE



TE Part #202758-3  
6 PL. BLOCK



TE Part #2007741-1  
IMP100S,R,RA6P10C,UG,39



TE Part #2007716-1  
IMP100S,R,RA4P10C,RG,39



TE Part #2-2176381-7  
RQ 0805 23K2 0.1% 10PPM 5K RL



TE Part #1934342-1  
Tin Man Header Assy 3x10 Double



TE Part #204530-1  
AMPLIMITE,ASY,RCPT,FB,90,4



TE Part #A65285-000  
KTT-381127-5-1A



TE Part #2007739-1  
IMP100S,R,RA6P10C,LG,39



TE Part #1-2176378-9  
RQ 0805 15R4 0.1% 10PPM 5K RL

## Documents

### Product Specifications

### Application Specification

English