




修 订 REV NO	标 记 MARK	修 改 描 要 REVISION DESCRIPTION	签 名 SIGNATURE	日 期 DATE
		NEW DWG		2016-03-12

A型:




SPECIFICATIONS

Current Rating: 2Amps
Insulator resistance: 5000 Megchms min.
Dielectric Withstanding: AC 500V
Operating Temperature: -40° ~ +105° C
Max Processing Temp: 230° for 30~60 seconds
(260° for 10 seconds)
Contact Material: Brass
Insulator Material: NYLON-6T

UNSPECIFIED TOLERANCE: ±0.20

Plastic Base

Type	
H	1.0
PA	4.0±0.2
PC	5.5±0.2



PCB LAYOUT



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				TITLE: 产品名称: 1.27*1.0 SMT 排针 PA4.0 PB1.5 PC5.5			
X.X ±0.30	X.X° ±3°	APPD: 核准:		PART NO: 产品编号: HDGC127-PS1-n			
X.XX ±0.20	X.XX° ±2°	CHECK: 校对: 王建业		DATE	SCALE	UNIT	CODE NUMBER
X.XXX ±0.10	X.XXX° ±1°	DRAW: 绘图: 黄艳兰		2016-03-12	1:1	mm	A001