



Connectors > Connector Accessories > Connector Backshells

Connector Backshell Product Type: **Backshell Kit**

Sealable: **No**

Compatible With Connector Shape: **Rectangular**

Operating Temperature Range: **-65 – 175 °C [-85 – 347 °F]**

Features

Product Type Features

Connector Backshell Product Type	Backshell Kit
Sealable	No

Housing Features

Compatible With Connector Shape	Rectangular
---------------------------------	-------------

Usage Conditions

Operating Temperature Range	-65 – 175 °C[-85 – 347 °F]
-----------------------------	----------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Cd (2% in plating) <small>Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #CS9493-000
SEB-D




TE Part #EM6035-000
55/4122-22-6/9-9




TE Part #980892-000
1330-3300-10




TE Part #CAT-55PC-TC-2T22
2 Core Twisted Pair Cable: Tin Coated Copper Cable, 22 AWG




TE Part #CS9494-000
SEB-E




TE Part #CS9495-000
SEB-F



TE Part #CS9491-000
SEB-B



TE Part #540835-000
55PC1131-22-3/6/9-9



TE Part #459729-000
55PC1111-22-9-9

Documents

Product Drawings

732-8002-01

English

Datasheets & Catalog Pages

DMC-M Series Single Module EN4165

English

