




TE Internal #: 1565158-1  
Preloaded - C-Clip PCB Spring Contact, 1.5 mm [.059 in]  
Uncompressed Height, 3.1 mm [.122 in] Length, 1.1 mm [.043 in]  
Width  
[View on TE.com >](#)

Connectors > Contacts > PCB Spring Contacts



Spring Finger Type: **Preloaded - C-Clip**  
Scalable: **No**  
Side Protected: **No**  
Uncompressed Height: **1.5 mm [.059 in]**  
Product Length: **3.1 mm [.122 in]**

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board
Spring Finger Type	Preloaded - C-Clip
Scalable	No

Configuration Features

Number of Positions	1
Side Protected	No

Contact Features

Contact Underplating Material	Nickel
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Gold
Contact Working Range (Low)	.9 mm[.035 in]
Contact Working Range (High)	1.2 mm[.047 in]
Point of Contact Area Plating Material	Gold



Contact Current Rating (Max)	1 A
------------------------------	-----

Dimensions

Uncompressed Height	1.5 mm[.059 in]
Product Length	3.1 mm[.122 in]
Product Width	1.1 mm[.043 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Method	Tape & Reel
Packaging Quantity	5000

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 2305018-2  
USB TYPE C, REC IPX8 ON BOARD  
DUAL SMT



TE Part # 1551572-5  
Shield Finger, Loose Piece


Customers Also Bought



TE Part #2-2013310-2  
EMBOSS TAPE DDR3 204P 9.2H STD



TE Part #5-103908-3  
04 MTE HDR SRST LATCH W/HLDWN



TE Part #2356408-1  
4P,COAX,HDR ASSY,180DEG,COD A,  
SHORT



TE Part #CAT-D9934-A75E  
Header Assembly: Wire-to-Board, 15A,  
gold or tin plated



TE Part #1-179276-2  
DYNAMIC 3200 HDR ASSY 2P H



TE Part #5-103908-2  
03 MTE HDR SRST LATCH W/HLDWN



TE Part #1827625-1  
SHIELD FINGER 3014 ANTI OVER  
STRESS TYPE



TE Part #4-794636-0  
10P MICRO MNL ASSY,VRT,SMT,LF



TE Part #2-928776-3  
MOD2 STIFT M A-PIN

Documents

Product Drawings  
SHIELD FINGER 1511

English

CAD Files  
3D PDF



3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1565158-1\\_G.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1565158-1\\_G.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1565158-1\\_G.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Products for Mobile Equipment](#)

English

Product Specifications

[Product Specification](#)

Japanese