

PSR-M-B2-SDI8-SDO4-DO4-SC - Safety module



1104974

<https://www.phoenixcontact.com/us/products/1104974>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Configurable safety module (basic module), 8 safe inputs, 4 safe outputs, 4 reset inputs or 4 signal outputs, 4 clock outputs, can be extended via TBUS, up to SIL 3, Cat. 4/PL e, plug-in screw terminal block, TBUS connector not included

Product description

The configurable and individually scalable PSRmodular safety system is a flexible safety solution for monitoring your machine or system. The freely configurable base module is used to monitor various pieces of safety equipment such as emergency stop, safety doors, and light grids. The base module has safe inputs and outputs, as well as signal outputs and clock outputs.

Your advantages

- Cost-effective safety solution with a high level of adaptability to individual requirements
- Fast startup, thanks to easy hardware and software configuration
- Machine downtimes minimized with comprehensive, easy-to-understand diagnostics
- Flexible extension with safe inputs and outputs
- Possibility of connecting fieldbus gateways for bidirectional communication between the base module and the higher-level controller
- Low housing width of just 22.6 mm
- Up to Cat. 4/PL e in accordance with EN ISO 13849-1, SIL 3 in accordance with EN IEC 62061, SIL 3 in accordance with IEC 61508
- Suitable for elevator applications in accordance with EN 81-20

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1104974 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DN02 |
| Product key | DNA361 |
| GTIN | 4055626973258 |
| Weight per piece (including packing) | 198 g |
| Weight per piece (excluding packing) | 159 g |
| Customs tariff number | 85371098 |
| Country of origin | IT |

Technical data

Notes

Note on application

| | |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

Product properties

| | |
|--------------|-----------------|
| Product type | Safety device |
| Application | Emergency stop |
| | Light grid |
| | Safety door |
| | Safe shutdown |
| Control | 1 and 2 channel |

Insulation characteristics

| | |
|------------------|-----|
| Protection class | III |
|------------------|-----|

Times

| | |
|---------------|-----------------------|
| Response time | see user manual |
| Restart time | min. 5 s (Boot time) |
| | max. 10 s (Boot time) |

Electrical properties

| | |
|---|---|
| Maximum power dissipation for nominal condition | 7.1 W (with max. permissible load) |
| Nominal operating mode | 100% operating factor |
| Interfaces | DIN rail TBUS for connection to the master module, not supplied as standard |

Air clearances and creepage distances between the power circuits

| | |
|--------------------------------|---|
| Rated surge voltage/insulation | Basic insulation 4 kV between all current paths and housing |
|--------------------------------|---|

Supply

| | |
|--|--|
| Designation | A1/A2 |
| Rated control circuit supply voltage U_S | 19.2 V DC ... 28.8 V DC |
| Rated control circuit supply voltage U_S | 24 V DC -20 % / +20 % (provide external protection, typically 5 A) |
| Rated control supply current I_S | typ. 55 mA (Outputs inactive) |
| | typ. 135 mA (Outputs active, without load) |
| Power consumption at U_S | typ. 1.32 W (Outputs inactive) |
| Inrush current | < 2.3 A ($\Delta t = 1$ ms at U_S) |
| Filter time | typ. 5 ms (at A1 in the event of voltage dips at U_S) |
| Protective circuit | Serial protection against polarity reversal |

Input data

Digital: IN1, IN2, IN3, IN4, IN5, IN6, IN7, IN8

PSR-M-B2-SDI8-SDO4-DO4-SC - Safety module



1104974

<https://www.phoenixcontact.com/us/products/1104974>

| | |
|---|---|
| Description of the input | Safety-related digital inputs |
| | IEC 61131-2 Type 2 |
| Number of inputs | 8 |
| Input voltage range "0" signal | 0 V DC ... 5 V DC (for safe Off) |
| Input voltage range "1" signal | 11 V DC ... 28.8 V DC |
| Input current range "0" signal | < 1 mA |
| Filter time | min. 3 ms \pm 2 ms (adjustable) |
| | max. 250 ms \pm 2 ms (adjustable) |
| | Test pulse rate \geq 2x set filter time, min. Test pulse rate = 10 ms |
| Cable length | max. 100 m (per input) |
| Max. permissible overall conductor resistance | max. 1.2 k Ω (Input and reset circuit at U_S) |
| Current consumption | typ. 10 mA (typ. with U_S) |
| | max. 12.1 mA (at a control voltage of 28.8 V DC) |

Digital: Reset inputs (FBK)

| | |
|---|--|
| Description of the input | configurable (as signal output or reset input) |
| | IEC 61131-2 Type 2 |
| Number of inputs | 4 |
| Input voltage range "0" signal | 0 V DC ... 5 V DC |
| Input voltage range "1" signal | 11 V DC ... 28.8 V DC |
| Input current range "0" signal | < 1 mA |
| Filter time | 250 ms \pm 2 ms (Test pulse rate > 500 ms) |
| Cable length | max. 100 m (per input) |
| Max. permissible overall conductor resistance | 1.2 k Ω (Input and reset circuit at U_S) |
| Current consumption | typ. 12 mA (typ. with U_S) |
| | max. 14.7 mA (at a control voltage of 28.8 V DC) |

Output data

Digital: O1, O2, O3, O4

| | |
|------------------------------|--|
| Output description | Safety-related digital outputs |
| | PNP, OSSD |
| | IEC 61131-2 type 0.5 (observe limiting continuous current) |
| Number of outputs | 4 |
| Short-circuit protection | Yes (max. permissible short-circuit current 12 A) |
| Leakage current | max. 250 μ A |
| Cable length | max. 100 m (per output) |
| Ohmic load | min. 50 Ω (Observe limiting continuous current) |
| Max. capacitive load | max. 820 nF |
| Max. inductive load | max. 2.4 mH |
| Limiting continuous current | 400 mA (per channel) |
| | 1.6 A (Total current of all safe digital outputs) |
| Inrush current | max. 600 mA ($\Delta t < 10$ ms) |
| Nominal output voltage | 24 V DC (Supply via A1) |
| Nominal output voltage range | 18.5 V DC ... 28.1 V DC ($U_S - 0,7$ V) |

PSR-M-B2-SDI8-SDO4-DO4-SC - Safety module



1104974

<https://www.phoenixcontact.com/us/products/1104974>

| | |
|----------------------------------|---|
| Switching frequency | max. $\frac{1}{4} \times t_{\text{Cycle}}$ [Hz] |
| Output voltage when switched off | < 0.1 V |
| Test pulses | < 120 μs (Test pulse width of low test pulses) |
| | ≥ 650 ms (Test pulse rate for low test pulse) |
| | < 150 μs (Test pulse width, high test pulse) |
| | ≥ 1.5 s (Test pulse rate, high test pulse) |
| Discharging circuit | Yes, internal |

Signal: MO1, MO2, MO3, MO4

| | |
|----------------------------------|--|
| Output description | PNP, IEC 61131-2 Typ 0,1 |
| | non-safety-related, configurable (as signal output or reset input) |
| Number of outputs | 4 |
| Output voltage when switched off | max. 0.1 V |
| Voltage | 24 V DC (via A1) |
| Maximum inrush current | 1.1 A ($\Delta t = 3$ s at U_s) |
| Limiting continuous current | 100 mA (per channel) |
| | 400 mA (Total current of all digital signal outputs) |
| Leakage current | max. 100 μA |
| Switching frequency | max. $\frac{1}{4} \times t_{\text{Cycle}}$ [Hz] |
| Short-circuit protection | Yes (self-limitation at 1.1 A) |
| Cable length | max. 100 m (per output) |

Clock: T1, T2, T3, T4

| | |
|----------------------------------|--|
| Output description | PNP, IEC 61131-2 Typ 0,1 |
| Number of outputs | 4 |
| Voltage | 24 V DC (via A1) |
| Output voltage when switched off | max. 0.1 V |
| Maximum inrush current | 1.1 A ($\Delta t = 3$ s at U_s) |
| Limiting continuous current | 100 mA (per channel) |
| | 400 mA (Total current of all outputs) |
| Leakage current | max. 100 μA |
| Test pulses | ≤ 200 μs (Test pulse duration) |
| | Test pulse rate = $8 \times t_{\text{Cycle}}$ [ms] |
| Short-circuit protection | Yes (self-limitation at 1.1 A) |
| Cable length | max. 100 m (per output) |
| Max. capacitive load | max. 470 nF |
| Max. inductive load | max. 2.4 mH |
| Discharging circuit | Yes, internal |

Connection data

Connection technology

| | |
|-----------|-----|
| pluggable | yes |
|-----------|-----|

Conductor connection

| | |
|-------------------|------------------|
| Connection method | Screw connection |
|-------------------|------------------|

| | |
|----------------------------------|---------------------|
| Conductor cross section rigid | 0.2 mm² ... 2.5 mm² |
| Conductor cross section flexible | 0.2 mm² ... 2.5 mm² |
| Conductor cross-section AWG | 24 ... 12 |
| Stripping length | 7 mm |
| Screw thread | M3 |
| Tightening torque | 0.5 Nm ... 0.6 Nm |

Signaling

| | |
|---------------------------|---|
| Status display | 1 x LED (green), 1 x LED (orange), 1 x LED (blue) |
| | 4 x LED (green, yellow, red) |
| | 12 x LED (yellow) |
| Operating voltage display | 1 x LED (green) |
| Error indication | 2 x LED (red) |

Dimensions

| | |
|--------|-----------|
| Width | 22.61 mm |
| Height | 112.58 mm |
| Depth | 113.6 mm |

Material specifications

| | |
|------------------|-----------------------------|
| Color (Housing) | yellow (RAL 1018) |
| Housing material | Polyamide PA non-reinforced |

Characteristics

Safety data

| | |
|---------------|---|
| Stop category | 0 |
|---------------|---|

Safety data: EN ISO 13849

| | |
|------------------------|----------------------|
| Performance level (PL) | e (2-channel wiring) |
| | d (1-channel wiring) |

Safety data: IEC 61508 - High-demand for 2-channel wiring

| | |
|------------------------------|---|
| Safety Integrity Level (SIL) | 3 |
|------------------------------|---|

Safety data: IEC 61508 - High-demand for 1-channel wiring

| | |
|------------------------------|---|
| Safety Integrity Level (SIL) | 2 |
|------------------------------|---|

Safety data: EN IEC 62061

| | |
|------------------------------|----------------------|
| Safety Integrity Level (SIL) | 3 (2-channel wiring) |
| | 2 (1-channel wiring) |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------|
| Degree of protection | IP20 |
| Min. degree of protection of inst. location | IP54 |

PSR-M-B2-SDI8-SDO4-DO4-SC - Safety module



1104974

<https://www.phoenixcontact.com/us/products/1104974>

| | |
|--|--|
| Ambient temperature (operation) | -10 °C ... 55 °C (observe derating) |
| Ambient temperature (storage/transport) | -20 °C ... 85 °C |
| Maximum altitude | ≤ 2000 m (Above sea level) |
| Max. permissible humidity (storage/transport) | 95 % (non-condensing) |
| Max. permissible relative humidity (operation) | 95 % (non-condensing) |
| Shock | 10g for $\Delta t = 16$ ms (continuous shock, 1000 shocks in each space direction) |
| Vibration (operation) | 10 Hz ... 150 Hz, 2g |

Approvals

CE

| | |
|----------------|--------------|
| Identification | CE-compliant |
|----------------|--------------|

Mounting

| | |
|-------------------|------------------------|
| Mounting type | DIN rail mounting |
| Assembly note | Observe derating |
| Mounting position | vertical or horizontal |

PSR-M-B2-SDI8-SDO4-DO4-SC - Safety module


1104974

<https://www.phoenixcontact.com/us/products/1104974>




Drawings

Application drawing



Block diagram




PSR-M-B2-SDI8-SDO4-DO4-SC - Safety module



1104974

<https://www.phoenixcontact.com/us/products/1104974>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1104974>



Functional Safety

Approval ID: Z10 029429 0013



cULus Listed

Approval ID: E238705

PSR-M-B2-SDI8-SDO4-DO4-SC - Safety module



1104974

<https://www.phoenixcontact.com/us/products/1104974>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27371819 |
| ECLASS-13.0 | 27371819 |
| ECLASS-12.0 | 27371819 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001449 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39122200 |
|-------------|----------|

Environmental product compliance

| | |
|---|--|
| EU RoHS | |
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
| China RoHS | |
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |
| EU REACH SVHC | |
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com