




**900V N-CHANNEL MOSFET**
**◆ Features:**

- ✧ Fast switching speed  
开关速度快
- ✧ High input impedance and low level drive  
高输入阻抗和低电平驱动
- ✧ Avalanche energy tested  
雪崩能量测试
- ✧ Improved dv/dt capability, high ruggedness  
提高 dv/dt 能力, 高耐用性

**◆ Applications**

- ✧ High efficiency switch mode power supplies  
高效率开关电源
- ✧ Power factor correction  
功率因数校正
- ✧ Electronic lamp ballast  
电子整流器


**TO-220F**


单位: mm  
TO-220F

**◆ Absolute Maximum Ratings (Tc=25°C)**

| Symbol           | Parameters                                            | Ratings    | Unit |
|------------------|-------------------------------------------------------|------------|------|
| V <sub>DSS</sub> | Drain-Source Voltage<br>漏源电压                          | <b>900</b> | V    |
| V <sub>GS</sub>  | Gate-Source Voltage-Continuous<br>栅源电压                | <b>±30</b> | V    |
| I <sub>D</sub>   | Drain Current-Continuous (Note 2) (Tc=25°C)<br>漏极持续电流 | <b>9</b>   | A    |
| I <sub>DM</sub>  | Drain Current-Single Plused (Note 1)<br>漏极单次脉冲电流      | <b>36</b>  | A    |
| P <sub>D</sub>   | Power Dissipation (Note 2)<br>功率损耗                    | <b>47</b>  | W    |
| T <sub>j</sub>   | Max.Operating junction temperature<br>最大结温            | <b>150</b> | °C   |

**◆ Electrical characteristics (Tc=25°C unless otherwise noted)**

| Symbo<br>l                    | Parameters                                                  | Min        | Typ        | Max         | Units | Conditions                                                          |
|-------------------------------|-------------------------------------------------------------|------------|------------|-------------|-------|---------------------------------------------------------------------|
| <b>Static Characteristics</b> |                                                             |            |            |             |       |                                                                     |
| B <sub>VDSS</sub>             | Drain-Source Breakdown<br>VoltageCurrent (Note 1)<br>漏极击穿电压 | <b>900</b> | --         | --          | V     | I <sub>D</sub> =250μA,<br>V <sub>GS</sub> =0V, T <sub>J</sub> =25°C |
| V <sub>GS(th)</sub>           | Gate Threshold Voltage<br>栅极开启电压                            | <b>2.0</b> | --         | <b>4.0</b>  | V     | V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =250μA            |
| R <sub>DS(on)</sub>           | Drain-Source On-Resistance<br>漏源导通电阻                        | --         | <b>1.0</b> | --          | Ω     | V <sub>GS</sub> =10V, I <sub>D</sub> =4.5A                          |
| I <sub>GSS</sub>              | Gate-Body Leakage Current<br>栅极漏电流                          | --         | --         | <b>±100</b> | nA    | V <sub>GS</sub> =±30V, V <sub>DS</sub> =0                           |
| I <sub>DSS</sub>              | Zero Gate Voltage Drain Current<br>零栅极电压漏极电流                | --         | --         | <b>10</b>   | μA    | V <sub>DS</sub> =900V, V <sub>GS</sub> =0                           |
| g <sub>fs</sub>               | Forward Transconductance<br>正向跨导                            | --         | <b>9.0</b> | --          | S     | V <sub>DS</sub> =40V, I <sub>D</sub> =4.5A                          |

| Switching Characteristics |                                                                          |    |      |     |      |                                                                                 |
|---------------------------|--------------------------------------------------------------------------|----|------|-----|------|---------------------------------------------------------------------------------|
| T <sub>d (on)</sub>       | Turn-On Delay Time<br>开启延迟时间                                             | -- | 55   | --  | ns   | V <sub>DS</sub> =450V, I <sub>D</sub> =9A,<br>R <sub>G</sub> =25Ω (Note 2)      |
| T <sub>r</sub>            | Rise Time<br>上升时间                                                        | -- | 130  | --  | ns   |                                                                                 |
| T <sub>d (off)</sub>      | Turn-Off Delay Time<br>关闭延迟时间                                            | -- | 110  | --  | ns   |                                                                                 |
| T <sub>f</sub>            | Fall Time<br>下降时间                                                        | -- | 80   | --  | ns   |                                                                                 |
| Q <sub>g</sub>            | Total Gate Charge<br>栅极总电荷                                               | -- | 670  | --  | nC   | V <sub>DS</sub> =480V ,<br>V <sub>GS</sub> =10V,<br>I <sub>D</sub> =9A (Note 2) |
| Q <sub>gs</sub>           | Gate-Source Charge<br>栅源极电荷                                              | -- | 13.5 | --  | nC   |                                                                                 |
| Q <sub>gd</sub>           | Gate-Drain Charge<br>栅漏极电荷                                               | -- | 27   | --  | nC   |                                                                                 |
| Dynamic Characteristics   |                                                                          |    |      |     |      |                                                                                 |
| C <sub>iss</sub>          | Input Capacitance<br>输入电容                                                | -- | 2780 | --  | pF   | V <sub>DS</sub> =25V, V <sub>GS</sub> =0,<br>f=1MHz                             |
| C <sub>oss</sub>          | Output Capacitance<br>输出电容                                               | -- | 228  | --  | pF   |                                                                                 |
| C <sub>rss</sub>          | Reverse Transfer Capacitance<br>反向传输电容                                   | -- | 28   | --  | pF   |                                                                                 |
| I <sub>S</sub>            | Continuous Drain-Source Diode<br>Forward Current (Note 2)<br>二极管导通正向持续电流 | -- | --   | 9   | A    |                                                                                 |
| V <sub>SD</sub>           | Diode Forward On-Voltage<br>二极管正向导通电压                                    | -- | --   | 1.4 | V    | I <sub>S</sub> =9A, V <sub>GS</sub> =0                                          |
| R <sub>th(j-c)</sub>      | Thermal Resistance, Junction to Case<br>结到外壳的热阻                          | -- | --   | 2.7 | °C/W |                                                                                 |

Note 1: Repetitive Rating : Pulse width limited by maximum junction temperature

Note 2: Pulse test:  $PW \leq 300\mu s$ , duty cycle  $\leq 2\%$ .