


1 Channel Ultra-low Capacitance ESD Protection

Features

- ♦ Ultra-Low capacitance: 0.05pF(typ.)
- ♦ Low leakage current (<10 nA)
- ♦ Fast response time (<1ns)
- ♦ Bi-directional, single line protection
- ♦ IEC 61000-4-2 (ESD Air): 15kV
- ♦ IEC 61000-4-2 (ESD Contact): 8kV

Application

- ♦ USB 3.0/3.1
- ♦ HDMI 1.3/1.4/2.0
- ♦ RF Antenna
- ♦ SATA and eSATA Interface



Limiting Values($T_A = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

Symbol	Parameter	Conditions	Min	Max	Unit
V_{ESD}	Electrostatic Discharge Voltage	IEC 61000-4-2; Contact Discharge	-	8	kV
		IEC 61000-4-2; Air Discharge	-	15	kV
T_A	Operating Temperature Range	-	-40	85	$^{\circ}\text{C}$
Tstg	Storage Temperature Range	-	-55	125	$^{\circ}\text{C}$

Electrical Characteristics($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise specified)

Symbol	Parameter	Conditions	Min	Typ.	Max	Unit
V_{DC}	Continuous Operating Voltage	-	-	-	15	V
V_T	Trigger Voltage	IEC61000-4-2 8kV contact discharge	-	450	-	V
V_C	Clamping Voltage	IEC61000-4-2 8kV contact discharge	-	40	-	V
I_L	Leakage Current	DC 15 V shall be applied on component	-	-	10	nA
C_J	Capacitance	Measured at 10MHz	-	0.05	-	pF

Typical Characteristics




Fig.1 Typical ESD Response (IEC 61000-4-2, 8kV contact discharge)




Fig.2 Typical Device Capacitance VS. Frequency






Fig.3 HDMI 2.0 Mask at 6.0 Gbps

ESD Protection for Signal Line


The PESD is designed for the protection of one bidirectional data line from ESD damage.

1. Place the PESD as close to the input terminal or connector as possible.
2. Minimize the path length between the PESD and the protected signal line.
3. Use ground planes whenever possible.




Package Outline

0402



Recommended Solder Pad Footprint



***Sizes in mm**


Notes:

This solder pad layout is for reference purposes only.

Dimension	Unit: Millimeters	
	Min.	Max.
A	0.25	0.45
b	0.20	0.40
D	0.90	1.10
E	0.40	0.60
e	0.65BSC	
L1	0.30	0.50
L2	0.00	0.05

Summary of Packing Options

Package	Packing Description	Packing Quantity	Industry Standard
0402	Tape/Reel, 7" reel	10000	EIA-481-1



Reflow Condition		Pb-Free Assembly
Pre-heat	-Temperature Min ($T_{S(min)}$)	+150°C
	-Temperature Max($T_{S(max)}$)	+200°C
	-Time (Min to Max) (t_s)	60-180 secs.
Average ramp up rate (Liquid us Temp (T_L) to peak)		3°C/sec. Max
$T_{S(max)}$ to T_L - Ramp-up Rate		3°C/sec. Max
Reflow	-Temperature(T_L)(Liquid us)	+217°C
	-Temperature(t_L)	60-150 secs.
Peak Temp (T_p)		+260(+0/-5)°C
Time within 5°C of actual Peak Temp (t_p)		30 secs. Max
Ramp-down Rate		6°C/sec. Max
xTime 25°C to Peak Temp (T_P)		8 min. Max
Do not exceed		+260°C

Disclaimer

The information presented in this document is for reference only. Guangdong Youfeng Microelectronics Co.,Ltd. reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise. The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), YFW or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale. This publication supersedes & replaces all information previously supplied. For additional information, please visit our website <https://www.yfwdiode.com>, or consult YFW sales office for further assistance.