



# 零件承认书

SPECIFICATION FOR APPROVAL

客户名称: 0110

规格描述: ZEPM1365一体成型电感规格书

日 期: 2023/10/10

增益签核:

| 制订 | 审核 | 核准 |
|----|----|----|
| 夏琳 | 陈雨 | 李万 |

客户签核:

| 工程 | 审核 | 核准 |
|----|----|----|
|    |    |    |



东莞市增益实业有限公司

地址: 东莞市塘厦镇林村塘厦大道北552号

电话: 0769-87321000

传真: 0769-87891229

物料类型: 一体成型电感

日 期: 2023/10/10

版 本: A



#### ◆特征:

- 低直流电阻和超大电流的薄型设计
- 磁屏蔽型抗电磁干扰强适用于高密度安装
- 高可靠性, 通过采用一体成型结构享有卓越的抗震动性
- 由于复合结构, 超低蜂鸣噪声
- 低损耗合金粉末压铸低阻抗, 小寄生电容
- 能效高, 可减少绕线的低直流电阻与磁芯的涡流损耗
- 频率高达 3MHz
- 绝缘最大电压 30VDC
- 符合 RoHS, 无卤和 REACH

#### ◆用途:

- PDA, 笔记本, 台式机, 服务器应用程序
- 大电流 POL 转换器
- 电池供电设备
- 分布式电源系统中的 DC/DC 转换器

#### ◆环境:

- 工作温度:  $-55^{\circ}\text{C}$  至  $+125^{\circ}\text{C}$   
(包括线圈自身温升)

#### ◆试验设备:

- 电感值: WK3260B 或同等仪器
- 电流: WK3260B+WK3265B
- 直流电阻: Chroma 16502 或同等仪器

#### ◆产品型号:

#### Features:

- Low RDC and ultra-high current thin design
- Magnetic shielding type, strong anti- electromagnetic Interference, suitable for high- density installation
- High-reliability, High vibration resistance as result of newly developed integral construction
- Ultra Low buzz noise, due to composite construction
- Die-casting by low loss alloy powder low impedance, Small parasitic capacitance
- High efficiency Low DC resistance of winding and low eddy-current loss of the core
- Frequency up to 3MHz
- Absolute maximum voltage 30VDC
- RoHS, Halogen Free and REACH Compliance

#### Applications:

- PDA , notebook ,desktop ,server applications
- High current POL converters
- Battery powered devices
- DC/DC converters in distributed power systems

#### Environmental Data:

- Operating Temperature:  $-55^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$   
(Including coils self-temperature rise)

#### Test Equipment:

- L: WK3260B LCR meter or equivalent
- Isat & Irms: WK3260B+WK3265B
- DCR: Chroma 16502 or equivalent

#### Product Identification:

**ZEPM**  
①

**1365H**  
②

**100**  
③

**M**  
④

① 产品代号 Product symbol PM: 平面一体成型电感

② 尺寸规格(L×W×H) (mm) Dimension(L×W×H) (mm): 1365H 13.5x12.6x6.5 合金

③ 电感量标称值 Inductance : 10uH

④ 电感量公差 Tolerance : M  $\pm 20\%$

产品外观尺寸:

Shape and Dimensions(dimensions are in mm):



| Part No  | ITEM       |           |          |          |         |      |      |      |
|----------|------------|-----------|----------|----------|---------|------|------|------|
|          | A          | B         | C        | D        | E       | F 参考 | G 参考 | H 参考 |
| ZEPM1365 | 13.5 ±0.35 | 12.6±0.40 | 6.5±0.30 | 3.85±0.5 | 2.7±0.3 | 6.50 | 14.5 | 5.10 |

规格特性 :

Specifications :

ZEPM1365 Series

| Part Number   | Inductance<br>(uH) @100KHz | DC Resistance<br>(mΩ) Max. | Heat Rating<br>Current (A) | Saturation<br>Current (A) |
|---------------|----------------------------|----------------------------|----------------------------|---------------------------|
| ZEPM1365HR47M | 0.47                       | 1.20                       | 36.0                       | 60.0                      |
| ZEPM1365H1R0M | 1.0                        | 2.10                       | 25.0                       | 36.0                      |
| ZEPM1365H1R5M | 1.5                        | 2.90                       | 24.0                       | 31.0                      |
| ZEPM1365H2R2M | 2.2                        | 4.50                       | 21.5                       | 28.5                      |
| ZEPM1365H3R3M | 3.3                        | 6.50                       | 17.5                       | 26.0                      |
| ZEPM1365H4R7M | 4.7                        | 8.5                        | 16.5                       | 25.0                      |
| ZEPM1365H5R6M | 5.6                        | 11.0                       | 14.5                       | 23.0                      |
| ZEPM1365H6R8M | 6.8                        | 14.0                       | 13.5                       | 20.0                      |
| ZEPM1365H8R2M | 8.2                        | 16.0                       | 12.5                       | 16.5                      |
| ZEPM1365H100M | 10                         | 17.0                       | 11.5                       | 15.5                      |
| ZEPM1365H150M | 15                         | 30.0                       | 10.0                       | 11.5                      |
| ZEPM1365H220M | 22                         | 44.0                       | 8.5                        | 9.5                       |
| ZEPM1365H270M | 27                         | 55.0                       | 7.5                        | 8.0                       |
| ZEPM1365H330M | 33                         | 65.0                       | 7.0                        | 8.5                       |
| ZEPM1365H470M | 47                         | 85.0                       | 6.0                        | 7.3                       |
| ZEPM1365H680M | 68                         | 130                        | 5.5                        | 5.7                       |
| ZEPM1365H101M | 100                        | 150                        | 4.0                        | 4.5                       |

Ls 测试频率/电压 Ls Test frequency/Voltage: 100kHz/1.0V;  
饱和电流: 指使电感量比初始值下降 30%的电流值。  
Isat: The DC current is that which cause a 30% inductance reduction from the initial value.  
温升电流: 指使电感器表面温度上升 40℃的电流值 (参考周围环境温度 25℃)。  
IDC: The DC current is inductor surface temperature to rise by 40℃ ( Reference ambient temperature 25℃).

1 . 可靠性 Reliability Data

| 项目<br>Items                              | 要求<br>Requirements                                                                               | 试验方法及备注<br>Test Methods and Remarks                                                                                                                    |
|------------------------------------------|--------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| 工作温度范围<br>Operating<br>Temperature Range | -55℃~+125℃                                                                                       | 包括自身发热的上升温度<br>Including self-heating temperature rise.                                                                                                |
| 可焊性<br>Solderability                     | 电极面 90%以上覆盖新的焊料。<br>90% or more of electrode area shall be coated by new solder.                 | 在 245 ℃±5 ℃ 熔 融 的 焊 锡 (96.5Sn/3.0Ag/0.5Cu) 中浸 5 s±1 s。<br>Dip pads in flux and dip in solder pot (96.5Sn/3.0Ag/0.5Cu) at 245 ℃±5 ℃ for (5±1) seconds.  |
| 耐焊接热<br>Resistance to<br>Soldering Heat  | 外观无可见机械损伤;<br>电感量变化率: ±10%以内。<br>No visible mechanical damage.<br>Inductance change: Within ±10% | 在 260 ℃±5 ℃ 熔 融 的 焊 锡 (96.5Sn/3.0Ag/0.5Cu) 中浸 10 s±1 s。<br>Dip pads in flux and dip in solder pot (96.5Sn/3.0Ag/0.5Cu) at 260℃±5 ℃ for (10±1) seconds. |
| 低温<br>Low temperature<br>stroe           | 外观无可见机械损伤;<br>电感量变化率: ±10%以内。<br>No visible mechanical damage.<br>Inductance change: Within ±10% | 温度-55 ℃±2℃, 时间 1000 h<br>Stroe temperature -55±2℃ for total 1000hr.                                                                                    |

|                                           |                                                                                                                                                                                          |                                                                                                                                                                                                                                                                                             |
|-------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 高温<br>High temperature<br>stroe           | 外观无可见机械损伤；电感量变化率：±10%以内。<br>No visible mechanical damage. Inductance change: Within ±10%                                                                                                 | 温度 125 °C ±2°C，时间 1000 h<br>Stroe temperature<br>125±2°C for total 1000hr.                                                                                                                                                                                                                  |
| 恒定湿热<br>Static Humidity                   | 外观无可见机械损伤；电感量变化率：±10%以内。<br>No visible mechanical damage. Inductance change: Within ±10%                                                                                                 | 将电感器放置在于湿度 (93±3)%RH, 温度 40 °C ±2 °C 的环境中存放 96 h ±2 h，在室温下放置 2 小时后、48 小时内测试。<br>Inductors shall be subjected to (93±3)%RH . at 40 °C ±2 °C for 96 h ±2 h . Inductors are to be tested after having air dried for 2 hours.                                                                   |
| 温度变化<br>Thermal shock                     | 外观无可见机械损伤；电感量变化率：±10%以内。<br>No visible mechanical damage. Inductance change: Within ±10%                                                                                                 | (-40±3) °C, 时间 (30±3) min ↔ (85°C ±2) °C / (30±3) min, 转换时间 (2~3) min, 循环5次；<br>在室温下放置 2 小时后、48 小时内测试。<br>The test sample shall be placed at (-40±3)°C and (85±2)°C for (30±3) min, different temperature conversion time is 2~3 minutes. The temperature cycle shall be repeated 5 cycles. |
| 机械冲击<br>Mechanical Shock                  |  <p>0.5m 自然下落<br/>基板</p> <p>电感无出现电极脱落、断线现象。<br/>No evidence of terminal peel off and wire broken.</p> | 把电感焊在厚度为 1.0mm 的基板上, 并固定在黄铜制 15cm 大, 重 1.4Kg 的立方体内, 然后从 0.5m 高度往地板自然下落 (X, Y, Z 方向各一回)<br>Inductors shall be Soldering on the PCB with 1.0mm thick and fixed them in a 15cm big., 1.4Kg weight cube with brass base, let it nature fallen form 0.5m height (X, Y, Z three axes)             |
| 端子强度<br>Adhesion of<br>terminal electrode | 元件的端子与本体结合无松动、无脱落。<br>Strong bond between the pad and the core, without come off PC board.                                                                                               | 将电感器用 260 °C ±5 °C，20 s ±5 s 焊在带有 0.3 mm 厚锡膏的基板上，然后用治具垂直电极面方向加压<br>10 N，10 s ±1 s。<br>Inductors shall be subjected to 260 °C ±5 °C for 20 s ±5 s Soldering in the base whit 0.3mm solder. And then aplomb electrode way plus tax 10 N for 10± 1s seconds.                                   |


2.产品包装:

Packaging:

- Tape and Reel Specifications: (Dimensions are in mm)



- Reel dimensions (mm)



- Tape Dimension (mm)



To maintain the solderability of terminal electrodes and to keep the packing material in good condition, product should be used within 6 months from the time of delivery. And the solderability of products electrodes may decrease as time passes, so in case

of storage over 6 months, solderability shall be checked before actual usage.

## 5.2 存储条件 Storage Conditions

①存放货物的仓库应满足以下条件:

温度:  $-10 \sim +40^{\circ}\text{C}$

相对湿度: 30~70%RH

Store products in a warehouse in compliance with the following condition:

Temperature:  $-10$  to  $+40^{\circ}\text{C}$

Humidity: 30~70%RH

②不要使产品遭受温度和湿度的快速变化。

Do not subject products to rapid changes in temperature and humidity.

③不要将产品存放在化学环境中,如硫酸气体或碱性气体中,否则会降低电极端子的焊接特性和使电感器腐蚀。

Do not store the products in chemical atmosphere such as one containing sulfurous acid gas or alkaline gas, that will causes poor solderability and corrosion of inductors.

④不要以散包装的形式存放产品以防止电感器间的相互碰撞造成磁芯破裂或断线。

Do not store products in bulk packaging to prevent collision among inductors which causes core chipping and wire breakage.

⑤为了避免受潮气、灰尘等物质的影响,产品应保管于货架上。

Store products on pallets to protect from humidity, dust, etc.

⑥产品应避免热冲击、振动以及直接光照等等。

Avoid heat shock, vibration, direct sunlight, etc.

## 6. 说明 NOTE

6.1 本承认书的数据更改需经双方确认,任何一方单独修改无效。

Any revision to the specification Approval must be confirmed by both the supplier and the customer, otherwise the revision is invalid.

6.2 当本公司的产品使用在一般电子设备以外的领域时,对于此所引发的设备失效我司将不承担任何法律责任。

In case of using the product for the purpose other than general electronics devices, we shall not be held liable for any dysfunctions in or damage to the equipment with which the product is used.

6.3 本承认书只保证我司产品作为一个单体时的质量情况,当我司产品被安装到贵司产品上时,请贵司对使用在贵司电路上的产品情况进行了有效评价和确认。

Our specification limits the quality of the component as a single unit. Please ensure the component is thoroughly evaluated in your application circuit.

6.4 本承认书在客户收到 7 天之内,必须签章返回,逾期视为默认。

The specification Approval should be sent back to the supplier with customer's chop on it within 7 days after receiving it, or we will take it as approved by customer.