




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: .32 – .82 mm²

Mating Tab Width: 2.8 mm, 3.18 mm [.11 in, .125 in]

Mating Tab Thickness: .41 mm [.016 in]

Features

Product Type Features

|                   |           |
|-------------------|-----------|
| Terminal Features | Wire Stop |
| Insertion Force   | Normal    |

Configuration Features

|                                   |               |
|-----------------------------------|---------------|
| Compatible With Wire & Cable Type | Discrete Wire |
| Connection Capacity               | Single        |

Electrical Characteristics

|                |       |
|----------------|-------|
| Voltage Rating | 600 V |
|----------------|-------|

Body Features

|                     |       |
|---------------------|-------|
| Insulation Material | Nylon |
|---------------------|-------|

Contact Features

|                                |                                  |
|--------------------------------|----------------------------------|
| Quick Disconnect Terminal Type | Receptacle                       |
| Mating Tab Width               | 2.8 mm, 3.18 mm[.11 in][.125 in] |
| Mating Tab Thickness           | .41 mm[.016 in]                  |
| Terminal Orientation           | Straight                         |



|                           |         |
|---------------------------|---------|
| Contact Base Material     | Brass   |
| Terminal Plating Material | Tin     |
| Crimp Type                | F-Crimp |
| Barrel Type               | Closed  |

Termination Features

|                       |              |
|-----------------------|--------------|
| Product Terminates To | Wire & Cable |
|-----------------------|--------------|

Mechanical Attachment

|                         |        |
|-------------------------|--------|
| Wire Insulation Support | With   |
| Mating Retention Type   | Dimple |

Dimensions

|                                      |                   |
|--------------------------------------|-------------------|
| Product Length                       | 18.67 mm[.735 in] |
| Compatible Insulation Diameter Range | 3.05 mm[.12 in]   |
| Terminal Material Thickness          | .41 mm[.016 in]   |
| Wire Size                            | .32 – .82 mm²     |

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Insulation Option           | Fully Insulated            |
| Operating Temperature Range | -40 – 110 °C[-40 – 230 °F] |

Industry Standards

|                                           |          |
|-------------------------------------------|----------|
| Compatible With Agency/Standards Products | UL       |
| UL Flammability Rating                    | UL 94V-2 |

Packaging Features

|                    |            |
|--------------------|------------|
| Packaging Quantity | 3000       |
| Packaging Method   | Strip/Reel |

Other

|              |     |
|--------------|-----|
| Barrel Color | Red |
|--------------|-----|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                         |
|-----------------------------------------------|-----------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                               |
| EU ELV Directive 2000/53/EC                   | Compliant                               |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006        |                                         |



Current ECHA Candidate List: JUNE 2024 (241)  
Candidate List Declared Against: JUNE 2024 (241)  
Does not contain REACH SVHC

|                           |                                                                                     |
|---------------------------|-------------------------------------------------------------------------------------|
| Halogen Content           | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability                                        |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2151698-2  
OCEAN\_2.0\_APPLICATOR-S-FA-176O-RSA

TE Part # 58628-1  
PROCRIMP T&D 26-14 ULTRAFast

TE Part # 7-2151698-7  
OCEAN\_2.0\_SPARE\_PART\_KIT-176O

TE Part # 58628-2  
PROCRIMP DIESET 26-14 ULTRAFast

TE Part # 90390-3  
DIES ULTRA-Fast FASTON 22-18 DIE SET

Also in the Series | [Ultra-Fast 110](#)



Quick Disconnects(14)

Customers Also Bought

TE Part #1718044-1

RAST2.5 W2W Crimp-IDC 2pos Motor Mnt

TE Part #61283-1

RING 22-16 AWG .0251 X .510 TPBR

TE Part #640455-6

06P MTA100 HDR ASSY SQ R/A POL

TE Part #ER2142-000

HT-CT-50M-1/4-OUT-0

TE Part #11032563-00

44006RC, THERM, ROHS

TE Part #1-2351052-5

LGA4677 E1A ASSY

TE Part #7-1123722-5

3.96 EP PLUG HSG 5P(NATURAL)

TE Part #6-1393250-3

W28-XT1A-10=W28

TE Part #2118707-2

1 PC STD SHIELD, CRS-16.50X16.50X3.60MM

TE Part #925574-2

RTV SOCKET

Documents

Product Drawings

ULTRA-FAST .110/.125 ASY REC 22-18 TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2-520080-2\_P.2d\_dxf.zip



English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-520080-2\\_P.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-520080-2\\_P.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Ultra-Fast and Ultra Fast Plus](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[Agency Approval Document](#)

English