



General ordering data

Order No.	1930070000
Part designation	BVZ 7.62HP/04F SN SW
Version	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 6 mm ² , Pitch: 7.62 mm, No. of poles: 4, 180°, Box
EAN	4032248579846
Qty.	100 pc(s).

System parameters

Conductor connection system	Clamping yoke connection
Outgoing direction of conductor	180°
Pitch	7.62 mm
Pitch in inch	0.3 inch
No. of poles	4
No. of rows	1
Screwdriver blade	0.6 x 3.5
Screwdriver blade standard	DIN 5264
Tightening torque, min.	0.5 Nm
Tightening torque, max.	0.6 Nm
Clamping screw	M 2.5
Stripping length	12 mm
L1 in mm	22.86 mm
L1 in inch	0 inch
Electric shock protection to DIN VDE 0470	IP 20
Electric shock protection to DIN VDE 0470	Safe from finger touch

Material data

Insulating material	PA GF
Colour	black
colour chart	Similar to RAL 9011
Insulating material group	I
Flammability class UL 94	V-0
CTI	>= 600
Contact base material	Copper alloy

Material data

Contact surface tinned

Connectable conductors

Clamping range, min.	0.2 mm ²
Clamping range, max.	6 mm ²
AWG, min.	22
AWG, max.	10
Solid, min. H05(07) V-U	0.2 mm ²
Solid, max. H05(07) V-U	6 mm ²
Flexible, min. H05(07) V-K	0.5 mm ²
Flexible, max. H05(07) V-K	6 mm ²
With wire end ferrule, acc. to DIN 46 228/1, min.	0.25 mm ²
With wire end ferrule, acc. to DIN 46 228/1, max.	6 mm ²
w. plastic collar ferrule, DIN 46228 pt 4, min.	0.25 mm ²
w. plastic collar ferrule, DIN 46228 pt 4, max.	6 mm ²
Gauge to EN 60999 a x b; ø	2.8 mm x 2.0 mm; 2.4 mm

DIN IEC rating data

Rated current, min. No. pins (Tu=20°C)	41 A
Rated current, min. No. pins (Tu=40°C)	41 A
Rated voltage for overvoltage class/pollution severity II/2	1,000 V
Rated voltage for overvoltage class/pollution severity III/2	1,000 V
Rated voltage for overvoltage class/pollution severity III/3	800 V
Rated impulse withstand voltage for overvoltage class/pollution severity II/2	6 kV
Rated impulse withstand voltage for overvoltage class/pollution severity III/2	8 kV
Rated impulse withstand voltage for overvoltage class/pollution severity III/3	8 kV

CSA rating data

Rated voltage (Use group C)	600 V
Rated current (Use group C)	35 A
AWG conductor (field wiring), min.	24
AWG conductor (field wiring), max.	10

UL 1059 rating data

Rated voltage (Use group C)	600 V
Rated current (Use group C)	35 A
AWG conductor, min.	24
AWG conductor, max.	10

Approvals

Approvals institutes



Classifications

eClass 5.1

27-26-07-04

Similar products

Order No.	Part designation	Version
1930050000	BVZ 7.62HP/02F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 6 mm ² , Pitch: 7.62 mm, No. of poles: 2, 180°, Box
1930060000	BVZ 7.62HP/03F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 6 mm ² , Pitch: 7.62 mm, No. of poles: 3, 180°, Box
1930080000	BVZ 7.62HP/05F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 6 mm ² , Pitch: 7.62 mm, No. of poles: 5, 180°, Box
1930090000	BVZ 7.62HP/06F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 6 mm ² , Pitch: 7.62 mm, No. of poles: 6, 180°, Box
1930100000	BVZ 7.62HP/07F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 6 mm ² , Pitch: 7.62 mm, No. of poles: 7, 180°, Box
1930110000	BVZ 7.62HP/08F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 6 mm ² , Pitch: 7.62 mm, No. of poles: 8, 180°, Box
1930120000	BVZ 7.62HP/09F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 6 mm ² , Pitch: 7.62 mm, No. of poles: 9, 180°, Box
1930130000	BVZ 7.62HP/10F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 6 mm ² , Pitch: 7.62 mm, No. of poles: 10, 180°, Box
1930140000	BVZ 7.62HP/11F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 6 mm ² , Pitch: 7.62 mm, No. of poles: 11, 180°, Box

1930150000 BVZ 7.62HP/12F SN SW

PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 6 mm², Pitch: 7.62 mm, No. of poles: 12, 180°, Box